



Philips X-tremeUltinon  
LED  
car signaling bulb

#### LED-RED [~P21/5W]

Number of bulbs: 2  
Advanced automotive system



12899RX2

## Brighter and more stylish

Strong, durable and vibrant LED signaling

For safe and modern driving, change to intense red Philips X-tremeUltinon LED stop & tail lights [~P21/5W]. They are powerful, precise and look good so you can signal in safety and with style.

#### Brighter LED exterior lights

- Signal your intent with brighter exterior lighting
- Instantly on lights make rapid braking safer

#### Upgrade your style

- Upgrade your lights, upgrade your style

#### Superior light diffusion

- Uniform light distribution for enhanced visibility

#### Longer lasting LED lights

- Durable and long-lasting LED lighting

#### Exceptional Philips quality

- Philips automotive lighting at the highest quality level
- Easy installation and compatible with many car models

# PHILIPS

# Highlights

## Bright and vibrant signals

Signaling the intended movement of your vehicle is vital to your safety. To avoid collisions, other people need to know what you're doing. And when poor weather conditions reduce visibility, the need for bright and vibrant signaling becomes even more important. Philips X-tremeUltinon LED signaling lights provide you with bright daylight effect and up to 6000K for reverse and positioning lights. With more intense colors for turn and stop applications, instantly on LEDs and a uniform and well-directed light, you'll give other drivers vital extra time to react to your movements.

## Stylish signaling colors

While the main goal of exterior lighting is to help you see and be seen, there's no reason why you shouldn't look good at the same time. If you're looking to upgrade your style, without buying a newer car, replacing your exterior lighting with LEDs is a smart way to spend your money. Upgrade your exterior lighting with a more intense red for stop lights, a vibrant amber for turning signals and bright white light for positioning and reversing. Your car is an expression of who you are, so make a style statement with Philips exterior signaling LED lights.

## Instantly on brake lights

Incandescent lamps take time to light up and reach peak performance. LED lights, on the other hand, are "instantly on". The difference is measured in fractions of a second. Under hard braking, fractions of a second matter. For example, at 100 km/h, just four tenths of a second difference in reaction time equates to an extra 11 meters of reaction distance – that's about 2.5 car lengths of extra thinking time. With Philips LED stop lights, as soon as you decide to brake, the driver behind will know.

## Uniform light distribution

Philips LED exterior lighting range is designed for a smarter light distribution to ensure that exterior signaling light is projected where you need it

(whether that's reversing, stopping, or signaling). With wide angle and uniform light diffusion, not only can you see more of the road, other drivers can see more of you.

## Automotive grade quality

The technologically advanced Philips lighting is renowned in the automotive industry, and has been for over 100 years. The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards. Major car manufacturers choose Philips lamps, because when you buy Philips, you buy quality. You get powerful bright light, and precise beam performance. You get high-end style. And you get an advanced LED lighting system for a safer, smoother and more enjoyable drive.

## Ready, steady, installed!

Designed to be easily installed in compatible vehicles, drivers with maintenance experience will be able to upgrade compatible lights with ease. However, it's recommended that you get your new Philips X-tremeUltinon LED lights installed by specialist mechanics – they will make sure you're ready to go. While these lamps are compatible with a wide range of existing car models, not all car types are supported.

## Long-lasting LED lighting

You want bright and stylish car lights. But you don't want to keep replacing failed lamps. That is a major weakness of conventional headlights; the more powerful the light, the shorter its lifespan. At the same light intensity, LEDs last much longer. And Philips X-tremeUltinon LED lights are extremely durable. Due to the latest technological innovation, they prevent heat and vibrational damage and last up to 12 years. With most cars replaced or upgraded within that time, your stylish new lights should last you the lifetime of your car.

# Specifications

## Packaging Data

- EAN1: 8727900396027
- EAN3: 8727900396034
- Packaging type: X2

## Marketing specifications

- Expected benefits: Advanced automotive system

## Lifetime

- Life time: Up to 12 years

## Ordering information

- Order entry: 12899RX2
- Ordering code: 39602730

## Outerpack information

- Gross weight per piece: 0.6 kg
- Height: 8.5 cm
- Length: 19.5 cm
- Width: 15.1 cm

## Packed product information

- Height: 9.2 cm
- Length: 6.8 cm
- MOQ (for professionals): 20
- Pack Quantity: 2
- Width: 2.8 cm

## Product description

- Application: Stop/tail
- Range: X-tremeUltinon LED
- Technology: LED
- Type: P21/5W



Issue date 2017-06-16

Version: 14.1.5

12 NC: 9237 953 17112  
EAN: 87 27900 38420 8

© 2017 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* This LED retrofit light is specifically designed and intended for off-road use only. It is your own responsibility that the use of the LED retrofit light complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability.