

# PHILIPS

Headlight bulb

X-tremeVision LED  
Moto

Type of lamp: H4

Pack of: 1

13.2 V, 23 W

12953BW1



## Maximum road safety and style

### Sparkling bright effect

Standout from the crowd. Upgrade your two wheeler style with Philips intense bright LED headlights, and get a sophisticated and modern light appearance, and a perfect color match with LED day running lights.

#### Intense bright headlight

- Intense bright headlight

#### Maximum road safety

- Up to +100 % more brightness

#### Constant brightness lighting

- Constant light brightness over entire motorcycle lifetime

#### 2 year limited warranty


- 2 year limited warranty for consumer usage

# Highlights

## Intense bright headlight

Philips LEDs headlight provides the most intense light upgrade solution to your two wheeler, with a perfect color match with LED day running lights, for a sophisticated and modern light appearance

## Maximum road safety



With up to +100%\* more brightness, Philips LED headlight brings you the best night driving experience, with improved eyes comfort and driving safety (\*Up to 100% more brightness compared to standard OEM halogen lamp, based on average of top 5 market representative scooter luminaires)

## Constant brightness lighting



Philips high power LEDs and Airflux optimal thermal management ensure ultra-long service life, with constant light out brightness over your entire motorcycle lifetime\*  
\*Constant light output after motorcycle usage of 10 years, based on 500 hours' usage per year

## 2 year limited warranty



Philips is committed to the high quality LED bulb supply. So Philips offers a 2-year warranty for supporting and using Philips LED bulbs. Philips LED bulbs that fail to work properly as a result of a product defect in non-commercial applications during the 2-year period are covered by the warranty. Terms and conditions applied.

# Specifications

## Packaging Data

EAN1: 8727900396379

## Light characteristics

Color temperature: White 6000 K

## Marketing specifications

Expected benefits: Maximum road safety and style

Product highlight: Up to +100% more brightness

## Product description

Range: X-tremeVision LED Moto

Technology: LED

Base: P43T

Application: High beam, Low beam

Type: H4

## Lifetime

Life time: 5000h

## Electrical characteristics

Voltage: 12 V

Wattage: 23 W

## Ordering information

Order entry: 12953BW1

## Logistic data

Quantity in box: X1

