

Philips  
LCD monitor with  
SmartControl Lite

V Line  
20 (19.5" / 49.5 cm diag.)

203V5LSB26



## Great LED images in vivid colors

Enjoy vivid LED pictures on this Philips display. Equipped with SmartControl lite, it's a great choice!

### **Vivid pictures every time**

- LED technology for vivid colors
- Easy display performance tuning with SmartControl Lite

### **Great choice**

- Compact design saves space
- Mercury Free eco-friendly display
- VESA mount allows for flexibility

# PHILIPS

# Specifications

## Picture/Display

- LCD panel type: TFT-LCD
- Backlight type: W-LED system
- Panel Size: 19.5 inch / 49.5 cm
- Effective viewing area: 433.9 (H) x 236.3 (V)
- Aspect ratio: 16:9
- Optimum resolution: 1600 x 900 @ 60 Hz
- Response time (typical): 5 ms
- Brightness: 200 cd/m<sup>2</sup>
- Contrast ratio (typical): 600:1
- Pixel pitch: 0.26 x 0.26 mm
- Viewing angle: 90° (H) / 50° (V), @ C/R > 10
- Display colors: 16.7 M
- Scanning Frequency: 30 -83 kHz (H) / 56 -75 Hz (V)
- sRGB

## Connectivity

- Signal Input: VGA (Analog)
- Sync Input: Separate Sync, Sync on Green

## Convenience

- User convenience: Power On/Off
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
- Other convenience: Kensington lock, VESA mount (100x100mm)
- Plug & Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 7, Windows 8

## Stand

- Tilt: -3/10 degree

## Power

- On mode: 14.52 W (typ.) (EnergyStar 6.0 test method)
- Standby mode: 0.5 W (typ.)
- Off mode: 0.5 W (typ.)

- Power LED indicator: Operation - White, Standby mode- White (blinking)
- Power supply: Built-in, 100-240VAC, 50-60Hz

## Dimensions

- Product with stand (mm): 465 x 345 x 170 mm
- Product without stand (mm): 465 x 285 x 48 mm
- Packaging in mm (WxHxD): 503 x 350 x 109 mm

## Weight

- Product with stand (kg): 2.33 kg
- Product without stand (kg): 2.03 kg
- Product with packaging (kg): 3.23 kg

## Operating conditions

- Temperature range (operation): 0°C to 40°C °C
- Temperature range (storage): -20°C to 60°C °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Non-operation: +40,000ft (12,192m)
- MTBF: 30,000 hour(s)

## Sustainability

- Environmental and energy: EnergyStar 6.0, EPEAT Silver, RoHS, Lead-free, Mercury Free
- Recyclable packaging material: 100 %

## Compliance and standards

- Regulatory Approvals: BSMI, CE Mark, FCC Class B, GOST, SEMKO, TUV/ISO9241-307, cETLus, WEEE

## Cabinet

- Color: Black
- Finish: Hairline (front bezel) / Texture (rear cover)

## What's in the box?

- Monitor with stand
- Cables: VGA, Power
- User Documentation

# Highlights

## LED technology

White LED's are solid state devices which light up to full, consistent brightness faster saving startup time. LED's are free from mercury content which allows for eco-friendly recycling and disposal process. LED's allow for better dimming control of LCD backlight, resulting in super high contrast ratio. It also gives superior color reproduction thanks to consistent brightness across the screen.

## SmartControl Lite

SmartControl Lite is the next generation 3D icon based GUI monitor control software. This allows user to fine-tune most parameters of the monitor like Color, Brightness, screen calibration, Multimedia, ID management, etc with the mouse.

## Mercury Free

Philips monitors with LED backlighting are free of Mercury content, one of the most toxic natural substances, which affects humans and animals. This reduces the environmental impact of the display throughout its life-cycle, from manufacturing to disposal.



Issue date 2018-03-22

Version: 4.0.1

12 NC: 8670 001 03168  
EAN: 87 12581 68838 7

© 2018 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)