



Philips 4200 series
Full HD Ultra Slim LED TV
with Digital Crystal Clear

55 cm (22")

Full HD LED TV
DVB T/C/T2/T2-HD/S/S2



22PFS4232

Full HD Ultra Slim LED TV

with Digital Crystal Clear

Feel at home wherever you are with the Philips 4200 TV. Compact in size, it's the perfect companion for camping trips or adventures. With a Full HD screen and slim design, it's great for small rooms and can be powered by a 12 volt input.

As flexible as you are

- Compact portable TV: designed to be where the fun is

A clear, vivid picture every time

- Digital Crystal Clear for precision you'll want to share
- Full HD LED TV—brilliant LED images with incredible contrast

Television viewing at your convenience

- Two HDMI inputs and Easylink for integrated connectivity
- USB for multimedia playback
- 12 volt DC power adapter connects TV to mobile power source

PHILIPS

Highlights

Portable Design

Stylish, compact and lightweight. Your small screen TV lets you catch up with your favorite programs in the kitchen, keeps you up to date with the news while you work in the garage, and gives you the latest sports scores as you BBQ. A TV this portable likes to be where the fun is!

Digital Crystal Clear

For natural looking pictures from any source, Philips created Digital Crystal Clear. Whether you're indulging in your favorite shows, movies, the news, or are simply having a few friends over for a night in, you'll enjoy it all in optimal contrast, color and sharpness.

Full HD LED TV

Picture Quality matters. Regular HDTVs deliver quality, but you expect more. Imagine crisp detail paired with high brightness, incredible contrast and realistic colors for a true to life picture.

Two HDMI inputs with Easylink

Avoid cable clutter with a single HDMI cable to carry both picture and audio signals from your devices to your TV. HDMI uses uncompressed signals, ensuring the highest quality from source to screen. Together with Philips Easylink, you'll need only one remote control to perform most operations on your TV, DVD, Blu-ray, set top box or home theatre system.

USB (photos, music, video)

Share the fun. Connect your USB memory-stick, digital camera, mp3 player or other multimedia device to the USB port on your TV to enjoy photos, videos and music with the easy to use onscreen content browser.

12 volt DC power adapter

Connect your TV easily when on the road using a 12 volt DC power adapter attached to your car, truck, boat, or any 12 volt power source.

Specifications

Picture/Display

- Display: LED Full HD
- Diagonal screen size: 22 inch / 55 cm
- Panel resolution: 1920x1080p
- Aspect ratio: 4:3/16:9
- Brightness: 250 cd/m²
- Picture enhancement: Digital Crystal Clear
- Peak Luminance ratio: 65 %

User Interaction

- Program: Pause TV, USB Recording*
- Ease of Use: One-stop Home button
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB
- Signal strength indication
- Teletext: 1000 page Hypertext
- Electronic Program Guide*: 8days Electronic Program Guide
- Screen Format Adjustments: Autozoom, Superzoom, Movie expand 16:9, Unscaled, 4:3, 16:9

Sound

- Output power (RMS): 6W
- Sound Enhancement: Incredible Surround, Clear Sound, Auto Volume Leveler, Bass Control, Smart Sound

Connectivity

- Number of HDMI connections: 2
- Number of USBs: 1
- Number of scarts (RGB/CVBS): 1
- Other connections: Common Interface Plus (CI+), Digital audio out (optical), Antenna IEC75, Satellite Connector, Audio in (DVI), Headphone out
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play

Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1, HEVC (H.265)
- Subtitles Formats Support: .SMI, .SRT, .SSA, .SUB, .TXT, .ASS
- Music Playback Formats: AAC, MP3, WAV, WMA

(v2 up to v9.2)

- Picture Playback Formats: JPEG, BMP, GIF, PNG

Supported Display Resolution

- Computer inputs: up to 1920x1080 @ 60Hz
- Video inputs: 24, 25, 30, 50, 60 Hz, up to 1920x1080p

Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM
- Teletext: 1000 page Hypertext

Power

- Mains power: AC 220 - 240 V 50/60Hz
- Standby power consumption: <0.3W
- Off mode power consumption: <0.3
- Ambient temperature: 5 °C to 35 °C
- Power Saving Features: Auto switch-off timer, Eco mode, Picture mute (for radio)
- Energy Label Class: A
- Eu Energy Label power: 19 W
- Annual energy consumption: 28 kWh
- Mercury content: 0 mg
- Presence of lead: Yes*


Dimensions

- Box dimensions (W x H x D): 595 x 475 x 112 mm
- Set dimensions (W x H x D): 512.3 x 317 x 54.1 mm
- Set dimensions with stand (W x H x D): 512.3 x 317 x 133.2 mm
- TV stand width distance: 448.5 mm
- Product weight: 2.6 kg
- Product weight (+stand): 2.65 kg
- Weight incl. Packaging: 3.75 kg
- Wall mount compatible: 75 x 75 mm

Accessories

- Included accessories: Remote Control, 2 x AAA Batteries, DC power adapter, 12 volt DC power car adapter, Quick start guide, Legal and safety brochure, Table top stand

Connections



Issue date 2022-07-14

Version: 5.1.1

12 NC: 8670 001 44278
EAN: 87 18863 01141 6

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* EPG and actual visibility (up to 8 days) is country and operator dependent.

* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

* (Philips) only compatible with specific Philips player device.

* This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.