



Philips Moda
Slim monitor with Ultra
Wide-Color

C Line

24 (23.8"/60.5 cm diag.)
Full HD (1920 x 1080)

245C7QJSB



Ultra Wide-Color in an ultra-slim design

The Moda display with Ultra Wide-Color features superb visuals, in our thinnest design yet. Crafted with premium materials, the thin display looks great on any desk. With an edge-to-edge Ultra Wide-Color display, images look bolder than ever

Superb Design

- Minimalistic looks with Ultra-Narrow Bezel
- UltraSlim for a stylish look
- EasySelect menu toggle key for quick on-screen menu access

Superb Picture Quality

- Ultra Wide-Color wider range of colours for a vivid picture
- IPS LED wide view technology for image and colour accuracy
- 16:9 Full HD display for crisp, detailed images
- Less eye fatigue with Flicker-Free technology
- SmartContrast for deep black level details
- SmartImage pre-sets for easy optimised image settings

Experience immersive multimedia

- HDMI-ready for Full HD entertainment
- DisplayPort connection for maximum visuals



PHILIPS

Highlights

Ultra-Narrow Bezel

Utilising the latest technology panels, the new Philips displays are designed with a minimalistic approach by limiting the outer bezel thickness to about 2.5 mm. Combined with an in-panel black matrix strip of around 9 mm, the overall bezel dimensions are reduced significantly, minimising distractions and maximising viewing size. Especially suited to multi-display or tiling setups like gaming, graphics design and professional applications, the Ultra-narrow bezel display gives you the feeling of using one large display.

UltraSlim for a stylish look




Our new display is impossibly thin! The UltraSlim profile offers a minimalistic look that looks great in living spaces and desks.

Ultra Wide-Color Technology



Ultra Wide-Color Technology delivers a wider spectrum of colours for a more brilliant picture. The Ultra Wide-Color wider "colour gamut" produces more natural-looking greens, vivid reds and deeper blues. Bring media entertainment, images and even productivity more alive with vivid colours from Ultra Wide-Color Technology.

IPS technology



IPS displays use an advanced technology that gives you extra-wide viewing angles of 178/178 degrees, making it possible to view the display from almost any angle. Unlike standard TN panels, IPS displays give you remarkably crisp images with vivid colours, making them ideal not only for Photos, movies and web browsing, but also for professional applications that demand colour accuracy and consistent brightness at all times.

16:9 Full HD display



Picture quality matters. Regular displays deliver quality, but you expect more. This display features enhanced Full HD 1920 x 1080 resolution. With Full HD for crisp detail paired with high brightness, incredible contrast and realistic colours, expect a true-to-life picture.

Flicker-Free technology



Due to the way brightness is controlled on LED-backlit screens, some users experience flicker on their screen which causes eye fatigue. Philips Flicker-Free technology applies

a new solution to regulate brightness and reduce flicker for more comfortable viewing.

SmartContrast



SmartContrast is a Philips technology that analyses the contents you are displaying, automatically adjusting colours and controlling backlight intensity to dynamically enhance contrast for the best digital images and videos or when playing games where dark hues are displayed. When Economy mode is selected, contrast is adjusted and backlighting fine-tuned for just-right display of everyday office applications and lower power consumption.



COMPUTEX d&i awards

Ultra-Wide Colour in an ultra-slim design
Excellent product design for an extremely slim, frameless display supported by a finely crafted open-frame metal stand.



ENERGY STAR Most Efficient 2017

It is an award that truly represents the best of ENERGY STAR.
Introducing ENERGY STAR Most Efficient 2017, a new distinction that recognises products that deliver cutting edge energy efficiency along with the latest technological innovation.



Specifications

Picture/Display

- LCD panel type: IPS technology
- Backlight type: W-LED system
- Panel Size: 23.8 inch/60.5 cm
- Effective viewing area: 527.04 (H) x 296.46 (V)
- Aspect ratio: 16:9
- Optimum resolution: 1920 x 1080 @ 60 Hz
- Pixel Density: 92.56 PPI
- Response time (typical): 5 ms (Grey to Grey)*
- Brightness: 250 cd/m²
- Contrast ratio (typical): 1000:1
- SmartContrast: 20,000,000:1
- Pixel pitch: 0.274 x 0.274 mm
- Viewing angle: 178° (H)/178° (V), @ C/R > 10
- Flicker-free
- Picture enhancement: SmartImage
- Colour gamut (typical): NTSC 106%*, sRGB 127%*
- Display colours: 16.7 M
- Scanning Frequency: 54 - 88 kHz (H) / 48 - 75 Hz (V)
- sRGB

Connectivity

- Signal Input: VGA (Analogue), DisplayPort 1.2, HDMI (digital, HDCP)
- Sync Input: Separate Sync, Sync on Green
- Audio (In/Out): Audio out

Convenience

- User convenience: Menu/OK, Input/Up, SmartImage/Return, Volume/Down, Power On/Off
- Control software: SmartControl
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
- Other convenience: Kensington lock
- Plug and Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 10 / 8.1 / 8 / 7

Stand

- Tilt: -5/20 degree degree

Power

- On mode: 13.65 W (typ.) (EnergyStar 7.0 test method)
- Standby mode: 0.3 W (typ.)
- Off mode: 0.3 W (typ.)
- Power LED indicator: Operation - White, Standby mode - White (flashing)
- Power supply: External, 100–240 VAC, 50–60 Hz

Dimensions

- Product with stand (mm): 541 x 412 x 197 mm
- Product without stand (mm): 541 x 323 x 31 mm
- Packaging in mm (W x H x D): 603 x 484 x 245 mm

Weight

- Product with stand (kg): 2.87 kg
- Product with packaging (kg): 5.30 kg

Operating conditions

- Temperature range (operation): 0 to 40 °C
- Temperature range (storage): -20 to 60 °C
- Relative humidity: 20%–80% %
- Altitude: Operation: +12,000 ft (3658 m), Non-operation: +40,000 ft (12,192 m)
- MTBF: 50,000 hrs (Excluding backlight) hour(s)

Sustainability

- Environmental and energy: EnergyStar 7.0, RoHS, Lead-free, Mercury Free
- Recyclable packaging material: 100 %

Compliance and standards

- Regulatory Approvals: CE Mark, FCC Class B, RCM, CECP, CU, SASO, KUCAS, cETLus, TUV/ISO9241-307, EPA, WEEE

Cabinet

- Front bezel: Black
- Rear cover: Grey
- Finish: Glossy

What's in the box?

- Monitor with stand
- Cables: D-Sub cable, HDMI cable, Power cable
- User Documentation



Issue date 2019-10-03

Version: 7.0.2

12 NC: 8670 001 40637
EAN: 87 12581 74156 3

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* "IPS" word mark / trademark and related patents on technologies belong to their respective owners.

* Response time value equal to SmartResponse

* NTSC Area based on CIE 1976

* sRGB Area based on CIE 1931