

Philips Evnia Curved Gaming Monitor Full HD gaming monitor

Evnia 5000

32 (31.5" / 80 cm diag.) 1920 x 1080 (Full HD)

32M1C5200W

# Feel your game

This Philips gaming monitor is designed for the highest intensity gameplay. Sync technology, ultra-fast 240Hz refresh rate and 0.5ms response time create tear-free and low latency gameplay. SmartImage HDR gives a vibrant, lifelike display.

### The gaming advantage is yours

- Ultra-fast 240 Hz refresh rate for virtually lag-free gaming
- 0.5 ms ultra-fast speed for crisp image and smooth gameplay
- Low input lag reduces time delay between devices to monitor
- SmartImage game mode optimized for gamers

#### **Immersive visuals**

- VA display delivers awesome images with wide viewing angles
- 16:9 Full HD display for crisp detailed images
- · Curved display design for more immersive experience

#### Features designed for you

- · LowBlue mode and Flicker-free easy-on-the eyes viewing
- Tilt, swivel and height-adjust for an ideal viewing position
- EasySelect menu toggle key for quick on-screen menu access

## Highlights

#### Ultra-fast 240 Hz refresh rate




While playing the most intense engaging action-oriented games, ultra-fast 240 Hz refresh rate enhances an ultra-smooth, lag-free gaming experience. This Philips display redraws the screen image up-to 240 times per second, effectively faster than a standard display. Especially for fast-paced games like FPS and racing games, 240 Hz gives a superior motion and clarity visuals. With Philips 240 Hz display, action sequences in gameplay look judder-free and ghost-free. You will experience deeper immersion and feeling alive in game.

#### 0.5 ms MPRT fast response



Philips Momentum display with 0.5 ms MPRT effectively eliminates smearing and motion blur, delivers shaper and precise visuals to enhance gaming experience. Fast-moving action and dramatic transitions will be rendered smoothly. Best choice for playing thrilling and twitch-sensitive games.

#### **Low Input Lag**



Input lag is the amount of time that elapses between performing an action with connected devices and seeing the result on screen. Low input lag reduces the time delay between entering a command from your devices to monitor, greatly improve on playing twitch-sensitive video games, particularly important to whom plays fast-paced, competitive games.

#### **VA** display



Philips VA LED display uses an advanced multidomain vertical alignment technology which gives you super-high static contrast ratios for extra vivid and bright images. While standard office applications are handled with ease, it is especially suitable for photos, web-browsing, movies, gaming, and demanding graphical applications. It's optimized pixel management technology gives you 178/178 degree extra wide viewing angle, resulting in crisp images.

#### 16:9 Full HD display



Picture quality matters. Regular displays deliver quality, but you expect more. This display

features enhanced Full HD 1920  $\times$  1080 resolution. With Full HD for crisp detail paired with high brightness, incredible contrast and realistic colors expect a true to life picture.

#### Curved display design



Desktop monitors offer a personal user experience, which suits a curve design very well. The curved screen provides a pleasant yet subtle immersion effect, which focuses on you at the center of your desk.

#### LowBlue Mode & Flicker-free



Our LowBlue Mode and Flicker-free technology have been developed to reduce eye strain and fatigue often caused by long hours in front of a monitor.

#### **Compact Ergo Base**



The Compact Ergo Base is a people-friendly Philips monitor base that tilts, swivels and height-adjusts so each user can position the monitor for maximum viewing comfort and efficiency.





















### **Specifications**

#### Picture/Display

- LCD panel type: VA LCD
- · Backlight type: W-LED system
- Panel Size: 31.5 inch / 80 cm
- Display Screen Coating: Anti-Glare, 3H, Haze 25%
- Effective viewing area: 698.4 (H) x 392.85 (V) -> at
- a 1500R curvature\*
- Aspect ratio: 16:9 Maximum resolution: 1920 x 1080 @ 240 Hz\*
- Pixel Density: 69.93 PPI
- Response time (typical): 4 ms (Gray to Gray)\*
- MPRT: 0.5 ms
- · Low Input Lag
- Brightness: 300 cd/m<sup>2</sup>
- SmartContrast: Mega Infinity DCR
- Contrast ratio (typical): 3500:1
- Pixel pitch: 0.36375 x 0.36375 mm
- Viewing angle: 178° (H) / 178° (V), @ C/R > 10
- · Flicker-free
- Picture enhancement: SmartImage game
- Display colors: 16.7 M (8 bit)
- Color gamut (typical): NTSC 100.1%\*, sRGB
- Scanning Frequency: 30 255 kHz (H) / 48 240 Hz
- · LowBlue Mode
- EasyRead
- sRGB
- · Adaptive sync

#### Connectivity

- Signal Input: HDMI 2.0 x 2, DisplayPort 1.4 x 1
- HDCP: HDCP 1.4 (HDMI / DisplayPort), HDCP 2.2 (HDMI / DisplayPort)
- Audio (In/Out): Audio out
- Sync Input: Separate Sync

#### Convenience

- User convenience: Power On/Off, Menu/OK, Input/Up, Game Settings/Down, SmartImage game/
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Simplified Chinese, Swedish, Turkish, Traditional Chinese, Ukrainian
- Other convenience: Kensington lock, VESA mount (100×100mm)
- Plug & Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 11 / 10 / 8.1 / 8 / 7

#### Stand

· Height adjustment: 130 mm

- Swivel: -/+ 45 degree
- Tilt: -5/20 degree

#### **Power**

- On mode: 39.4 W (typ.)
- Standby mode: 0.5 W (typ.)
- Off mode: 0.3 W (typ.)
- · Energy Label Class: E
- Power LED indicator: Operation White, Standby mode- White (blinking)
- Power supply: Internal, 100-240VAC, 50-60Hz

#### **Dimensions**

- Product with stand(max height): 709 x 638 x 308 mm
- Product without stand (mm):  $709 \times 423 \times 95 \text{ mm}$
- Packaging in mm (WxHxD):  $782 \times 523 \times 227$  mm

#### Weight

- Product with stand (kg): 7.61 kg
- Product without stand (kg): 6.10 kg
- Product with packaging (kg): 9.97 kg

#### **Operating conditions**

- $\bullet$  Temperature range (operation): 0°C to 40 °C
- Temperature range (storage): -20°C to 60 °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Nonoperation: +40,000ft (12,192m)
- MTBF: 50,000 (Excluded backlight) hour(s)

#### Sustainability

- · Environmental and energy: RoHS
- Recyclable packaging material: 100 %
- Specific Substances: Mercury free, PVC / BFR free housing

### Compliance and standards

• Regulatory Approvals: CB, CE Mark, FCC Class B, ICES-003, CU-EAC, EAEU RoHS, TUV/ISO9241-307, TUV-BAUART

- · Color: Black
- · Finish: Textured

#### What's in the box?

- · Monitor with stand
- · Cables: HDMI cable, DisplayPort cable, Power cable
- User Documentation

\* Radius of the arc of the display curvature in mm \* The maximum resolution works for either HDMI input or DP input.

\* For best output performance, please always ensure that your g card is capable of achieving the maximum resolution and refresh rate of this Philips display.

Response time value equal to SmartResponse

\* MPRT is to adjust brightness for blur reduction, so cannot adjust brightness while MPRT is turned on. To reduce motion blur, LED backlight will strobe synchronously with screen refresh, which may cause noticeable brightness change.

\* MPRT is gaming-optimized mode. Turn on MPRT may cause noticeable screen flickering. It is recommended to turn off when you are not using the gaming function
NTSC Area based on CIE1976

- \* sRGB Area based on CIE1931
- \* The monitor may look different from feature images.

Issue date 2023-08-23 © 2023 Koninklijke Philips N.V.

All Rights reserved.

Version: 2.0.1 Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V.

or their respective owners.

12 NC: 8670 001 88395 EAN: 87 12581 80071 0

www.philips.com