

Philips Evnia Gaming Monitor 4K UHD gaming monitor

Evnia 5000 32 (31.5" / 80 cm diag.) 3840 x 2160 (4K UHD)

32M1N5800A

Feel your game

This Philips gaming monitor brings games to life with its 4K IPS display and DisplayHDR 400. Rapid 144Hz refresh rate, 1ms response time and Sync technology guarantee smooth visuals.

Best synchronization between GPU and monitor

- Certified NVIDIA® G-SYNC® compatible for smooth fast gaming
- AMD FreeSync™ Premium; tear free, stutter free, fluid gaming

Meet the most recent update of HDMI specification

- UltraClear 4K UHD (3840x2160) resolution for precision
- 144Hz refresh rates for ultra-smooth, brilliant images
- · Low input lag reduces time delay between devices to monitor
- \bullet SmartImage HDR gives optimal viewing from your HDR content

Immersive visuals

- IPS LED wide view technology for image and color accuracy
- $\bullet\,$ Ultra Wide-Color wider range of colors for a vivid picture

Features designed for you

- SIAA certified antibacterial treatment to keep sanitary
- MultiView enables simultaneous dual connection and view
- 1ms (MPRT) fast response for crisp image and smooth gameplay





Highlights

AMD FreeSync™ Premium



AMD FreeSync™ OFF

AMD FreeSync™ ON

Gaming shouldn't be a choice between choppy gameplay or broken frames. AMD FreeSync™ Premium equips serious gamers with a fluid, tear-free gameplay experience at peak performance. There are no compromises, game confidently with a high refresh rate, low framerate compensation, and low latency.

NVIDIA[®] G-SYNC[®] compatible



When playing intense games with high refresh rates, screen tearing may appear without optimal graphics synchronization. This Philips display is certified as NVIDIA® G-SYNC® compatible, reducing screen tearing and syncing your monitor's refresh rate with your graphic card's output for a smoother gaming experience. Scenes appear instantly, objects look sharper, and gameplay is smooth, giving you a stunning visual experience and a serious competitive edge.

UltraClear 4K UHD resolution



These Philips displays utilize high performance panels to deliver UltraClear, 4K UHD (3840 \times

2160) resolution images. Whether you are demanding professional requiring extremely detailed images for CAD solutions, using 3D graphics applications or a financial wizard working on huge spreadsheets, Philips displays will make your images and graphics come alive.

144Hz Gaming




You play intense, competitive gaming. You demand display with lag free, ultra-smooth images. This Philips display redraws the screen image up-to 144 times per second, effectively 2.4x faster than a standard display. A lower frame rate can make enemies appear to jump from spot to spot on the screen, making them difficult targets to hit. With 144Hz frame rate, you get those critical missing images on the screen which shows enemy movement in ultrasmooth motion so you can easily target them. With ultra-low input lag and no screen tearing, this Philips display is your perfect gaming partner

1ms MPRT fast response



MPRT (motion picture response time) is more intuitive way to describe the response time, which directly refers the duration from seeing blurry noise to clean and crisp images. Philips gaming monitor with 1 ms MPRT effectively eliminates smearing and motion blur, delivers shaper and precise visuals to enhance gaming experience. Best choice for playing thrilling and twitch-sensitive games.

Low Input Lag



Input lag is the amount of time that elapses between performing an action with connected devices and seeing the result on screen. Low input lag reduces the time delay between entering a command from your devices to monitor, greatly improve on playing twitch-sensitive video games, particularly important to whom plays fast-paced, competitive games.

SmartImage HDR



Select one of SmartImage HDR modes to best suit your needs. HDR Game: Optimize for playing video games. With brighter white and darker black, the gaming scene is vivid and revealing more details, easily spot enemies hiding in the dark corner and shadows. HDR Movie: Ideal for watching HDR movie. Deliver better contrast and brightness for more realistic and immerse viewing experience. HDR Photo: Enhance red, green, and blue for lively visuals. DisplayHDR: VESA DisplayHDR certified*. Personal: Customize settings in picture menu. *Please refer to specification for HDR grade.

















Specifications

Picture/Display

- LCD panel type: IPS technology
- · Backlight type: W-LED system
- Panel Size: 31.5 inch / 80 cm
- Display Screen Coating: Anti-Glare, 3H, Haze 25%
 Effective viewing area: 697.344 (H) x 392.2344 (V)
- · Aspect ratio: 16:9
- Maximum resolution: 3840 x 2160 @ 144 Hz
- Pixel Density: 139.87 PPI
- Response time (typical): 1 ms (Gray to Gray)*
- MPRT: 1 ms
- · Low Input Lag
- Brightness: 500 cd/m²
- SmartContrast: Mega Infinity DCR
- Contrast ratio (typical): 1000:1
- Pixel pitch: 0.181 x 0.181 mm
- Viewing angle: 178° (H) / 178° (V), @ C/R > 10
- HDR: DisplayHDR 400 certified
- Color gamut (typical): NTSC 113%*, sRGB 124%*, Adobe RGB 87.5%*
- Picture enhancement: SmartImage game
- Display colors: Color support 1.07 billion colors
- Scanning Frequency: 30 255 kHz (H) / 48 144 Hz
- SmartUniformity: 93 ~ 105%
- Delta E: < 2 (sRGB)
- · LowBlue Mode
- EasyRead
- sRGB
- G-SYNC: Compatible (DP)*
- AMD FreeSync[™] technology: Premium

Connectivity

- Signal Input: $\dot{\text{HDMI}}$ 2.1 x 2, DisplayPort 1.4 x 2
- HDCP: HDCP 1.4 (HDMI / DP); HDCP 2.2 (HDMI
- USB:: USB-B x 1 (upstream), USB 3.2 Gen 1 x 4 (downstream with 2 fast charge B.C 1.2)
- Audio (In/Out): Audio out
- Sync Input: Separate Sync

Convenience

- Built-in Speakers: 5 W x 2
- MultiView: PBP (2x devices)
- · User convenience: Power On/Off, Menu/OK, Input/Up, Game Settings/Down, SmartImage game/
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Simplified Chinese, Swedish, Turkish, Traditional Chinese, Ukrainian
- · Other convenience: Kensington lock, VESA mount (100x100mm)
- Plug & Play Compatibility: DDC/CI, Mac OS X,

sRGB, Windows 10 / 8.1 / 8 / 7

- · Height adjustment: 130 mm
- Pivot: -/+ 90 degree
- Swivel: -/+ 45 degree
- Tilt: -5/20 degree

- On mode: 64.0 W (typ.)
- Standby mode: 0.5 W (typ.)
- Off mode: 0.3 W (typ.)
- Energy Label Class: G
- Power LED indicator: Operation White, Standby mode- White (blinking)
- Power supply: Internal, 100-240VAC, 50-60Hz

Dimensions

- Product with stand(max height): 715 x 640 x 297 mm
- Product without stand (mm): 715 x 420 x 60 mm
- Packaging in mm (WxHxD): $930 \times 526 \times 186$ mm

Weight

- Product with stand (kg): 10.55 kg
- Product without stand (kg): 7.74 kg
- Product with packaging (kg): 15.37 kg

Operating conditions

- Temperature range (operation): 0° C to 40 $^{\circ}$ C
- Temperature range (storage): -20°C to 60 °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Nonoperation: +40,000ft (12,192m)
- MTBF: 50,000 (Excluded backlight) hour(s)

Sustainability

- · Environmental and energy: RoHS
- Recyclable packaging material: 100 %
- Specific Substances: Mercury free, PVC / BFR free housing, SIAA

Compliance and standards

• Regulatory Approvals: CB, CE Mark, FCC Class B, ICES-003, CU-EAC, EAEU RoHS, TUV/ISO9241-307, TUV-BAUART

- · Color: Black
- Finish: Textured

What's in the box?

- · Monitor with stand
- · Cables: HDMI cable, DisplayPort cable, USB upstream cable, Power cable
- User Documentation

- * "IPS" word mark / trademark and related patents on technologies belong to their respective owners.
- * For best output performance, please always ensure that your graphic card is capable of achieving the maximum resolution and refresh rate of this Philips display.
- Response time value equal to SmartResponse
- * MPRT is to adjust brightness for blur reduction, so cannot adjust brightness while MPRT is turned on. To reduce motion blur, LED backlight will strobe synchronously with screen refresh, which may
- * MPRT is gaming-optimized mode. Turn on MPRT may cause noticeable screen flickering. It is recommended to turn off when you are not using the gaming function.

 * NTSC Area based on CIE1976

 * sRGB Area based on CIE1931

- * Adobe RGB Coverage based on CIE1976
 * NVIDIA® G-SYNC® support interface: DisplayPort
 * Make sure to update NVIDIA® G-SYNC® driver to the latest version, see more information on NVIDIA website: https://
- www.nvidia.com/

 * Make sure your graphic card supports NVIDIA® G-SYNC®
- * 2020 Advanced Micro Devices, Inc. All rights reserved. AMD, the AMD Arrow logo, AMD FreeSync™ and combinations thereof are trademarks of Advanced Micro Devices, Inc. Other product names used in this publication are for identification purposes only and may be trademarks of their respective companies
- * The monitor may look different from feature images.

Issue date 2023-05-17 © 2023 Koninklijke Philips N.V.

All Rights reserved.

Version: 7.2.1 Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V.

or their respective owners.

12 NC: 8670 001 79614 EAN: 87 12581 78106 4

www.philips.com