



Philips Cineos
widescreen flat TV with
Pixel Plus 2 and Ambilight

81 cm (32")

LCD
HD Ready

CINEOS

32PF9966



Turn up your viewing experience

with Pixel Plus 2 and Ambilight

Enjoy the ultimate viewing experience with this Philips Cineos Flat TV with premium picture quality from Pixel Plus 2, Ambilight and the latest LCD technology. The elegant design with a convenient swivel stand will enhance your interior.

Be an eyewitness

- HD LCD WXGA display, with a 1366 x 768p resolution
- HD Ready for the highest quality display of HD signals
- Pixel Plus 2 for better details, depth and clarity
- Active Control with Light Sensor optimizes picture quality

Slim, stylish design to complement your interior

- Matching design swivel stand included

Add a new dimension to your viewing

- Full-color ambient lighting enhances the viewing experience

One touch convenience

- Text Dualscreen to view teletext and TV simultaneously.
- 1200 page Hypertext for instant fast access to teletext

Advanced connection to your audio/video products

- DVI-I HD input with HDMI, VGA and Component video support

PHILIPS

Highlights

LCD WXGA display, 1366 x 768p

This WXGA display with state-of-the-art LCD screen technology gives you widescreen HD resolution of 1366 x 768p pixels. It produces brilliant flicker-free progressive scan pictures with optimum brightness and superb colors. This vibrant and sharp image will provide you with an enhanced viewing experience.

HD Ready

Enjoy the exceptional picture quality of High Definition pictures and be fully prepared for HD sources like HDTV settop box or Blu-ray disc. HD Ready is a protected label that offers picture quality beyond that of progressive scan. It conforms to strict standards laid out by EICTA to offer a HD screen that displays the benefits of resolution and picture quality of a High Definition signal. It has a universal connection for both analog YPbPr and uncompressed Digital connection of DVI or HDMI, supporting HDCP. It can display 720p, and 1080i signals at 50 and 60Hz.

Pixel Plus 2

Pixel Plus 2 is a digital picture processing technology that improves the resolution of still and moving pictures. It does more than adding pixels, it also makes the pixels better, resulting in incredible sharpness and picture depth every time and from any source. And it does not just improve the resolution either, because you also benefit from improved color reproduction, resulting in the finest color details and superior brilliance.

Ambilight

The full-color ambient lights offers you relaxed viewing and a unique ambiance via a soft light glow on the walls surrounding the TV. Research has shown that watching television with adapted ambient lighting promotes more relaxed TV viewing. the Ambilight colors automatically adapt to the images on the screen to add a new sensation to the viewing experience. The light can also be switched to fixed colors or various shades of white. In

standby mode, the lights can be operated to any color and create a unique ambiance in the room.

DVI-I with HDMI and YPbPr

A DVI-I input connects the non-compressed high-bandwidth digital RGB signal from source to screen. By eliminating the conversion of the digital signals to analog, it delivers an unblemished and noise-free image, that is clear and flicker-free. The DVI input supports HDCP copy protection that allows viewing of copy protected programs from Digital Settop boxes, DVD players and HD recorders. DVI-I is future proof as it can be connected to all HDMI devices (a converter cable is required). The DVI-I input also supports analog PC-VGA and YPbPr Component video signals (adapters supplied).



Specifications

Picture/Display

- Aspect ratio: 16:9
- Brightness: 600 cd/m²
- Dynamic screen contrast: 6000:1
- Response time (typical): 6 ms
- Viewing angle (H / V): 176 / 176 degree
- Diagonal screen size: 32 inch / 80 cm
- Display screen type: LCD WXGA Active Matrix TFT
- Color cabinet: Pearl - White Silver (11092)
- Panel resolution: 1366 x 768p
- Picture enhancement: 3D Combfilter, Active Control + Light sensor, Digital Natural Motion, Dynamic contrast enhancement, Jagged Line Suppression, Movie Plus, Pixel Plus 2, Progressive scan, Widescreen Plus
- Screen enhancement: Anti-Reflection coated screen

Ambilight

- Ambilight Features: Auto adaptive to video content, Full operation in stand-by
- Color Settings: Full Multi Color
- Dimming Function: Manual and via Light Sensor
- Preset modes: 6 Preset modes and user preset, 2 Active Adaptive preset modes

Supported Display Resolution

Computer formats

Resolution	Refresh rate
640 x 480	60Hz
800 x 600	60Hz
1024 x 768	60Hz
1280 x 768	60Hz

Video Formats

Resolution	Refresh rate
640 x 480i	1Fh
640 x 480p	2Fh
720 x 576i	1Fh
720 x 576p	2Fh
1280 x 720p	3Fh
1920 x 1080i	2Fh
1920 x 1152i	2Fh

Sound

- Output power (RMS): 2x15W
- Sound Enhancement: Auto Volume Leveller, Digital Signal Processing, Dynamic Bass Enhancement, Graphic Equaliser
- Sound System: Virtual Dolby Surround

Loudspeakers

- Built-in speakers: 4
- Loudspeaker types: Integrated woofers with wOOx, Dome tweeter

Tuner/Reception/Transmission

- Aerial Input: 75 ohm coaxial (IEC75)
- Tuner bands: Hyperband, S-Channel, UHF, VHF
- TV system: PAL, SECAM
- Video Playback: NTSC, PAL, SECAM

Connectivity

- Ext 1 Scart: Audio L/R, CVBS in/out, RGB
- Ext 2 Scart: Audio L/R, CVBS in/out, RGB, S-video in, Y/C
- Ext 3 Scart: Audio L/R, CVBS in
- Ext 4: DVI-I with HDCP, YPbPr, VGA PC-in, HDMI compatible
- Front / Side connections: Audio L/R in, CVBS in, Headphone Out, S-video in
- Other connections: Analog audio Left/Right out, Centre Speaker connection in, Subwoofer out

Convenience

- Child Protection: Child Lock+Parental Control
- Clock: Smart Clock
- Connection Enhancement: Cinema link, Easy link
- Ease of Installation: Auto Program Naming, Automatic Channel Install(ACI), Automatic Tuning System (ATS), Autostore, Fine Tuning, PLL Digital Tuning, Plug & Play, Program Name, Sorting
- Ease of Use: 9-channel smart surf list, Backlight side controls, Delta Volume per preset, Program List, Side Control, Smart Picture, Smart Sound
- Electronic Program Guide: NexTVIEW 3
- Picture in Picture: Text dual screen
- Remote Control: Multi-functional

- Remote control type: RC4302
- Screen Format Adjustments: 4:3, 6 Widescreen Modes, Auto Format, Movie expand 14:9, Movie expand 16:9, Subtitle and Heading Shift, Subtitle Zoom, Super Zoom, Widescreen
- Teletext: 1200 page Hypertext
- Teletext enhancements: Habit Watch, Program information Line, Word Search

Accessories

- Included accessories: DVI-I to VGA adapter, Tabletop swivel stand, VGA to YPbPr-Cinch cable, Wall mounting bracket
- Optional accessories: 5 in one connection cable, Floor stand

Dimensions


- Set dimensions (W x H x D): 875 x 610 x 107 mm
- Weight incl. Packaging: 35 kg
- Product weight: 22 kg
- Box dimensions (W x H x D): 100 x 105.1 x 234 mm

Power

- Ambient temperature: 5 °C to 40 °C
- Mains power: AC 220 - 240 V +/- 10%
- Power consumption: 145 W
- Standby power consumption: 1.3

stereo system						transmission system					
2CS DK	NICAM DK	2CS BG	NICAM BG	NICAM I	NICAM LL'	PAL BG	PAL DK	PAL I	SECAM BG	SECAM DK	SECAM LL'
•	•	•	•	•	•	•	•	•	•	•	•

Rear connectors



Side connectors



Issue date 2019-06-25

Version: 20.0.21

12 NC: 8670 000 22339
EAN: 87 10895 87933 0

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com