




Philips 4000 series
Ultra Slim LED TV with
Digital Crystal Clear

80 cm (32")

LED TV
DVB T/C/T2/T2-HD/S/S2



32PHS4032

Ultra Slim LED TV

with Digital Crystal Clear

Portable and beautiful. The Philips 4000 TV is designed to go wherever you do. With its ultra slim contour and clean white frame, it will look great in any room.

The right features presented elegantly

- Elegant white color lends a fresh modern look to every room

A clear, vivid picture every time

- Digital Crystal Clear for precision you'll want to share
- LED TV for images with incredible contrast
- Picture Performance Index improves every viewing element

Television viewing at your convenience

- Two HDMI inputs and Easylink for integrated connectivity
- USB for multimedia playback

PHILIPS

Highlights

Modern white design

We know you want a small screen TV that looks as great as it performs. That's why our design team paired an elegant frame of sophisticated white and gloss finish to create a fresh, modern design that compliments any room.

Digital Crystal Clear

For natural looking pictures from any source, Philips created Digital Crystal Clear. Whether you're indulging in your favorite shows, movies, the news, or are simply having a few friends over for a night in, you'll enjoy it all in optimal contrast, color and sharpness.

LED TV

With LED backlight you can enjoy low power consumption and beautiful lines combined with

high brightness, incredible contrast and vibrant colors.

Picture Performance Index



Picture Performance Index combines Philips display technology and advanced picture processing engines to improve the elements of perception: sharpness, motion, contrast and color. No matter the source, you'll always enjoy razor sharp pictures with incredible detail and depth, the deepest blacks, the brightest whites, and the most vivid, brilliant

colors as well as natural, lifelike skin tones every time.

Two HDMI inputs with Easylink

Avoid cable clutter with a single HDMI cable to carry both picture and audio signals from your devices to your TV. HDMI uses uncompressed signals, ensuring the highest quality from source to screen. Together with Philips Easylink, you'll need only one remote control to perform most operations on your TV, DVD, Blu-ray, set top box or home theatre system.

USB (photos, music, video)

Share the fun. Connect your USB memory-stick, digital camera, mp3 player or other multimedia device to the USB port on your TV to enjoy photos, videos and music with the easy to use onscreen content browser.

Specifications

Picture/Display

- Display: LED HD TV
- Diagonal screen size: 32 inch / 80 cm
- Panel resolution: 1366 x 768p
- Aspect ratio: 4:3/16:9
- Brightness: 280 cd/m²
- Peak Luminance ratio: 65 %
- Picture enhancement: Digital Crystal Clear

User Interaction

- Program: Pause TV, USB Recording*
- Ease of Use: One-stop Home button
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB
- Signal strength indication
- Teletext: 1000 page Hypertext
- Electronic Program Guide*: 8days Electronic Program Guide
- Screen Format Adjustments: Autozoom, Superzoom, Movie expand 16:9, Unscaled, 4:3, 16:9

Sound

- Output power (RMS): 16W
- Sound Enhancement: Incredible Surround, Clear Sound, Auto Volume Leveler, Bass Control, Smart Sound

Connectivity

- Number of HDMI connections: 2
- Number of scarts (RGB/CVBS): 1
- Number of USBs: 1
- Other connections: Common Interface Plus (CI+), Digital audio out (optical), Audio in (DVI), Headphone out, Antenna IEC75, Satellite Connector
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play

Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1, HEVC (H.265)
- Subtitles Formats Support: .SMI, .SRT, .SSA, .SUB,

- .TXT, .ASS
- Music Playback Formats: AAC, MP3, WAV, WMA (v2 up to v9.2)
- Picture Playback Formats: JPEG, BMP, GIF, PNG

Supported Display Resolution

- Computer inputs: up to 1366x768 @ 60Hz
- Video inputs: 24, 25, 30, 50, 60 Hz, up to 1366x768p

Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM

Power

- Mains power: AC 220 - 240 V 50/60Hz
- Ambient temperature: 5 °C to 35 °C
- Eu Energy Label power: 31 W
- Annual energy consumption: 46 kWh
- Energy Label Class: A+
- Standby power consumption: <0.3W
- Off mode power consumption: 0.5
- Power Saving Features: Auto switch-off timer, Eco mode, Picture mute (for radio)
- Presence of lead: Yes*
- Mercury content: 0 mg

Dimensions


- Box dimensions (W x H x D): 798 x 520 x 140 mm
- Set dimensions (W x H x D): 726.5 x 425.36 x 81.8 mm
- TV stand width distance: 341.44 mm
- Set dimensions with stand (W x H x D): 726.5 x 476.9 x 183.25 mm
- Product weight: 5.1 kg
- Product weight (+stand): 5.25 kg
- Weight incl. Packaging: 7.14 kg
- Wall mount compatible: 100 x 100 mm

Accessories

- Included accessories: Remote Control, 2 x AAA Batteries, Table top stand, Power cord, Quick start guide, Legal and safety brochure

Connections

Side



Rear



Issue date 2022-07-14

Version: 7.2.1

12 NC: 8670 001 43545
EAN: 87 18863 01098 3

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* EPG and actual visibility (up to 8 days) is country and operator dependent.

* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

* (Philips) only compatible with specific Philips player device.

* This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.