



Philips 7000 series  
Ultra Slim Smart Full HD  
LED TV with Ambilight 2-  
sided and Smart TV

**107cm (42")**

Full HD LED TV  
Dual Core  
DVB-T/T2/C/S/S2



**42PFS7189**

## Ultra Slim Smart Full HD LED TV

With Ambilight 2-sided

The Philips 7100 series Smart LED TV has an extreme narrow bezel with diamond cut trim that will capture your heart. But it's more than just good-looking: it's fully loaded with features like Ambilight, 3D, Skype™ and more.

### Light up your life. Love it. Live it.

- Ambilight changes the way you look at TV forever

### A TV that's more than Smart, it's beautiful

- Ultra Slim lines for a refined profile
- Frameless design: no bezel means more TV to love

### A picture so real, you'll forget it's TV

- Pixel Precise HD Engine: discover vivid Picture Quality
- 800Hz PMR for the ultimate in smooth moving images
- 3D realistically takes you places you've never been before

### Connect, communicate, record and share

- Smart TV: a whole new world to explore
- Keyboard remote control with pointer—more control than ever
- Wi-Fi Miracast™—mirror your smartphone screen to your TV
- Cloud TV and Cloud Explorer bring worlds together
- Multiroom TV—share live TV and recordings between TVs



**PHILIPS**

# Highlights

## Frameless design

Sleek. Minimalist. Discreet. Our frameless bezel is beautifully crafted from high quality glass and edged with an ultra thin aluminum wrap; minimizing the frame and maximizing your viewing.

## Ambilight 2-sided

You've created a home that's more than just a house, so why not choose a TV that is warm and inviting too? Philips unique Ambilight technology makes your screen much wider—and your viewing experience more immersive—by projecting an extra wide glow from two-sides of your TV screen onto the surrounding wall. Color, vibrancy and excitement move beyond the screen and into your living room, bringing with it a more thrilling, intense and immersive viewing experience.

## Ultra Slim profile

Sleek. Cutting edge. Refined. Precise. The Philips Ultra Slim silhouette. That something so slim can inspire so much interest shouldn't be surprising, given how much sophistication it will bring to your décor.

## Pixel Precise HD

The Philips Pixel Precise HD Engine brings the world to you. Experience your favorite nature and travel programs in vivid clarity. Drenched in color and high contrast thanks to deeper blacks and brighter whites, you'll explore new frontiers without ever leaving your couch.

## 800Hz Perfect Motion Rate

Nothing beats the adrenaline rush of gaming, fast paced sporting events or action films. That's why this Philips TV has 800Hz Perfect Motion Rate; so you'll enjoy the ultimate in smooth moving images. Because even though your pulse may jump, the image you're watching shouldn't.

## 3D

Enjoy hours of viewing comfort thanks to passive 3D technology that delivers you high quality 3D. Convert any 2D content into vivid and flawless 3D. The stylish, lightweight 3D glasses are comfortable to wear and do not require batteries.

## Smart TV

Discover a Smarter experience that lies beyond traditional TV. Rent and stream movies, videos or games from online video stores. Watch catch-up TV from your favorite channels and enjoy a growing selection of online apps such as Youtube.

## Keyboard RC with Pointer

Our totally intuitive remote control has all the usual functions like cursor keys, volume control and short cut buttons. And, for something extra, simply touch and hold the OK key for easy navigation. The pointer operates as a mouse allowing you to point, click, and scroll easily onscreen. Flip the remote over and there's a full keyboard for easy text entry on the other side! Best of all,

our intelligent remote has gyroscopic sensors, so it knows up from down—which means you can text without worrying about changing channels.

## Wi-Fi Miracast™\*

Mirror what you see on your smart device and share it with friends and family on your TV. From photos to videos, games and more, mirror anything from your smartphone and tablet to your big screen with a simple command.

## Cloud TV\* & Explorer

"Because you're unique, we think the way you watch TV should be too. With it's constantly growing selection, Philips Cloud TV lets you choose from hundreds of TV channels from around the world. Cloud Explorer makes sharing with friends near and far easy by allowing you to access your Dropbox™ account via your TV, letting you view your content on the big screen.

## Multiroom client & server

Break free of traditional broadcasting. Acting as a server, your Philips Smart TV has the power to connect to another TV on the same Wi-Fi network. Once connected, you can share digital broadcast TV and recordings from this TV to a client TV, all without laying new cables or spending money on multiple subscriptions.

# Specifications

## Ambilight

- Ambilight Version: 2 sided
- Ambilight Features: Dual View Fixed Color, Dynamic, linked to light sensor, Lounge mode, sunset, Wall colour adaptive, 3D
- Ambilight light system: Built-in AL + Hue

## Picture/Display

- Display: LED Full HD
- Diagonal screen size: 42 inch / 107 cm
- Panel resolution: 1920x1080p
- 3D: Passive 3D, 2 Player Full Screen Gaming\*, 3D Depth adjustment, 2D to 3D conversion, Auto 3D detection, Flickerfree 3D
- Aspect ratio: 4:3/16:9
- Brightness: 400 cd/m<sup>2</sup>
- Picture enhancement: Micro Dimming Pro, Perfect Natural Motion, Pixel precise HD, 800 Hz Perfect Motion Rate

## Smart TV

- Interactive TV: HbbTV
- SmartTV apps\*: Catch-up TV, Netflix, Spotify, Online apps, Online Video stores, Open Internet browser, YouTube
- Social TV: Skype, Twitter
- TV programme guide\*: 8 day Electronic Program Guide

## Smart Interaction

- User interaction: SimplyShare, MultiRoom Client and Server, Wi-fi Miracast Certified\*, Cloud TV\* and Cloud Explorer, Pointer remote control\*, Smart text remote control
- Program: Pause TV, USB Recording\*
- Ease of Installation: Auto detect Philips devices, Device connection wizard, Network installation wizard, Settings assistant wizard
- Ease of Use: One-stop Home button, Onscreen Usermanual
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB, Online firmware upgrade
- Signal strength indication
- Teletext: 1000 page Hypertext
- My Remote App\*: Control, Simply Share, TV Guide, Wi-fi Smart Screen
- Screen Format Adjustments: Basic - Fill Screen, Fit to Screen, Advance - Shift, Zoom, Stretch

## CPU

- Processor type: Dual-Core

## Sound

- Output power (RMS): 24W
- Sound Features: Smart Stereo, Ambi wOOx, Natural Sound
- Sound Enhancement: Incredible Surround, Incredible Surround 3D, Clear Sound, Auto Volume Leveller, Bass Enhancement, Smart Sound

## Connectivity

- Number of HDMI connections: 4
- Number of component in (YPbPr): 1
- Number of scarts (RGB/CVBS): 1
- Number of USBs: 2
- Wireless connections: Wi-Fi 2x2 Integrated
- Other connections: CI+1.3 certified, Audio in (DVI), Antenna IEC75, Common Interface Plus (CI+), Ethernet-LAN RJ-45, Digital audio out (optical), Audio L/R in, Headphone out, Service connector
- HDMI features: 3D, Audio Return Channel
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, Auto subtitle shift (Philips)\*, Pixel Plus link (Philips)\*, One touch play

## Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1
- Subtitles Formats Support: .AAS, .SMI, .SRT, .SSA, .SUB, .TXT
- Music Playback Formats: AAC, AMR, LPCM, M4A, MP3, MPEG1 L1/2, WMA (v2 up to v9.2)
- Picture Playback Formats: JPEG, BMP, GIF, JPS, PNG, PNS

## Supported Display Resolution

- Computer inputs: up to 1920x1080 @ 60Hz
- Video inputs: 24, 25, 30, 50, 60 Hz, up to 1920x1080p

## Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/C/S/S2
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM

## Power

- Mains power: AC 220 - 240 V 50/60Hz
- Ambient temperature: 5 °C to 35 °C
- Eu Energy Label power: 42 W
- Annual energy consumption: 61 kW h
- Standby power consumption: < 0.3 W
- Power Saving Features: Auto switch-off timer, Eco mode, Picture mute (for radio)
- Off mode power consumption: < 0.3 W

## Dimensions

- Box dimensions (W x H x D): 1440 x 665 x 133 mm
- Set dimensions (W x H x D): 949 x 554 x 35.8 mm
- Set dimensions with stand (W x H x D): 949 x 614 x 232 mm
- Product weight: 11.5 kg
- Product weight (+stand): 12.8 kg
- Weight incl. Packaging: TBC kg
- VESA wall mount compatible: 400 x 400 mm


## Accessories

- Included accessories: Table top stand, Family pack PTA469, 4x Passive 3D Glasses, 2 x Dual view gaming glasses, Remote Control, 2 x AA Batteries, Power cord, Quick start guide, Legal and safety brochure, Warranty Leaflet
- Optional accessories: Philips TV camera PTA317, 3D glasses PTA417, 3D glasses Game kit PTA436




## Connections

### Side



### Rear



Issue date 2019-06-13

Version: 2.0.1

12 NC: 8670 001 11293  
EAN: 87 12581 70916 7

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* MyRemote app and related functionalities varies per TV model and country, as well as smart device model and OS. For more detail, please visit: [www.philips.com/TV](http://www.philips.com/TV).

\* For smart TV app, visit [www.philips.com/TV](http://www.philips.com/TV) to discover the services offering in your country

\* Cloud TV offering depends on country availability and regulations

\* Compatibility depends on Wifi Miracast certification & Android 4.2 or later. For more details please refer to your device documentation.

\* USB recording for digital channels only, recordings may be limited by broadcast copy protection (CI+). Country and channel restrictions may apply.

\* Philips TV camera (PTA317) is sold separately.

\* Parents should monitor their children during 3D viewing and ensure they do not experience any discomfort as mentioned above. Watching 3D is not recommended for children under 6 years of age as their visual system is not fully developed yet.

\* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

\* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

\* EPG and actual visibility (up to 8 days) is country and operator dependent.

\* (Philips) only compatible with specific Philips player device.