

Philips 5500 series  
Full HD Ultra-Slim LED TV  
with Pixel Plus HD

**108 cm (43")**

Full HD LED TV  
DVB T/C/T2/T2-HD/S/S2



**43PFS5503**

## Full HD Ultra-Slim LED TV

with Pixel Plus HD

Enhanced simplicity comes to the big screen. The Philips 5500 offers full HD resolution, clear sound and a great viewing experience. Simply plug it in and start enjoying your shows, movies and games with ease.

### As flexible as you are

- Slim, refined stands communicate lightness

### A clear, vivid picture every time

- Pixel Plus HD gives you beautiful images you'll love
- Full HD LED TV—brilliant LED images with incredible contrast

### Television viewing at your convenience

- Two HDMI input ports and Easylink for integrated connectivity
- USB for multimedia playback

# PHILIPS

# Highlights

## Full HD LED TV

Picture Quality matters. Regular HDTVs deliver quality, but you expect more. Imagine crisp detail paired with high brightness, incredible contrast and realistic colours for a true to life picture.

## Two HDMI input ports with Easylink

Avoid cable clutter with a single HDMI cable to carry both picture and audio signals from your devices to your TV. HDMI uses uncompressed signals, ensuring the highest quality from

source to screen. Together with Philips Easylink, you'll need only one remote control to perform most operations on your TV, DVD, Blu-ray, set top box or home theatre system.

## USB (photos, music, video)

Share the fun. Connect your USB memory-stick, digital camera, mp3 player or other multimedia device to the USB port on your TV to enjoy photos, videos and music with the easy to use onscreen content browser.

## Pixel Plus HD

Philips' Pixel Plus HD engine optimises picture quality to deliver crisp images with beautiful contrast. So whether you're streaming online or watching from a disc, you'll enjoy sharper images with brighter whites and blacker blacks.

## Sticks Stand

Slim, refined stands communicate lightness

# Specifications

## Picture/Display

- Display: LED Full HD
- Picture enhancement: Pixel Plus HD
- Panel resolution: 1920 x 1080
- Aspect ratio: 4:3/16:9
- Diagonal screen size: 43 inch / 108 cm
- Peak Luminance ratio: 65 %

## Smart Interaction

- Programme: Pause TV, USB Recording\*
- Ease of Use: One-stop Home button
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB
- Signal strength indication
- Teletext: 1000-page Hypertext
- Electronic Programme Guide\*: 8 days Electronic Programme Guide
- Screen Format Adjustments: Autozoom, Superzoom, Movie expand 16:9, Unscaled, 4:3, 16:9

## Sound

- Output power (RMS): 16 W
- Sound Enhancement: Incredible Surround, Clear Sound, Auto Volume Leveller, Bass Control, Smart Sound

## Connectivity

- Number of HDMI connections: 2
- Number of USBs: 1
- Number of scarts (RGB/CVBS): 1
- Other connections: Common Interface Plus (CI+), Digital audio out (optical), Antenna IEC75, Satellite Connector, Audio in (DVI), Headphone out
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play

## Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1, HEVC (H.265)
- Subtitles Formats Support: .SMI, .SRT, .SSA, .SUB, .TXT, .ASS
- Music Playback Formats: AAC, MP3, WAV, WMA

(v2 up to v9.2)

- Picture Playback Formats: JPEG, BMP, GIF, PNG

## Supported Display Resolution

- Computer inputs: up to 1920 x 1080 @ 60 Hz
- Video inputs: up to 1920 x 1080p

## Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM

## Power

- Mains power: AC 220–240 +/- 10%
- Standby power consumption: <0.3 W
- Off mode power consumption: < 0.5 W
- Ambient temperature: 5°C to 35°C
- Power Saving Features: Auto switch-off timer, Eco mode, Picture mute (for radio)
- Energy Label Class: A+
- EU Energy Label power: 40 W
- Annual energy consumption: 59 kWh
- Mercury content: 0 mg
- Presence of lead: Yes\*

## Dimensions

- Box dimensions (W x H x D): 1070 x 660 x 150 mm
- Set dimensions (W x H x D): 970.6 x 563.0 x 80.5 mm
- Set dimensions with stand (W x H x D): 970.6 x 585.0 x 218.1 mm
- TV stand width distance: 768.6 mm
- Product weight: 7.1 kg
- Product weight (+stand): 7.2 kg
- Weight incl. Packaging: 10.2 kg
- VESA wall mount compatible: 200 x 200 mm

## Colour & Finish


- TV Front: Black High Gloss

## Accessories


- Included accessories: Remote Control, 2 x AAA Batteries, Power cord, Quick start guide, Legal and safety brochure, Tabletop stand

## Connections

### Side



### Rear



Issue date 2018-01-24

Version: 1.0.1

12 NC: 8670 001 51289  
EAN: 87 18863 01470 7

© 2018 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)



\* EPG and actual visibility (up to 8 days) is country- and operator-dependent.

\* Energy consumption in kWh per year based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

\* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

\* (Philips) only compatible with specific Philips player device.

\* This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.