



Philips 4000 series
Full HD Ultra Slim LED TV
with Digital Crystal Clear

108 cm (43")

LED TV
DVB-T/T2/C



43PFT4001

Full HD Slim LED TV

With Digital Crystal Clear

The stylish design of the Philips 4000 Series with Digital Crystal Clear brings great value to your home. Enjoy its full HD picture quality with Perfect Motion Rate and clear sound for an effortless entertainment experience.

The right features presented elegantly

- Razor-thin blade stands in black
- Ultra Slim lines for a refined profile

A clear, vivid picture every time

- Picture Performance Index improves every viewing element
- Digital Crystal Clear for precision you'll want to share
- Full HD LED TV—brilliant LED images with incredible contrast

Television viewing at your convenience

- USB for multimedia playback
- Three HDMI inputs and Easylink for integrated connectivity

PHILIPS

Highlights

Ultra Slim profile



Sleek. Cutting edge. Refined. Precise. The Philips Ultra Slim silhouette. That something so slim can inspire so much interest shouldn't be surprising, given how much sophistication it will bring to your décor.

Black blade stands

Dark, mysterious and incredibly strong. The Philips black blade stands take your TV to another level. Durable construction in an ultra-thin design meticulously exude the elegance and style of your new TV. And with their powerful stance, it's a wonder how something so small can do so much.

Digital Crystal Clear

For natural looking pictures from any source, Philips created Digital Crystal Clear. Whether you're indulging in your favorite shows,

movies, the news, or are simply having a few friends over for a night in, you'll enjoy it all in optimal contrast, color and sharpness.

Picture Performance Index



Picture Performance Index combines Philips display technology and advanced picture processing engines to improve the elements of perception: sharpness, motion, contrast and color. No matter the source, you'll always enjoy razor sharp pictures with incredible detail and depth, the deepest blacks, the brightest whites, and the most vivid, brilliant colors as well as natural, lifelike skin tones every time.

USB (photos, music, video)

Share the fun. Connect your USB memory-stick, digital camera, mp3 player or other multimedia device to the USB port on your TV

to enjoy photos, videos and music with the easy to use onscreen content browser.

Three HDMI with Easylink



Avoid cable clutter with a single cable to carry both picture and audio signals from your devices to your TV. HDMI uses uncompressed signals, ensuring the highest quality from source to screen. Together with Philips Easylink, you'll need only one remote control to perform most operations on your TV, DVD, Blu-ray, set top box or home theatre system.

Full HD LED TV

Picture Quality matters. Regular HDTVs deliver quality, but you expect more. Imagine crisp detail paired with high brightness, incredible contrast and realistic colors for a true to life picture.

Specifications

Picture/Display

- Display: LED Full HD
- Diagonal screen size: 43 inch / 108 cm
- Panel resolution: 1920x1080p
- Aspect ratio: 4:3/16:9
- Brightness: 200 cd/m²
- Picture enhancement: Digital Crystal Clear

Smart Interaction

- Program: Pause TV, USB Recording*
- Ease of Use: One-stop Home button
- Firmware upgradeable: Firmware upgradeable via USB
- Signal strength indication
- Teletext: 1000 page Hypertext
- Electronic Program Guide*: 8 days Electronic Program Guid
- Screen Format Adjustments: Autozoom, 4:3, 16:9, Zoom 1, Zoom 2

Sound

- Output power (RMS): 16W
- Sound Enhancement: Incredible Surround

Connectivity

- Number of HDMI connections: 3
- Number of component in (YPbPr): 1
- Number of USBs: 1
- Other connections: Common Interface Plus (CI+), Digital audio out (optical), Headphone out, Antenna IEC75, PC Audio In (3.5mm)
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play

Multimedia Applications

- Video Playback Formats: MPEG-2, MPEG-4
- Subtitles Formats Support: .SMI, .SRT, .SUB, .TXT
- Music Playback Formats: AAC, MP3, WAV, WMA

(v2 up to v9.2)

- Picture Playback Formats: JPEG, BMP, GIF, PNG

Supported Display Resolution

- Computer inputs: up to 1920x1080 @ 60Hz
- Video inputs: 24, 25, 30, 50, 60 Hz, up to 1920x1080p

Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/C
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM

Power


- Mains power: AC 220 - 240 V 50/60Hz
- Ambient temperature: 5 °C to 35 °C
- Eu Energy Label power: 70 W
- Annual energy consumption: 102 kWh
- Energy Label Class: A
- Standby power consumption: <0.5
- Off mode power consumption: 0 W
- Power Saving Features: Auto switch-off timer, Eco mode, Picture mute (for radio)

Dimensions

- Box dimensions (W x H x D): 1085 x 667 x 150 mm
- Set dimensions (W x H x D): 970 x 564 x 74 mm
- Set dimensions with stand (W x H x D): 970 x 614 x 219 mm
- Product weight: 8.1 kg
- Product weight (+stand): 8.5 kg
- Weight incl. Packaging: 10.5 kg
- VESA wall mount compatible: 200 x 300 mm

Accessories

- Included accessories: Remote Control, 2 x AAA Batteries, Table top stand, Power cord, Quick start guide, Legal and safety brochure, Warranty Leaflet



Issue date 2019-06-18

Version: 9.1.1

12 NC: 8670 001 40951
EAN: 87 18863 01056 3

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* EPG and actual visibility (up to 8 days) is country and operator dependent.

* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

* This TV does not support Pause TV/USB recording when your CI Plus CAM card inserted