



Philips 6000 series  
4K Ultra Slim TV powered  
by Android TV™ with  
Ambilight 2-sided and Pixel  
Plus Ultra HD

**108 cm (43")**

4K Ultra HD LED TV  
Quad Core, 8GB & expandable  
DVB T/C/T2/T2-HD/S/S2



**43PUS6401**

## 4K Ultra Slim LED TV powered by Android TV with Ambilight 2-sided

Design meets performance with the Philips 6400 Series. Sitting on minimalist stand elements, your picture comes to life in 4K Ultra HD and Pixel Plus Ultra HD picture quality. With Android TV your entertainment options are virtually endless

### Crafted Lightness

- Ambilight changes the way you look at TV forever
- Slim aluminum pinch stands for a premium lightweight look

### Passionate about Picture Quality

- 4K Ultra HD is unlike any resolution you've ever seen before
- Discover Ultra HD Picture Quality with Pixel Plus Ultra HD
- Micro Dimming Pro for incredible contrast
- Experience better contrast, color & sharpness with HDR Plus
- The new integrated HEVC standard to enjoy high quality 4k

### Exhilarating. Limitless. Powered by Android

- Unleash the power of Quad Core and integrated Android
- Google Play™: your window to fun
- Cloud Gaming: high quality games for all ages



androidtv



**PHILIPS**

# Highlights

## Ambilight 2-sided

You've created a home that's more than just a house, so why not choose a TV that is warm and inviting too? Philips unique Ambilight technology makes your screen much wider—and your viewing experience more immersive—by emitting an extra wide glow from two-sides of your TV screen onto the surrounding wall. Color, vibrancy and excitement move beyond the screen and into your living room to bring you a viewing experience beyond the ordinary.

## Slim aluminum pinch stands

Every great artwork needs its own easel. And like every great artwork, your new Philips TV needs to be displayed in its rightful manner. Developed specifically for this model by our design team, these slim aluminum pinch stands are a true testament to the lightness and slim construction of this powerful TV series.

## 4K Ultra HD

Ultra HD TV has four times the resolution of a conventional Full HD TV. With over 8 million pixels and our unique Ultra Resolution Upscaling technology, you'll experience the best possible picture quality. The higher the quality of your original content, the better

images and resolution you will be able to experience. Enjoy improved sharpness, increased depth perception, superior contrast, smooth natural motion, and flawless details.

## Pixel Plus Ultra HD

Experience 4K Ultra HD sharpness with the Philips Pixel Plus Ultra HD engine. It optimizes picture quality to deliver smooth, fluid images with incredible detail and depth – Enjoy sharper 4K images with brighter whites and blacker blacks every time.

## Micro Dimming Pro

Micro Dimming Pro optimizes the contrast on your TV based on the lighting conditions of your room. Combined with its special software that analyzes the picture in 6400 different zones, you'll enjoy incredible contrast and image quality for a truly lifelike visual experience-day or night.

## Quad Core + Android

Philips Quad Core processor meets the power of Android to deliver an exciting gaming experience. And with Android on your TV you'll navigate, launch apps and play videos in a way that is super fast, super intuitive, and super fun.

## Google Play

Google Play™ has a rich catalogue of high quality games for all ages. Optimized for use on your TV, they look as great as they play. And there's no need to clutter up your house with yet another gaming console; with a universal USB gaming control you can navigate and play with ease.

## Cloud Gaming


Cloud Gaming offers a vast online catalogue of high quality games for every age, taste and gaming level. Simply pick a game and play on your TV!

## High Dynamic Range Plus

High Dynamic Range Plus is a new video standard. It redefines in-home entertainment through advances in contrast and color. Enjoy a sensory experience that captures the original richness and liveliness, yet accurately reflects the content creator's intent. The end result? Brighter highlights, greater contrast, a broader range of colors and detail like never before.

## HEVC support for 4k broadcast

The new integrated HEVC (H.265) standard allows you to enjoy high picture quality 4k resolution broadcast.



# Specifications

## Ambilight

- Ambilight Version: 2-sided
- Ambilight Features: Built in Ambilight+hue, Ambilight Music, Game Mode, Wall colour adaptive, Lounge mode

## Picture/Display

- Display: 4K Ultra HD LED
- Peak Luminance ratio: 65 %
- Diagonal screen size: 43 inch / 108 cm
- Panel resolution: 3840x2160
- Aspect ratio: 16:9
- Brightness: 350 cd/m<sup>2</sup>
- Picture enhancement: Micro Dimming Pro, Ultra Resolution, Natural Motion, Pixel Plus Ultra HD

## Android TV

- OS: Android™ 6.0 (Marshmallow)
- Pre-installed apps: Google Play Movies\*, Google Play Music\*, Google Search, YouTube
- Memory size(Flash): extendable via USB storage, 8GB

## Smart TV Features

- User Interaction: MultiRoom client and server, SimplyShare
- Interactive TV: HbbTV
- Program: Pause TV, USB recording\*
- SmartTV apps\*: Online video stores, Open internet browser, Social TV, TV on demand, Youtube
- Ease of Installation: Auto detect Philips devices, Device connection wizard, Network installation wizard, Settings assistant wizard
- Ease of Use: One-stop smart menu button, Onscreen usermanual
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB, Online firmware upgrade
- Screen Format Adjustments: Basic - Fill Screen, Fit to screen, Advance - Shift, Zoom, stretch
- Philips TV Remote app\*: Apps, Channels, Control, NowOnTV, TV Guide, Video On Demand

## Processing

- Processing Power: Quad Core

## Sound

- Output power (RMS): 20W
- Sound Enhancement: DTS Premium Sound, Clear

Sound, Smart Sound

## Connectivity

- Number of HDMI connections: 4
- Number of component in (YPbPr): 1
- Number of scarts (RGB/CVBS): 1
- Number of USBs: 3
- Wireless connection: Dual Band, Wi-Fi 802.11n 2x2 integrated
- Other connections: Antenna IEC75, Common Interface Plus (CI+), Ethernet-LAN RJ-45, Digital audio out (optical), Audio L/R in, Audio in (DVI), Headphone out, Service connector, Satellite Connector
- HDMI features: 4K, Audio Return Channel
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play
- HDCP 2.2: Yes on HDMI1, Yes on HDMI2

## Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1, HEVC (H.265)
- Subtitles Formats Support: .SRT, .SUB, .TXT, .SMI
- Music Playback Formats: AAC, MP3, WAV, WMA (v2 up to v9.2), WMA-PRO (v9 and v10)
- Picture Playback Formats: JPEG

## Supported Display Resolution

- Computer inputs on HDMI1/2: up to 4K UHD 3840x2160 @60Hz
- Computer inputs on HDMI3/4: up to 4K UHD 3840x2160 @30Hz, up to FHD 1920x1080 @60Hz
- Video inputs on HDMI1/2: up to 4K UHD 3840x2160@60Hz
- Video inputs on HDMI3/4: up to FHD 1920x1080 @60Hz, up to 4K UHD 3840x2160 @30Hz

## Tuner/Reception/Transmission

- HEVC support
- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM
- TV Program guide\*: 8 day Electronic Program Guide
- Signal strength indication
- Teletext: 1000 page Hypertext

## Power

- Off mode power consumption: 0.3
- Presence of lead: Yes\*
- Mercury content: 0 mg
- Mains power: AC 220 - 240 V 50/60Hz
- Ambient temperature: 5 °C to 35 °C
- Eu Energy Label power: 67 W
- Annual energy consumption: 98 kW h
- Standby power consumption: <0.3
- Power Saving Features: Auto switch-off timer, Light sensor, Picture mute (for radio)
- Energy Label Class: A

## Dimensions

- Box dimensions (W x H x D): 1054 x 669 x 133 mm
- TV stand width distance: 625.41 mm
- Set dimensions (W x H x D): 968 x 576 x 77 mm
- Set dimensions with stand (W x H x D): 968 x 623 x 204 mm
- VESA wall mount compatible: 200 x 200 mm
- Product weight: 9.4 kg
- Product weight (+stand): 9.7 kg
- Weight incl. Packaging: 12.3 kg


## Accessories

- Included accessories: Remote Control, 2 x AA Batteries, Table top stand, Power cord, Quick start guide, Legal and safety brochure




## Connections

Side



Rear



Issue date 2022-06-03

Version: 15.1.1

12 NC: 8670 001 35004  
EAN: 87 18863 00777 8

© 2022 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

- \* EPG and actual visibility (up to 8 days) is country and operator dependent.
- \* Android App offerings vary per country. For more details please visit your local Google Play Store.
- \* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.
- \* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.
- \* Google Cast functionality is subject to Google Cast Ready apps and devices. For more details please visit Google Cast product page.
- \* Philips TV Remote app and related functionalities vary per TV model, operator, and country, as well as smart device model and OS. For more details please visit: [www.philips.com/TVRemoteapp](http://www.philips.com/TVRemoteapp).
- \* Smart TV app offerings vary per TV model and country. For more details please visit: [www.philips.com/smarttv](http://www.philips.com/smarttv).
- \* USB recording for digital channels only, recordings may be limited by broadcast copy protection (CI+). Country and channel restrictions may apply.
- \* Please note that your Amazon Apps may not always be available in your country. (Currently Amazon apps works only in UK, Germany, Austria)