



Philips 6500 series  
Ultra Slim 4K UHD LED  
Smart TV

**139 cm (55")**

900 Picture Performance Index  
HDR Plus  
Pixel Precise Ultra HD



**55PUS6503**

## Ultra Slim 4K UHD LED Smart TV

with Pixel Precise UHD and Saphi system

Enjoy the clarity of 4K UHD in a Smart TV that's brilliantly easy to use. Pixel Precise Ultra HD ensures everything looks smooth and sharp. SAPHI gives you instant access to favourite content: Netflix movie night is just a button away.

### **Beautiful. Even on standby.**

- Slender bezel and stand.
- Slim yet sturdy build.

### **See every detail**

- 4K Ultra HD. Pictures so sharp you'll think you're there.
- Pixel Precise Ultra HD. Fluid images with incredible depth.

### **Rich colour. Sharp contrast.**

- HDR Plus. Enhanced contrast, colour, and sharpness.
- Micro Dimming optimizes the contrast on your TV

### **SAPHI: intuitive app content selection**

- SAPHI. The smart way to enjoy your TV
- Philips app gallery. Access Youtube, Netflix, and more.

### **Slim TV. Clear sound.**

- Deep bass and crystal-clear dialogue.

**PHILIPS**

# Highlights

## Sticks Stand

Our new stick stand were engineered to change space beneath your TV where a traditional stand would normally sit, offering you a more immersive viewing experience. A TV that stands confidently with a nod to the future.

## 4K Ultra HD

With four times the resolution of conventional Full HD, Ultra HD lights up your screen with over 8 million pixels and our unique Ultra Resolution Upscaling technology. Experience improved images regardless of the original content, and enjoy a sharper picture with superior depth, contrast, natural motion and vivid details.

## Pixel Precise Ultra HD

The beauty of 4K Ultra HD TV is in savoring every detail. Philips Pixel Precise Ultra HD

engine converts any input picture into stunning UHD resolution on your screen. Enjoy a smooth, yet sharp moving image and exceptional contrast. Discover deeper blacks, whiter whites, vivid colors and natural skin tones - every time, and from any source.

## High Dynamic Range Plus

High Dynamic Range Plus is a new video standard. It redefines in-home entertainment through advances in contrast and color. Enjoy a sensory experience that captures the original richness and liveliness, yet accurately reflects the content creator's intent. The end result? Brighter highlights, greater contrast, a broader range of colors and detail like never before.

## SAPHI

SAPHI is a fast, intuitive operating system that makes your Philips Smart TV a real pleasure to

use. Enjoy great picture quality and one-button access to a clear icon-based menu. Operate your TV with ease, and quickly navigate to popular Philips Smart TV apps including YouTube, Netflix, and more.

## Philips app gallery

Philips app gallery is a wide-ranging collection of online apps that you can access as soon as your Smart TV is connected to the Internet. It's that easy! Just switch on your TV, connect to the Internet and experience a whole new world of entertainment online.

## DTS HD

DTS HD optimizes sound processing by preserving the original sound content so that you can enjoy a better sound from your speakers with crystal-clear dialog.

# Specifications

## Picture/Display

- Display: 4K Ultra HD LED
- Diagonal screen size (inch): 55 inch
- Diagonal screen size: 55 inch / 139 cm
- Panel resolution: 3840x2160
- Aspect ratio: 16:9
- Picture enhancement: Micro Dimming, Pixel Precise Ultra HD, Ultra Resolution, 900 PPI

## Smart TV Features

- User Interaction: MultiRoom Client, SimplyShare, Wi-Fi Miracast Certified\*
- Interactive TV: HbbTV
- Program: Pause TV, USB Recording\*
- SmartTV apps\*: Online Video Stores, Open Internet Browser, Social TV, TV on Demand, Youtube
- Ease of Installation: Auto detect Philips devices, Device connection wizard, Network installation wizard, Settings assistant wizard
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB, Online firmware upgrade
- Screen Format Adjustments: Advance - Shift, Basic - Fill Screen, Fit to Screen, Zoom, Stretch
- Philips TV Remote app\*: Apps, Channels, Control, NowOnTV, TV Guide, Video On Demand

## Processing

- Processing Power: Quad Core

## Sound

- Output power (RMS): 20W
- Sound Enhancement: Incredible Surround, Clear Sound, Auto Volume Leveller, Smart Sound
- Speaker configuration: 2x10W full range speaker

## Connectivity

- Number of HDMI connections: 3
- Number of component in (YPbPr): 1
- Number of USBs: 2
- Wireless connections: Wi-Fi 802.11n 2x2 integrated, Dual Band
- Other connections: Antenna IEC75, Satellite Connector, Ethernet-LAN RJ-45, Common Interface Plus (CI+), Digital audio out (optical), Audio L/R in, Headphone out
- HDMI features: Audio Return Channel, 4K
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play

- HDCP 2.2: Yes on all HDMI
- Number of CVBS: 1

## Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1, VP9, HEVC (H.265)
- Subtitles Formats Support: .SMI, .SRT, .SUB, .TXT, .AAS
- Music Playback Formats: AAC, MP3, WAV, WMA (v2 up to v9.2), WMA-PRO (v9 and v10)
- Picture Playback Formats: JPEG, BMP, GIF, PNG

## Supported Display Resolution

- Computer inputs on HDMI1: up to 4K UHD 3840x 2160 @30Hz
- Computer inputs on HDMI2/3: up to 4K UHD 3840x 2160 @60Hz
- Video inputs on HDMI1: up to 4K UHD 3840x 2160 @30Hz
- Video inputs on HDMI2/3: up to 4K UHD 3840x 2160 @60Hz

## Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- HEVC support
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM
- TV Program guide\*: 8 day Electronic Program Guide
- Signal strength indication
- Teletext: 1000 page Hypertext

## Power

- Mains power: AC 220 - 240 V 50/60Hz
- Ambient temperature: 5 °C to 35 °C
- Standby power consumption: <0.3W
- Off mode power consumption: 0.3 W
- Power Saving Features: Auto switch-off timer, Picture mute (for radio)
- Energy Label Class: A+
- Eu Energy Label power: 86 W
- Annual energy consumption: 126 kWh
- Mercury content: 0 mg
- Presence of lead: Yes\*

## Dimensions

- Box dimensions (W x H x D): 1360 x 860 x 160 mm
- Set dimensions (W x H x D): 1244.2 x 719.0 x 81.4 mm

- Set dimensions with stand (W x H x D): 1244.2 x 742.2 x 227.4 mm
- TV stand width distance: 768.0 mm
- Product weight: 15.1 kg
- Product weight (+stand): 15.4 kg
- Weight incl. Packaging: 20.5 kg
- VESA wall mount compatible: 300 x 200 mm

## Color & Finishing

- TV Front: Black High Gloss


## Accessories

- Included accessories: Remote Control, 2 x AAA Batteries, Power cord, Quick start guide, Legal and safety brochure, Table top stand



## Connections

### Side



### Rear



### Bottom



Issue date 2019-01-17

Version: 9.0.1

12 NC: 8670 001 51565  
EAN: 87 18863 01494 3

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* EPG and actual visibility (up to 8 days) is country and operator dependent.

\* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

\* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

\* (Philips) only compatible with specific Philips player device.

\* Philips TV Remote app and related functionalities vary per TV model, operator, and country, as well as smart device model and OS. For more details please visit: [www.philips.com/TVRemoteapp](http://www.philips.com/TVRemoteapp).

\* Smart TV app offerings vary per TV model and country. For more details please visit: [www.philips.com/smarttv](http://www.philips.com/smarttv).

\* USB recording for digital channels only, recordings may be limited by broadcast copy protection (CI+). Country and channel restrictions may apply.

\* Compatibility depends on Wifi Miracast certification & Android 4.2 or later. For more details please refer to your device documentation.

\* This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.