



Philips Signage Solutions
Multi-Touch Display

65"

Powered by Android
Multi-touch

SignageSolutions

65BDL3051T

Discover a new level of interaction

using the power of android

Get even closer to your audience than ever before. Fast, precise and extremely durable, its high performance is matched by excellent reliability and functionality.

Supreme audience interaction

- Experience amazing interactivity with true Multi-Touch
- 10 points touch
- Anti-glare glass with low optical parallax

Innovative solutions for any signage application

- Integrated WiFi
- Android: Run your own app or choose your favorite app to run
- Save and play content with internal memory
- Enhance your connectivity with an integrated mPCIe slot.

Maximizing the impact of your message

- CMND: Take control of your displays

Care about you, your business and your audience

- SmartPower for energy saving
- Simplify meetings with FailOver for conferencing

PHILIPS

Highlights

Plug & Play Multi-Touch



A brand new level of interactivity is now available thanks to integrated touch technology. More flexibility and optimum simultaneous touch performance coupled with excellent operability opportunities to give you the ultimate in user interaction. The Multi-Touch displays are enabled with automatic touch recognition. The USB connector is HID compliant, providing true plug-and-play operation.

10 points touch

10 points touch

Powered by Android

With Android integrated into the touch display, you can work with the most developed OS on the planet, and save your own app directly into the display. This also means, for the built-in apps, like the browser, it's touch capable right out of the box. Just connect the power and you've got immediate interactivity. You can also use the built-in scheduler to

daypart your apps and content based on the time of day. And, using the auto orientation feature, switching from portrait to landscape content is as simple as turning the display.

WiFi

Integrated WiFi

Internal Memory



Save and play content with internal memory. Upload your media into the display and playback content immediately. Working in conjunction with the internal browser, it also serves as a memory cache when streaming online content. If the network ever fails, the internal memory keeps content running by playing a cached version of the content, ensuring that your media stays up even if the network goes down.

Anti-glare glass

With this integrated touch display, the anti-glare glass with low optical parallax allows for the most immersive touch experience. With little to no glare and low reflection on the display, images are crystal clear with pure color and great clarity.

CMND



A robust display management platform, CMND puts the power back into your hands. Update and manage content with CMND & Create or control your settings with CMND & Control. It's all possible with CMND.

FailOver for Meeting Rooms

Using FailOver, simplify your presentations and videoconferencing. When a meeting or conference room is not in use, background content can run from whatever input source you choose. When the meeting starts and you need to share a presentation or your screen, simply connect your computer and the display automatically switches inputs and shows what's on your screen, with no need to manually switch inputs.

PCI Slot

With an integrated PCI slot, you can connect a WiFi/bluetooth or 4G LTE module, allowing for even greater communication with the display. Machine to machine communication is also enhanced, with numerous configurations available for customers to use, such as the ability to expand product features or signal-handling capability.

Specifications

Picture/Display

- Diagonal screen size: 65 inch / 163.9 cm
- Panel resolution: 1920x1080p
- Optimum resolution: 1920 x 1080 @ 60 Hz
- Brightness: 350 cd/m²
- Contrast ratio (typical): 4000:1
- Surface treatment: Anti-Glare coating
- Aspect ratio: 16:9
- Response time (typical): 8 ms
- Pixel pitch: 0.74 x 0.74 mm
- Display colors: 16.7 million
- Viewing angle (H / V): 178 / 178 degree
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement
- Dynamic contrast ratio: 500,000:1
- Panel technology: VA

Interactivity

- Multi-touch technology: Infrared touch
- Touch points: 10 simultaneous touch points
- Plug and play: HID compliant
- Protection glass: 5 mm tempered safety glass, Anti-Glare, Anti-Reflective

Connectivity

- Video input: DisplayPort (1.2), HDMI (x2), DVI-D, USB, VGA (via DVI)
- Video output: DisplayPort, DVI-I, DVI, VGA (via DVI)
- Audio input: Audio Left/Right (RCA), 3.5 mm jack
- Audio output: Audio Left/Right (RCA)
- External control: RJ45, IR (in/out) 3.5 mm jack, RS232C (in/out) 2.5 mm jack
- Other connections: USB, micro SD, micro USB, mPCIe, OPS, USB power outlet (5 V, 2 amp)

Supported Display Resolution

Computer formats

Resolution	Refresh rate
640 x 480	60, 67, 72, 75Hz
1024 x 768	60Hz
1280 x 768	60Hz
1280 x 800	60Hz
1280 x 1024	60Hz
1360 x 768	60Hz
1600 x 1200	60Hz
1920 x 1080	60Hz
1920 x 1200	60Hz

720 x 400	70Hz
800 x 600	60, 72, 75Hz
• Video formats	
Resolution	Refresh rate
480p	60Hz
576p	50Hz
720p	50, 60Hz
1080p	50, 60Hz
1080i	25, 30Hz
480i	30, 60Hz
576i	25, 50Hz

Convenience

- Placement: Landscape (16/7), Portrait (12/7)
- Signal Loop Through: RS232, VGA, IR Loopthrough, DisplayPort, DVI
- Network controllable: RS232, RJ45, One Wire (HDMI-CEC), HDMI (One Wire)
- Picture performance: Advanced color control
- Picture in picture: PIP
- Screen saving functions: Pixel Shift, Low Brightness
- Keyboard control: Hidden, Lockable
- Remote control signal: Lockable
- Energy saving functions: Smart Power
- Other convenience: Carrying handles
- Memory: 16GB eMMC
- Ease of installation: Smart Insert

Dimensions

- Set dimensions (W x H x D): 1492.40 x 867.40 x 99.8 mm
- Product weight: 43.1 kg
- VESA Mount: 400 x 400 mm, M6
- Bezel width: 29.2 mm
- Product weight (lb): 95 lb
- Set dimensions in inch (W x H x D): 58.76 x 34.15 x 3.93 inch
- Smart Insert mount: 100 x 100 mm, 100 x 200 mm

Sound

- Built-in speakers: 2 x 10W RMS

Operating conditions

- Temperature range (operation): 5 ~ 40 °C
- Relative humidity: 20 ~ 80 %
- MTBF: 50,000 hour(s)
- Altitude: 0 ~ 3000 m
- Temperature range (storage): -20 ~ 60 °C

Power

- Mains power: 100 ~ 240 VAC, 50 ~ 60 Hz
- Standby power consumption: <0.5W
- Consumption (On mode): 147 W
- Power Saving Features: Smart Power

Accessories

- Included accessories: AC Power Cord, RS232 cable, USB cable, Remote Control, Batteries for remote control, Quick start guide
- Optional accessories: ColourCalibrationKit (CCK4602), HDBaseT OPS Receiver (CRD25), Table top stand
- Stand: BMO5922 (Optional)

Miscellaneous


- On-Screen Display Languages: Arabic, English, French, German, Italian, Japanese, Polish, Spanish, Turkish, Russian, Simplified Chinese, Traditional Chinese, Danish, Dutch, Finnish, Norwegian, Portuguese, Swedish
- Regulatory approvals: CE, FCC, Class B, UL/cUL, RoHS, CB, C-Tick, EnergyStar 7.0, GOST, BSMI
- Warranty: 3 year warranty

Multimedia Applications

- USB Playback Picture: BMP, GIF, JPEG, JPG, PDF
- USB Playback Audio: AAC, AIF, AIFF, ASF, LPCM, M3U, M4A, MP3, MP4, WAV, WMA
- USB Playback Video: M2TS, M4V, MK3D, MKV, MP4, MPEG, MPG, MTS, TS, TTS, VOB, WMV

Internal Player

- CPU: Quad Core Cortex A9 1.8GHz
- GPU: ARM Mali400 Quad Core 533MHz
- Memory: 2GB DDR3
- Storage: 16GB EMMC



Issue date 2018-12-06

Version: 1.0.1

12 NC: 8670 001 40082
EAN: 87 12581 74131 0

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com