



Philips
Recessed spot light

66021 3" 40K WHITE 5.5W
white
LED



66021/40/66

Essential lighting for a bright home

Never miss out the essentials with Philips Essmet LED downlight White. With long lasting LED light source and high quality anti glare diffuser encapsulated on a metal body, it is reliable and comfortable bright light without the hassle.

Match your interior style

- Available in various sizes

Energy saving

- Built-in LED, as part of the system

Light effect

- Even light distribution

Long lifespan

- Extremely long life 20,000 hours

PHILIPS

Recessed spot light
66021 3" 40K WHITE 5.5W white, LED

Specifications

Design and finishing

- Material: metal
- Color: white

Extra feature/accessory incl.

- LED integrated
- Diffused light effect
- Photometric data available

Product dimensions & weight

- Length: 10.5 cm
- Width: 6.5 cm
- Net weight: 0.108 kg
- Recessed distance: 8.0 cm
- Cut out length: 9.0 cm
- Cut out width: 9.0 cm

Technical specifications

- Mains power: Range 100 V - 240 V, 50-60 Hz
- Number of bulbs: 16
- Wattage bulb included: 0.3 W

- Maximum wattage replacement bulb: 5.5 W
- Fixture dimmable: No
- LED
- Built in LED
- Lifetime up to: 20,000 hrs
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: I - earthed

Packaging dimensions & weight

- Height: 11.4 cm
- Length: 10.9 cm
- Width: 7.1 cm
- Weight: 0.160 kg

Miscellaneous

- Especially designed for: Functional, Living- & Bedroom
- Style: Functional
- Type: Recessed spot light

660214066


Highlights

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Even light distribution



Even light distribution

Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Available in various sizes

Available in various sizes



Issue date 2017-05-11

Version: 1.0.1

12 NC: 9150 050 92201
EAN: 69 47830 42705 5

© 2017 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com