

PHILIPS

Mobile Phone

I908

Black

WCDMA / GSM

CTI908BK



Exquisite, absolutely amazing

Philips I908 packs a 5 inch full HD screen with 441ppi resolution. That's 36.5% sharper than the retina display! Not to mention a 13 megapixel camera. And with a powerful 1.7GHz octa core processor everything runs faster

Brilliantly smart

- 5" full HD brilliant display with crystal clear clarity
- Best in class speed with 1.7GHz octa core processor
- Android 4.4

Always on, always connected

- Up to 45 days of standby time
- Up to 37 hours of talk time
- Dual mode (WCDMA and GSM), dual coverage
- Superlative 3000mAh build-in battery

Extras in life

- Awesome 13MP AF camera with F2.2 lens and flash
- 5MP front camera with wide angle for fun self-portraits
- Sleek and sensuous mobile chic

Highlights

1.7GHz octa core processor

Blaze ahead of others with the almighty 1.7GHz octa core processor on your Philips mobile phone. This phenomenal powerhouse zips along with your demanding needs without a cinch like no other processor before it - be it watching videos, downloading web pages or engaging in immersive gaming - and with exceptional picture quality to boot. With lightning speeds like this, what's not to like?

13MP AF F2.2 lens camera

Never miss another picture perfect moment again with your Philips mobile phone. Whether you are shooting in low light or macro conditions, your phone's 13 megapixel auto focus camera with flash and F2.2 lens will capture every precious detail. And that's not all. The phone camera comes equipped with a fantastic array of creative effects to jazz up your snapshots. With different shooting modes like automatic face retouch, makeup effects, high-dynamic-range imaging (HDR) and continuous frame shooting, you're just a click away from photographic genius.

3000mAh build-in battery

Your Philips mobile phone comes packed with a standout 3000mAh built-in battery for seamless and long lasting connections on the go. With such exceptional battery performance, you can banish nagging worries about missing important calls from both your professional and personal contacts. And when both work and family matters have been tackled to your satisfaction, you can hone in on transcendent

gaming and surfing experiences on a single charge, thanks to the phone's best-in-class power technology.

5" full HD display



Let the magnificence of the 5" full HD display on your Philips mobile phone take your breath away. With colors that spring to life and details that are clear as crystal, be blown away by the rich definition on the awesome screen. Navigating on the wide screen is just as amazing, with swift and effortless moves to get from function to feature to app. Whether you are surfing your favorite websites or viewing your latest snapshots and videos, the 5" screen gives you an unbeatable visual treat while on the go.

5MP wide angle front camera

Bring yourself to the forefront of fun snapshots with your family and friends, thanks to the 5 megapixel front camera with an 88 degree wide angle on your Philips mobile phone. If you're a fan of spontaneous selfies, this phone is for you.

Android 4.4

Empowered by Android, your Philips mobile now comes with a fully customizable mobile platform that is open to a wide range of smart

applications and functions. Find your pocket PC, games console and telephone all rolled conveniently into one.

Dual mode (WCDMA and GSM)



Your Philips mobile phone incorporates two SIM cards to allow you access to WCDMA and GSM network connections at the same time. Now you can enjoy wider mobile coverage on two networks with just one phone.

Sleek mobile chic

Step out in sensational style with your ultra sleek Philips mobile phone. With a light and beautifully streamlined silhouette encased in a slim frame of a whisper thin depth of 8.2 mm, this phone is a pleasure to be hold and a tribute to all your senses.

Up to 37 hours talk time

The phone can support up to 37 hours conversation on a single charge.

Up to 45 days standby time

The phone can be on and in standby mode continuously for up to 45 days on a single charge.

Specifications

Network Features

GSM band: 900, 1800, 1900 MHz

Messaging: Concatenated SMS (Long SMS), E-mail, MMS, Multimedia Message Service, Predefined messages (SMS, MMS), SMS (Short Message Service), SMS multi-target, Predefined SMS

Services: OTA provisioning (WAP, MMS), SIM Toolkit / Release 99, WAP 2.0, Internet on mobile

Voice Codec: FR/EFR/AMR/HR

EDGE

3G: WCDMA

WLAN

GSM band(Primary SIM): 1800, 1900, 900 MHz

GSM band(Secondary SIM): 1800, 1900, 900 MHz

WCDMA band: 2100MHz, 900MHz

GPRS (Rx+Tx): Class 12, class B and C

Dimensions

Antenna: Integrated

Form Factor: Candy bar

Handset dimensions: 143 mm x 70 mm x 8.8mm

Handset weight: 155.8g

Handset color: Black

Handset Color: Black

Picture/Display

Main Display Resolution: 1080x1920 pixel

Main Display Technology: TFT

Touch panel

Touch-sensitive screen: Touch Screen

Capacity touch panel

Diagonal screen size (inch): 5.0 inch

Capacitive touchscreen

Main Display Colors: 16M

Still Picture Capturing

Camera: Integrated

Flash: built-in

Integrated flash

Image sensor type: CMOS

Preview frame rate: 30 frames/second

Picture file format: JPEG

Picture resolution: 13M (4096X3072)

White balance: Automatic, Cloudy,

Incandescent, Fluorescent, Daylight, Tungsten

Picture quality: Normal, Fine, Superfine

Still Picture Playback

Picture Compression Format: BMP, GIF, GIF (87a & 89a), JPEG, WBMP

Rotation: 90 degree steps

Slide show

Picture Enhancement: Create albums, Edit photos (colors, filters), Fake, Flip photos, Frames & Icons, Picture editing, Picture editor

Video Capturing

Video format: 3GP, H.263, MPEG4, H.264, mp4

Video resolution: QVGA, QCIF, VGA

Video Playback

Compression formats: MPEG4, 3GP, H.263, H.264

Frame rate (fps): 15, 30

Resolution (pxl): 352x288, 640x480, 176x144, 320x240, 1280x720, 800x600

Video Recording

Compression formats: MPEG4, 3GP, H.263, H.264

Frame rate: 30, 15 fps

Audio Capturing

Voice recording: Yes, AMR

Audio Playback

Audio supported formats: AMR, MP3, AAC, Midi, WAV, APE, eACC+, FLAC

Sound

Ringers: MP3 ringer, Polyphonic (64 tones), AMR ringer

Storage Media

Built-in memory (RAM): 2GB

Memory Card Types: Micro SD

Memory management: Memory status, Dynamic memory allocation

User memory: 12697 MB

Maximum memory card capacity: 32 GB

Built-in memory (ROM): 16GB

Convenience

Buttons and controls: Power On/Off, Side keys, Soft keys

Call Management: Call Forwarding, Call on Hold, Call Time, Call Waiting*, Caller ID*, Conference Call, Emergency Call, Microphone mute, Missed Calls, Multi-party call, Received Calls, Firewall

Clock/Version: Analogue, Digital, International clock

Ease of Navigation: Touch panel

Ease of Use: Graphical User Interface, Hands free mode, Hot Keys, In-flight mode, Keypad Lock, Vibra Alert, Dual SIM cards, Blinking Lights, Dedicated Headset plug, Screen saver

Games and applications: Agenda, Alarm Clock, Calculator, Calendar, Stopwatch, Countdown timer, Handwriting recognition, Document Viewer, Documents Reader, Motion sensor, Widget, File Manager, Photo Editor

Language available: UI: English, Vietnamese

Operating System: Android4.4.2

Personalisation/Customization:

Downloadable Animated GIF, Downloadable Picture, Downloadable Ringtones, Wallpaper, Ringtones, Screen Saver

Text input: Smart predictive input

Vibrator

Volume control

Multimedia: FM Radio

Personal Info Management: Daylight saving, International clock, Quick Note, Smart Phonebook, Task list, Time Zone

GPS

Built-in GPS

Supports A-GPS



* MicroSD memory card is not included.

* Availability of certain features is subject to valid service subscription from your network operator.

* All visuals provided are for reference purposes only. Actual product features such as phone colors and screenshots may vary from those pictured.

* Actual available memory for end user usage may vary from market to market due to pre-configuration.

* Specifications indicated are based on an initial full battery charge tested in a laboratory with Bluetooth and WiFi switched off. Actual performance will depend on network service provider and usage.

* Specifications indicated are subject to change without prior notice.