



Philips
Xenium

X510

Black

CTX510BLK

Enduring connection

Enjoy the extra convenience of the Philips Xenium X510. Its 8 hours talk time, dual SIM card slots, touch screen and keypad all work to make your connections easy and reliable wherever you may be.

Always connected

- Dual SIM for 2 groups of contacts
- Up to 8 hours of talk time

Multimedia - anytime, anywhere

- Capture your memories with 2 megapixel camera
- Easy tuning with on-screen display on RDS FM radio stations
- Enjoy Bluetooth stereo music
- MicroSD memory card slot for extra memory/ data storage

PHILIPS
sense and simplicity

Highlights

Dual SIM

Organize your life better and keep your contacts separate by using 2 different phone numbers. With Dual SIM, you don't need to carry 2 phones around.

Up to 8 hours talk time

The phone can support up to 8 hours conversation on a single charge.

RDS FM Radio

Enjoy quick and easy tuning to your favorite stations with Radio Data System (RDS) display, which shows the name of the station instead of

frequency numbers. RDS also allows stations to transmit text messages and information directly to your radio display, so you can keep updated with news updates and radio promotions.

Bluetooth stereo music

Your Philips mobile phone supports A2DP Bluetooth Profile. It lets you enjoy your favorite tunes wirelessly and in high quality stereo music from your Bluetooth headphones.

MicroSD memory card slot

You can now enjoy extra capacity and storage of multimedia files by inserting a MicroSD memory card into the built-in memory card slot of your phone.

2 Megapixel camera

Capture and enjoy precious memories in clear and sharp picture quality with 2 megapixel resolution. Vibrant, colorful pictures are just a click away.



Specifications

Dimensions

- Antenna: Integrated
- Form Factor: Slider
- Handset dimensions: 106X51.8X15.65mm
- Handset weight: 103g

Picture/Display

- Main Display Colors: 262K
- Main Display Resolution: 240x320 pixel
- Main Display Technology: TFT
- Touch-sensitive screen: Touch Screen
- Diagonal screen size (inch): 2.4 inch

Network Features

- GPRS (Rx+Tx): Class 10 (4+2), Class B
- GSM band: 900, 1800 MHz
- Messaging: Concatenated SMS (Long SMS), E-mail, MMS, Multimedia Message Service, Predefined messages (SMS, MMS), SMS CB (Cell Broadcast), SMS (Short Message Service), SMS multi-target
- Services: OTA provisioning (WAP, MMS), SIM Toolkit / Release 99, WAP 2.0
- Voice Codec: FR/EFR/AMR/HR

Still Picture Capturing

- Camera: Integrated
- Image sensor type: CMOS
- Picture file format: JPEG
- Picture Mode: Night mode, Self-timer mode, Multi-shot
- Picture resolution: 768x1024, QVGA (320x240)
- Special effects preview mode: Blue effect, Color invert, Green effect, Grey scale, Normal, Sepia
- White balance: Automatic, Night
- Picture quality: Normal, High, Low

Still Picture Playback

- Picture Compression Format: BMP, GIF, JPEG
- Picture Enhancement: Create albums
- Rotation: 90 degree steps
- Slide show

Sound

- Ringers: MP3 ringer, Polyphonic (64 tones), Voice memo ringer, AMR ringer
- Equalizer settings: Classical, Dance, Pop, Rock, Bass, Normal, Treble, Party

Video Recording

- Compression formats: MPEG4, 3GP, H.263
- Resolution (pxl): 176x144

Video Playback

- Compression formats: MPEG4, H.263, 3GP
- Resolution (pxl): 176x144

Audio Recording

- Record your own voice

Audio Playback

- Audio supported formats: AMR, Midi, MP3, AAC, WAV, AAC+

Storage Media

- Memory Card Types: Micro Secure Digital (SD)
- Memory management: Memory status, Dynamic memory allocation
- Maximum memory card capacity: 8 GB
- User memory: 1 MB

Convenience

- Buttons and controls: 4-way navigation key and enter, Soft keys, Power On/Off
- Call Management: Call Forwarding, Call on Hold, Call Time, Call Waiting, Caller ID, Emergency Call, Microphone mute, Missed Calls, Received Calls, Firewall, Conference Call
- Clock/Version: Analogue, Digital, International clock
- Ease of Navigation: Touch panel, Active Slider
- Ease of Use: Hands free mode, Hot Keys, In-flight mode, Screen Saver Digital Clock, Softkeys, Vibra Alert
- Games and applications: Agenda, Alarm Clock, Calculator, Java MIDP 2.0, Lunar Calendar, Stopwatch, Handwriting recognition, Currency converter
- Language available: UI: Chinese Simplified, Chinese Traditional, English
- Personal Info Management: Daylight saving, Time Zone, Smart Phonebook, International clock
- Personalisation/Customization: Downloadable Animated GIF, Downloadable Java Applications, Downloadable Picture, Downloadable Ringtones, Wallpaper, Ringtones
- Text input: T9
- Vibrator
- Volume control
- Multimedia: FM Radio

Power

- Battery saving manager: Auto switch on/off
- Battery Type: Li-ion
- Battery capacity: 1050mAh
- Standby time: Up to 600 hours
- Talk time: Up to 8 hours

Accessories

- Standard Package Includes: Battery, CD ROM (Mobile Phone Tools), Charger, Handset, Stylus, User Manual, USB data cable, Premium Stereo Headset

Connectivity

- Headset: via 3.5mm jack connector
- Modem Capabilities: CSD (Voice, Data), GPRS
- PC Link: USB 2.0
- Serial connections: USB-miniUSB data cable
- Synchronisation PC organizer: MS Outlook
- Bluetooth profiles: A2DP, Handsfree, Headset, Object push profile, File transfer profile
- Bluetooth: Bluetooth V2.0

Green Specifications

- Lead-free soldered product
- Packaging material: Carton



Issue date 2010-06-14

Version: 5.2.2

12 NC: 8670 000 66212
EAN: 69 23410 70456 3

© 2010 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com

* Specification indicated based on initial full battery charge tested in laboratories with Bluetooth switched off. Actual performance is dependent on network service provider and usage.