



Philips
Cordless phone

4.6cm display/ white backlight
Handset speakerphone



D4601B

Smart Elegance

With a large reverse display, extended privacy settings, micro USB charging and stylish contours, the Philips D460 Cordless Phone blends sleek form and function while offering superior sound. Enjoy every call in crystal clarity.

As convenient as it should be

- High contrast, 4.6cm (1.8") white on black graphical display
- Keypad backlight for fast access even in dark room
- Three-field entries for assigning 3 numbers to one contact
- Black list, anonymous call, silence mode, call barring
- Up to 16 hours of talk time on a single charge
- AOH / Caller ID – so you always know who is calling*
- Stay connected during power cuts via micro-USB power bank

Exceptional sound

- HQ-Sound: high quality acoustic engineering for superb sound
- MySound profiles to match your sound preference
- Freestanding handset with a speaker for easy handsfree calls

Eco-conscious product

- Low radiation and power consumption


PHILIPS

Cordless phone
4.6cm display/ white backlight Handset speakerphone

D4601B/51

Highlights

4.6cm (1.8") graphical display



High contrast, 4.6cm (1.8") white on black graphical display

Eco-conscious product




Philips phones are energy efficient and designed to be respectful to the environment.

Handset speakerphone




Handsfree mode uses a built-in loud speaker to amplify the voice of the caller, allowing you to speak and listen during a call without holding the phone to your ear. This is especially useful if you want to share the call with others or simply multitask.

HQ-Sound



Philips cordless phones with HQ-Sound: build upon decades of experience and breakthrough innovations in developing Hi-Fi audio products and high-end headphones to deliver excellent voice clarity on our DECT phones. When it comes to improving sound quality, our acoustics engineers and architects have thought of everything – high quality components, digital signal processing, precise acoustic design, advanced testing and fine-tuning. The result is sound that is crisp, clear and authentic. Sound so good and natural, it is almost like being there in person.

MySound profiles



Sound perception is subjective, and everyone has their own listening preference. MySound brings personality back to every conversation by allowing you to choose the audio profile that best matches your sound preferences: Clear – to make voices sound crisper and clearer; Soft – for friendly, softer tones; Warm – to make voices sound welcoming and warm.

Up to 16 hours talk time



Up to 16 hours of talk time on a single charge

Keypad backlight



The soft white backlight makes keys easy to read in low light conditions and at night.

Micro-USB connector

The integrated micro-USB connector socket on the base unit ensures that the phone can stay powered via a pre-charged power bank, allowing you to make calls even if the power cuts out. The power bank charging feature supports most power bank products with which are able to provide a minimum output current below 85mA without automatic shutdown. Power bank sold separately.

AOH / Caller ID*



Sometimes it is good to know who is calling before you answer. And our Caller ID lets you keep track of who is on the other end of the line.

Specifications

Convenience

- Menu structure in the handset: List Menu
- Speakerphone - talk handsfree
- Personalization: Silent mode
- Call barring: Restrict the phone from making specific outgoing calls
- Block callers/ Blacklist*: Restrict the phone from ringing on specific incoming numbers
- Signal strength indicator: 3-bar indicator
- Battery level indicator: 3-bar battery icon
- Date / Time display
- Event light on the handset
- Programmable hot keys: Key 1 and 2
- Call Management: Call Waiting*, Caller ID*, Microphone mute, Missed Calls, Received Calls, Dialed calls
- Keypad lock
- Key tone on/off
- Auto Registration
- Auto hang up
- Multi handset capability: Up to 4
- Number of keys: 20
- Backlit keypad: White at navigation keys; soft amber at numeric keys
- Illuminated keypad
- Enlarge dialing digit
- Base Station keys: Paging key
- Up to 16 hrs talk time
- Up to 250 hrs standby time
- Charge time: 8 hours
- Line cord length: 1.8m
- Power cord length: 1.8m
- Range: Open field <300m; indoor <50m
- Event notifications: For voice message, missed calls and incoming calls
- Non-slip grip: Vertical pill shape texture
- Alarms: Alarm Clock
- Call block: Anonymous call, Black list
- Family Notes
- Intercom - multiple handsets

Sound

- Sound Profile: MySound
- Volume control on handset

- Ringtones on handset: 10 polyphonic
- HQ-Sound

Picture/Display

- Display size: 4.6cm / 1.8"
- Display type: Reversed dot matrix
- Backlight: Yes
- Backlight color: White

Memory Capacity

- Phonebook: 50 names and numbers
- Redial List Capacity: 20 last numbers
- Call log entries: 50 entries
- Phonebook store in the base
- Multiple phonebook entries: 3-field

Power

- Battery Capacity: 550 mAh
- Battery type: AAA NiMH Rechargeable
- Mains power: AC 100-240V ~50/60Hz
- Power Consumption: < 0.7 W

Security

- Transmission encryption : Yes

Network Features

- Compatible: GAP

SAR Value

- Philips handsets: <0.1 W/kg

Eco Design

- EcoMode: automatic & manual
- Eco+

Packaging dimensions

- Packaging type: Carton
- Number of products included: 1
- Type of shelf placement: Laying
- Packaging dimensions (W x H x D): 18.4 x 13.5 x 5.9 cm
- Gross weight: 0.393 kg
- Nett weight: 0.315 kg
- Tare weight: 0.078 kg
- EAN: 48 95185 62956 8



Issue date 2019-05-30

Version: 1.1.3

12 NC: 8670 001 44934
EAN: 48 95185 62956 8

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* *This feature requires additional subscription of Caller ID service.
Please check with your local network operator for details.