

# PHILIPS

Handheld vacuum cleaner

9.6 V



FC6091



## The first anti-allergy Mini Vac by Philips

With high NiMH Power and HEPA filtration

This is the first Mini Vac that has a HEPA filter to trap even the finest dust. Its high-powered Nickel-Metal hydride batteries ensure lasting cleaning performance.

**Environmentally friendly, longer-lasting power**

- Green NiMH battery, longer-lasting performance

**Clean air in your home**

- HEPA filter to trap fine dust

**Cleaning in comfort**

- Exceptionally quiet

**Easy to empty and hygienic to clean**

- One-step click-off nozzle, dishwasher safe

**Lasting cleaning performance**

- Cyclonic airflow and 2-stage filtration system

# Highlights

## Green NiMH battery, longer-lasting performance



Nickel-Metal hydride (NiMH) batteries are green batteries. This means they do not have highly toxic elements, which makes them better for the environment. Furthermore, NiMH batteries have longer-lasting power that ensures performance over time.

## HEPA filter to trap fine dust



The HEPA filter ensures that fine dust and microscopic vermin stay inside the dirt chamber.

## Exceptionally quiet



The Philips Mini Vac, with its powerful motor, is exceptionally quiet thanks to its special streamlined design. The comfortable noise level allows you to tidy up your home any time you want to.

## One-step click-off nozzle, dishwasher safe



The Philips Mini Vac is easy and quick to empty and hygienic to clean. The Philips Mini Vac has a nozzle that easily clicks off in just one step, so you can empty the Mini Vac without touching the dirt. When the nozzle needs cleaning, you simply put it in the dishwasher. That way you've always got a spotless, dirt-free Mini Vac at hand.

## Cyclonic and 2-stage filter



The Philips MiniVac's cyclonic airflow keeps the dirt inside rotating to ensure optimal, high suction power and lasting cleaning performance. Its 2-stage filtration system ensures that, once inside, the dirt cannot escape. The first filter blocks most dirt, while the pleated, second filter traps the finer dust particles.

## Brush tool, crevice tool and bendable crevice tool



The Philips Mini Vac comes with a number of accessories to tackle any job with ease. The soft brush attachment is gentle on delicate surfaces and the bendable crevice tool and crevice tool let you clean even those awkward, hard-to-reach places.

# Specifications

## Design

**Colour:** Titanium and marine blue

**Design features:** Translucent dust chamber

## Filtration

**Dust capacity:** 0.5 l

**Filter system:** 2-stage HEPA

## Nozzles and accessories

**Other accessories:** Charging base

## Performance

**Airflow (max):** 810 l/min

**Battery type:** NiMH

**Battery voltage:** 9.6 V

**Charging time:** 16-18 hour(s)

**Input power (max):** 100 W

**Noise level (Lc IEC):** 78 dB

**Runtime:** 10 minute(s)

**Suction power (max):** 19 W

**Vacuum (max):** 4.1 kPa

## Usability

**Special features:** Charging indication, Direct charging plug, Soft touch handle

## Weight and dimensions

**Dimensions of A-box (L x W x H):** 403 x 393 x 444 mm

**Appliances per A-box:** 4

**Dimensions of product (L x W x H):** 195 x 190 x 426 mm

**Weight of product:** 1.4 kg

