

PHILIPS

Handheld vacuum cleaner

MiniVac

Car

12 V



FC6093



The first anti-allergy Mini Vac by Philips Ideal for your car and home

The Philips MiniVac Car 12 V FC6093/01 has a HEPA filter to trap even the finest dust. It is the ideal combination for car and home. Its battery gives cordless freedom in your home, while the car plug gives extra cleaning time in your car.

Environmentally friendly, longer-lasting power

- Green NiMH battery, longer-lasting performance

Clean air in your home

- HEPA filter to trap the fine dust

Cleaning in comfort

- Exceptionally quiet

Easy to empty and hygienic to clean

- One-step click-off nozzle, dishwasher safe

Ideal anywhere - even in your car!

- Brush tool, bendable crevice tool and car plug

Highlights

Green NiMH battery, longer-lasting performance



Nickel-Metalhydride (NiMH) batteries are green batteries. This means they do not have highly toxic elements, which makes them better for the environment. Furthermore NiMH batteries have longer-lasting power that ensures performance over time.

HEPA filter to trap the fine dust



The HEPA filter ensures the fine dust and microscopic vermin stay inside the dirt chamber.

Exceptionally quiet



The Philips Mini Vac, with its powerful motor, is exceptionally quiet thanks to its special streamlined design. The comfortable noise level allows you to tidy up your home any time you want to.

One-step click-off nozzle, dishwasher safe



The Philips Mini Vac is easy and quick to empty and hygienic to clean. The Philips Mini Vac has a nozzle that easily clicks off in just one step, so you can empty the Mini Vac without touching the dirt. When the nozzle needs cleaning, you simply put it in the dishwasher. That way you've always got a spotless, dirt-free Mini Vac at hand.

Brush tool, bendable crevice tool and car plug



The Philips mini vacuum cleaner with rechargeable battery (12 V) includes a special car-cleaning kit with car plug for unlimited runtime, which means consumers can clean their cars thoroughly in one go. This model also comes with an extra-long, flexible crevice tool for easy cleaning around car seats and other hard-to-reach areas.

Cyclonic and 2-stage filter



The Philips MiniVac's cyclonic airflow keeps the dirt inside rotating to ensure optimal, high suction power and lasting cleaning performance. Its 2-stage filtration system ensures that, once inside, the dirt cannot escape. The first filter blocks most dirt, while the pleated, second filter traps the finer dust particles.

Specifications

Design

Color: Titanium and orange red

Design features: Translucent dust chamber

Filtration

Dust capacity: 0.5 L

Filter system: 2-stage HEPA

Nozzles and accessories

Other accessories: Car plug, Charging base

Performance

Airflow (max): 840 l/min

Battery type: NiMH

Battery voltage: 12 V

Charging time: 16-18 hour(s)

Input power (max): 120 W

Noise level (Lc IEC): 79 dB

Runtime: 11 minute(s)

Suction power (max): 22 W

Vacuum (max): 4.2 kPa

Usability

Special features: Charging indication, Direct charging plug, Soft touch handle

Weight and dimensions

Dimensions of A-box (LxWxH): 403 x 393 x 444 mm

Appliances per A-box: 4

Dimensions of packaging (LxWxH): 195 x 190 x 426 mm

Weight of product: 1.5 kg

