

PHILIPS

Handheld vacuum cleaner

14.4 V

2-in-1



FC6094



High power, great results

With comfort kit for larger areas

For powerful, multi-faceted cleaning, the new Philips FC6094 (14.4 V) has it all. Its comfort kit includes a floor nozzle and a telescopic stick to comfortably clean spills and messes even across larger areas.

Fast and effective cleaning

- 14.4 V rechargeable appliance with cyclonic airflow

Cleaning in comfort

- Exceptionally quiet

Easy-to-clean nozzle

- Detachable dishwasher-proof nozzle

The right accessory for any surface or job

- Telescopic tube, floor nozzle, brush, crevice tool

Always at hand

- Smart-design charging base for wall or table

Highlights

14.4V rechargeable appliance with cyclonic airflow



The Philips Mini Vac's cyclonic airflow keeps the dirt inside rotating to ensure optimal, high suction power and cleaning performance that lasts.

Exceptionally quiet



The Philips Mini Vac, with its powerful motor, is exceptionally quiet thanks to its special streamlined design. The comfortable noise level allows you to tidy up your home any time you want to.

Detachable dishwasher-proof nozzle



The Philips Mini Vac is also easy to maintain. If the nozzle needs cleaning, you simply put it in the dishwasher. That way you've always got a spotless, dirt-free Mini Vac at hand.

Telescopic tube, floor nozzle, brush, crevice tool



The Philips FC6094 (14.4 V) comes with a number of accessories to tackle any job with ease. Its comfort kit includes a floor nozzle and a telescopic stick to comfortably clean spills and messes even across larger areas. Its soft brush attachment is gentle on delicate surfaces and its crevice tool lets you clean even those awkward, hard-to-reach places.

Smart-design charging base for wall or table



You can store the Philips Mini Vac on a convenient charging base, against a wall or on a table. This means the Philips Mini Vac, with its powerful rechargeable battery, is always ready when you are.

Cyclonic and 2-stage filter



The Philips MiniVac's cyclonic airflow keeps the dirt inside rotating to ensure optimal, high suction power and lasting cleaning performance. Its 2-stage filtration system ensures that, once inside, the dirt cannot escape. The first filter blocks most dirt, while the pleated, second filter traps the finer dust particles.

Specifications

Design

Color: Queens red

Filtration

Dust capacity: 0.5 L

Filter system: 2-stage

Nozzles and accessories

Other accessories: Charging base

Standard nozzle: Floor nozzle

Performance

Airflow (max): 900 l/min

Battery voltage: 14.4 V

Charging time: 16-18 hour(s)

Noise level (Lc IEC): 80 dB

Runtime: 11 minute(s)

Suction power (max): 26 W

Vacuum (max): 5 kPa

Usability

Special features: Battery low indication, Charging indication, Soft touch handle

Tube type: Telescopic tube

Weight and dimensions

Dimensions of A-box (LxWxH): 403 x 393 x 546 mm

Appliances per A-box: 4

Dimensions of packaging (LxWxH): 195 x 190 x 528 mm

