

# PHILIPS

Stick vacuum cleaner

MiniVac

2-in-1

14.4 V



FC6095/01



## The first anti-allergy Mini Vac by Philips Most powerful cordless 2-in-1

The Philips MiniVac 2-in-1 14.4 V is the first MiniVac that has a HEPA filter to trap even the finest dust. Moreover, it is the most powerful 2-in-1 cordless cleaner that tackles every spot and floor.

### **Environmentally friendly, longer-lasting power**

- Green NiMH battery, longer-lasting performance

### **Clean air in your home**

- HEPA filter to trap the fine dust

### **Cleaning in comfort**

- Exceptionally quiet

### **Easy to empty and hygienic to clean**

- One-step click-off nozzle, dishwasher safe

### **Easy to park and charge handstick**

- Telescopic stick, self-standing, direct charge

# Highlights

## Green NiMH battery, longer-lasting performance



Nickel-Metalhydride (NiMH) batteries are green batteries. This means they do not have highly toxic elements, which makes them better for the environment. Furthermore NiMH batteries have longer-lasting power that ensures performance over time.

## HEPA filter to trap the fine dust



The HEPA filter ensures the fine dust and microscopic vermin stay inside the dirt chamber.

## Exceptionally quiet



The Philips Mini Vac, with its powerful motor, is exceptionally quiet thanks to its special streamlined design. The comfortable noise level allows you to tidy up your home any time you want to.

## One-step click-off nozzle, dishwasher safe



The Philips Mini Vac is easy and quick to empty and hygienic to clean. The Philips Mini Vac has a nozzle that easily clicks off in just one step, so you can empty the Mini Vac without touching the dirt. When the nozzle needs cleaning, you simply put it in the dishwasher. That way you've always got a spotless, dirt-free Mini Vac at hand.

## Telescopic stick, self-standing, direct charge



The FC6094/11 is a real 2-in-1, it is used as handheld or handstick. With the telescopic stick and floor nozzle it cleans comfortably spills and messes even across larger areas. After use the FC6094/11 can be parked in between cleaning jobs and directly charged when needed.

## Cyclonic and 2-stage filter



The Philips MiniVac's cyclonic airflow keeps the dirt inside rotating to ensure optimal, high suction power and lasting cleaning performance. Its 2-stage filtration system ensures that, once inside, the dirt cannot escape. The first filter blocks most dirt, while the pleated, second filter traps the finer dust particles.

# Specifications

## Design

**Color:** Titanium and fresh red

**Design features:** Translucent dust chamber

## Filtration

**Dust capacity:** 0.5 L

**Filter system:** 2-stage HEPA

## Nozzles and accessories

**Other accessories:** Charging base

**Standard nozzle:** Floor nozzle

## Performance

**Airflow (max):** 900 l/min

**Battery type:** NiMH

**Battery voltage:** 14.4 V

**Charging time:** 16-18 hour(s)

**Input power (max):** 130 W

**Noise level (Lc IEC):** 80 dB

**Runtime:** 11 minute(s)

**Suction power (max):** 26 W

**Vacuum (max):** 5 kPa

## Usability

**Special features:** Charging indication, Direct charging plug, Soft touch handle

**Tube type:** Telescopic tube

## Weight and dimensions

**Dimensions of A-box (LxWxH):** 403 x 393 x 546 mm

**Appliances per A-box:** 4

**Dimensions of packaging (LxWxH):** 195 x 190 x 528 mm

**Weight of product:** 1.6 kg

