

Lithium

10.8 V



FC6146/02

Powerful MiniVac for a better cleaning result

Bagless cyclonic airflow and aerodynamic nozzle

Enjoy a better cleaning result with the powerful Philips MiniVac Lithium 10.8 V. The bagless cyclonic airflow and 2-stage filtration system guarantee lasting performance, while the aerodynamic nozzle design ensures a superior dust pick-up.

Environmentally friendly

· Green Lithium-Ion technology

Optimal filtration

• 2-stage bagless cyclonic airflow for optimal filtration

Easy to use

· One-step click-off nozzle for easy emptying

Guaranteed

- Longer-lasting lightweight Lithium-Ion batteries
- Quick charge in 8 hours

Superior cleaning results

• Aerodynamic nozzle design for a better dust pick-up







Highlights

Green Lithium-Ion technology



Lithium-Ion batteries are really green batteries. They do not have toxic elements, which makes them better for the environment. Next to that, they do not discharge when the product is not in use and they guarantee a very low standby-power. Therefore, they are also energy saving.

2-stage bagless cyclonic



The bagless cyclonic airflow keeps the dirt inside rotating to ensure optimal, high suction power and lasting cleaning performance. Its 2-stage filtration system ensures that, once inside, the dirt cannot escape. The first filter blocks most dirt, while the second filter traps the finer dust particles.


Aerodynamic nozzle design



The aerodynamic nozzle design of the Philips MiniVac is created to ensure an optimum dust pickup of even the most fine dust particles. The

ergonomic shape of the nozzle helps you to clean even the most hard-to-reach areas.

Longer-lasting lightweight Lithium-Ion batteries




The powerful Lithium-Ion (Li-Ion) batteries of the Philips Mini Vac have longer-lasting power versus standard Nickel-Cadmium (NiCd) batteries. Li-Ion batteries are also very lightweight, giving you a more enjoyable cleaning experience.

One-step click-ff nozzle



The Philips MiniVac vacuum cleaner is easy and quick to empty and hygienic to clean. The Philips MiniVac has a nozzle that easily clicks off in just one step, so you can empty the Mini Vac without touching the

Quick charge in 8 hours



The Lithium batteries charges an empty battery in only 8 hours, twice as fast as in ordinary chargers.

· Color: Black/stainless steel/ red accents

Specifications

· Design features: Translucent dust chamber

Filtration

- Dust capacity: 0.5 l
- · Filter system: 2-stage cyclonic action

Nozzles and accessories

· Other accessories: Charging base

Performance

- Airflow (max): 950 l/min
- Battery type: Li-lon
- Battery voltage: 10.8 V
- Charging time: 8 hour(s)
- Input power (max): 100 W • Noise level (Lc IEC): 81 dB
- Runtime: 9 minute(s)
- Suction power (max): 22 W
- Vacuum (max): 4.3 kPa

· Special features: Charging indication, Soft touch

Weight and dimensions

- Dimensions of A-box (LxWxH): 508 x 335 x
- Appliances per A-box: 6
- Dimensions of packaging (LxWxH): $460 \times 160 \times$
- Weight of product: 0.8 kg



Issue date 2013-04-19

Version: 4.1.1

© 2013 Koninklijke Philips Electronics N.V. All Rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.