

PHILIPS

Cordless rechargeable
vacuum cleaner


PowerPro Aqua

3-in-1

Vacuum, mop and handheld

25.2 V

Mini turbo brush



FC6409/01



Vacuums and mops in one stroke

Always at hand to quickly clean daily messes

The new cordless (25.2V) PowerPro Aqua is a 3in1 powerful tool to deal with daily messes. A bagless vacuum cleaner includes a handheld for chair or corners, a mini turbo brush for soft surfaces and a mopping system to clean damp dirt.

Cleans everyday messes with vacuum and mop

- PowerCyclone technology for high vacuum cleaning performance
- New mopping system with optimal wetness on hard floors
- Handheld for vacuuming furniture and hard to reach corners
- TriActive Turbo nozzle for powerful performance on carpets
- 3 layer filter technology captures micro particles

Always at hand and convenient for daily usage

- Cordless cleaning: freedom to clean everywhere
- Bagless: one-step empty dust bucket, simple and hygienic
- Powerful 25.2V Lithium Ion battery for up to 1 hour cleaning
- Mini turbo brush for cleaning soft surfaces
- Instant click on/off mopping system for wet cleaning
- High maneuverability and light weight for easy handling
- Microfiber pads

Highlights

3 layer filter



3 layer washable filter can capture >90% of allergens like pollen, pet hair and dust, for a clean air.

Bagless



With the new bagless PowerPro Aqua vacuum cleaner, you can dispose dust from the dust bucket without touching the dirt.

Cordless operation



The rechargeable batteries for cordless operation gives you freedom to clean everywhere. Now the cable is not a barrier anymore and you can easily clean in different rooms with no hassle.

Handheld included



Handheld for vacuuming furniture and hard to reach corners

Light and maneuverable



High maneuverability and light weight are ensured with the new PowerPro Aqua vacuum cleaner for easy handling.

Click on/off mopping system



With the magnet on both sides, the mopping system is easily clicked on and off to the nozzle.

Microfiber pads

The new PowerPro Aqua includes two types of microfiber pads to mop different surfaces: 1) One universal microfiber pad for regular mopping, which is ideal for such surfaces like tiles. 2) One soft microfiber pad for cleaning more delicate surfaces, such as wooden surfaces. The microfiber pads can be washed by hand*

Innovative mopping system



The unique mopping system controls the water release to maintain optimal wetness for all hard floors throughout the cleaning. The microfiber pads* can be washed by hand or in washing machine.

PowerCyclone technology



PowerCyclone fan rotates with speeds up to 300 km/h to create high G-force in the PowerCyclone which effectively separates dust from air, hence continuously high cleaning performance.

25.2V Lithium Ion battery



Cordless cleaning with powerful 25.2V Lithium Ion battery for up to 1 hour of runtime. You can charge anytime without needing to wait for an empty battery

Specifications

Performance

Battery type: Li-Ion

Battery voltage: 25.2 V

Charging time: 5 hour(s)

Mopping element: Unique mopping system

Runtime: up to 60 minute(s)

Surface coverage per tank: 50 m²

Sound power level: 83 dB

Usability

Clean water tank capacity (max): 0.2 L

Detergents that can be used: clear detergent or just water

Design

Color: Petrol blue metallic

Design features: On-off

Filtration

Dust capacity: 0.6 L

Exhaust filter: Foam filter

Filter system: 3 layer German technology

Nozzles and accessories

Accessories included: 2-in-1 brush, AC power adaptor, Crevice tool, 1 pad holder, 2 microfiber pads

Standard nozzle: TriActive Turbo Nozzle

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Weight and dimensions

Weight of product: 4.7 kg

