

# PHILIPS

## TriActive+ multi-purpose nozzle

Suitable for all floors

Universal fitting

With connection adapter



FC8075/01



## 3 cleaning actions in one go

with side brushes and large front opening

The unique TriActive+ nozzle performs 3 cleaning actions in one go, to deliver a high cleaning performance. The nozzle is suitable for use on all types of floors, and has a universal fitting thanks to the connection adapter provided.

### High cleaning performance

- Large front opening for big crumbs
- Side brushes to clean along walls
- Soleplate designed for high dust pick-up
- Suction power from 3 directions
- Suitable for all hard floors and carpets

### Compatible with most vacuum cleaners

- A connection adapter makes the nozzle universally fitting

# Highlights

## Large front opening



The TriActive+ nozzle picks up more big particles due to its large front opening.

## Side brushes




The TriActive+ nozzle is equipped with soft brushes on the sides, to improve the cleaning performance alongside walls and furniture.

## Designed for high dust pick-up



The TriActive+ nozzle is equipped with a special soleplate design, to maximize the dust removal on carpets and hard floors.

## Suction from 3 directions



The TriActive+ nozzle has air channels that allow dust removal from the front of nozzle, as well as from the side. With one stroke, dust is being removed from 3 directions.

## Suitable for all floors



The nozzle is suitable to operate on all types of floors: hard floors (parquet, tiles, vinyl) and especially carpets.

## Universal fitting



The nozzle is provided together with a connection adapter. Thus, it is compatible with Philips, Miele, Electrolux, AEG, Bosch, Siemens, Samsung, Rowenta, Hoover, LG, Panasonic, Zelmer models and many other vacuum cleaners with 32 or 35 mm connection.

# Specifications

## Accessory specifications

Number of nozzles: 1  
Number of adaptors: 1

## Usability

Tube coupling: Universal, Conical

## Suitable for

**EasyLife:** FC8130 - FC8139, FC8140 - FC8149

**EasyGo:** FC8082 - FC8083

**CompactGo:** FC8120, FC8121, FC8291

**PowerLife:** FC8320 - FC8329, FC8450 - FC8459

**PowerGo:** FC8293 - FC8296, FC8240 - FC8246, FC8250, FC8253, FC8289

**Performer Compact:** FC8383 - FC8391,

FC8370 - FC8379, FC8366 - FC8367 (A+)

**PerformerActive:** FC8650 - FC8664, FC8580 - FC8593, FC8520 - FC8527, FC8574 - FC8579, FC8563

**Jewel:** FC9050 - FC9079

**Performer:** FC9150 - FC9179, FC8680 - FC8682

**PerformerPro:** FC9180 - FC9199

**Performer Expert:** FC8720 - FC8728

**Performer Silent:** FC8779 - FC8786, FC8741 - FC8745

**Performer Ultimate:** FC8921 - FC8925, FC8941 - FC8957

**SilentStar:** FC9300 - FC9319

**PowerPro Compact:** FC8370 - FC8379, FC8515 - FC8517, FC9320 - FC9329, FC9330 - FC9334, FC9350 - FC9353

**PowerPro Active:** FC8630 - FC8649, FC9520 - FC9525, FC8670 - FC8679, FC9528 - FC9533, FC9540, FC9541

**PowerPro:** FC8760 - FC8767, FC8769, FC8770

**PowerPro Expert:** FC9712 - FC9714, FC9720 - FC9725, FC9728, FC9732 - FC9735,

FC9729, FC9741 - FC9746

**PowerPro Ultimate:** FC9911 - FC9912, FC9919 - FC9934

**Marathon:** FC9200 - FC9225

**Aqua Action:** FC8950 - FC8952

## Sustainability

Packaging: > 90% recycled materials

