



Philips PowerLife
Vacuum cleaner with bag

Energy efficiency class B
TriActive nozzle



FC8322/09

Full performance

Less energy consumption

The new Philips PowerLife delivers full cleaning performance thanks to the unique TriActive nozzle, engineered for high dust removal.

Excellent cleaning results


- Energy efficiency class B
- A-class performance on hard floors
- The TriActive nozzle applies 3 cleaning actions in one go

Convenience

- 3L dust compartment and s-bag for long lasting performance
- Comfortable cleaning thanks to the lightweight aluminum tube
- Reach all corners thanks to the extra long ergonomic grip

Highlights

Energy efficiency class B



This vacuum cleaner is engineered to achieve full performance with an energy efficiency class B.

A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

3L dust capacity



The 3L dust compartment maximizes the potential of the s-bag Classic dust bag, thus ensuring long lasting performance.

Aluminum telescopic tube



The lightweight, aluminum vacuum cleaner tube is comfortable to use and carry. The 2-piece telescopic tube can be easily adjusted to your preferred height.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

Specifications

Performance

- Energy efficiency rating: B
- Annual energy consumption: 33.7 kW h
- Carpet cleaning class: E
- Hard floor cleaning class: A
- Dust re-emission class: E
- Sound power level: 84 dB
- Airflow (max): 29,4 l/s l/s
- Vacuum (max): 19,5 kPa
- Input power (IEC): 750 W

Design

- Color: Full red

Filtration

- Dust bag type: s-bag Classic Long Performance
- Exhaust filter: Microfilter
- Motor filter: Microfilter
- Dust capacity: 3 L

Usability

- Tube type: Aluminium 2-P telescopic tube
- Tube coupling: Conical
- Wheel type: Plastic
- Carrying handle: Front
- Dust full indicator
- Action radius: 8 m
- Cord length: 5 m

Nozzles and accessories

- Standard nozzle: TriActive nozzle
- Accessories included: Crevice tool, Small nozzle
- Additional nozzle: Hard floor nozzle

Sustainability

- Packaging: > 90% recycled materials
- User manual: 100% recycled paper

Weight and dimensions

- Weight of product: 4.2 kg
- Dimensions of product (LxWxH): 406 x 282 x 220 mm



Issue date 2018-05-23

Version: 13.1.1

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com