

PHILIPS

Vacuum cleaner
with bag

PowerLife

TriActive nozzle

FC8457/91



Full performance

Less energy consumption

The new Philips PowerLife delivers full cleaning performance thanks to the unique TriActive nozzle, engineered for high dust removal.

Excellent cleaning results

- A-class performance on hard floors
- The TriActive nozzle applies 3 cleaning actions in one go

Convenience

- 3L dust compartment and s-bag for long lasting performance
- Comfortable cleaning thanks to the lightweight aluminum tube
- Reach all corners thanks to the extra long ergonomic grip



asimpleswitch.com

Highlights

A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

3L dust capacity




The 3L dust compartment maximizes the potential of the s-bag Classic dust bag, thus ensuring long lasting performance.

Aluminum telescopic tube



The lightweight, aluminum vacuum cleaner tube is comfortable to use and carry. The 2-piece telescopic tube can be easily adjusted to your preferred height.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

Specifications

Performance

Annual energy consumption: 33.7 kW·h
 Sound power level: 84 dB
 Airflow (max): 29,4 l/s l/s
 Vacuum (max): 19,5 kPa
 Input power (IEC): 750 W

Design

Color: Deep black and green

Filtration

Dust bag type: s-bag Classic Long Performance
 Exhaust filter: Microfilter
 Dust capacity: 3 L

Usability

Carrying handle: Front
 Dust full indicator
 Tube coupling: Conical
 Tube type: Aluminum telescopic tube
 Wheel type: Plastic
 Power control: Electronic on appliance
 Action radius: 8 m
 Cord length: 5 m

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
 Standard nozzle: TriActive nozzle
 Accessory storage: On tubeclip
 Additional nozzle: Hard floor nozzle

Weight and dimensions

Dimensions of product (LxWxH): 406 x 282 x 220 mm
 Weight of product: 4.2 kg



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.