

PHILIPS

Bagless vacuum
cleaner

PowerPro Compact

1500 W

PowerCyclone 4

TriActive nozzle



FC8478/91



Full performance

Less energy consumption

The new Philips PowerPro Compact vacuum cleaner delivers powerful performance without compromises thanks to the PowerCyclone 4 technology and advanced bucket design.

Excellent cleaning results

- PowerCyclone 4 technology separates dust and air in one go
- The TriActive nozzle applies 3 cleaning actions in one go
- A-class performance on hard floors

Clean air in your home

- EPA10 filter system with AirSeal for healthy air

Ergonomic grip for far reach

- Reach all corners thanks to the extra long ergonomic grip

Easy to clean

- Advanced dust container design for hygienic emptying

Highlights

PowerCyclone 4 Technology



PowerCyclone 4 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

EPA10 Clean air system



EPA10 filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

Easy to empty dust container



The dust container is carefully designed to dispose collected dirt without creating a dust cloud. It is one-hand operated and thanks to its unique shape and smooth surface, you can easily control the emptying of the dust container.

Specifications

Performance

Sound power level: 84 dB
Airflow (max): 36 l/s
Vacuum (max): 23 kPa
Annual energy consumption: 51,7 kW·h
Input power (IEC): 1400 W
Input power (max): 1500 W

Design

Color: Ink Black

Filtration

Exhaust filter: Sponge
Motor filter: Washable foam inlet filter
Dust capacity: 1.5 L

Usability

Tube type: Metal 2-piece telescopic tube
Carrying handle: Front
Tube coupling: Conical
Wheel type: Plastic
Action radius: 8 m
Cord length: 5 m

Nozzles and accessories

Standard nozzle: TriActive nozzle
Accessories included: Crevice tool, Small nozzle
Additional nozzle: Hard floor nozzle

Weight and dimensions

Weight of product: 4.5 kg
Dimensions of product (LxWxH): 406 x 285 x 238 mm

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper