

PHILIPS

Bagged vacuum cleaner

5000 series

99.9% dust pick-up

900W

4L

Remote control



FC8579/09



Most powerful bagged vacuum cleaner by Philips

Locks >99.9%* of dust with 50% longer bag usage**

The Philips Performer vacuum cleaner delivers top cleaning performance with low energy consumption. Keep the air in your home clean and healthy, too, thanks to our Allergy Filter that traps 99.9%+ of harmful particles.

Superior performance

- Revolutionary AirflowMax technology for strong suction power
- 900W motor for high suction power
- 99.9% dust pick-up* to deliver deep cleaning results
- Allergy Filter captures 99.9% of particles – ECARF certified
- TriActive+ nozzle to deliver high performance on all floors

Effortless cleaning

- ErgoGrip with remote control allows for easy manoeuvrability
- Soft brush integrated into handle, always ready to use
- Easy long-lasting bags fit into large 4-liter dust chamber
- ActiveLock couplings easily adjust to every task



Highlights

AirflowMax technology



Uniquely designed dust chamber maximizes capacity and airflow with a non-clogging dustbag, that enables strong suction power right up until the dustbag is full.

High-efficiency 900W motor



High-efficiency 900W motor delivers high suction power for deep cleaning results.

99.9% dust pick-up*



TriActive+ nozzle and high suction power ensure you can vacuum 99.9% of fine dust*.

ErgoGrip with Remote control



Remote control and ErgoGrip guarantees effortless operation and manoeuvrability.

Certified Allergy Filter



Certified allergy filter captures 99.9% of dust particles - including pollen, pet hair and dust mites - ideal for allergy sufferers.

Integrated brush



Dusting brush tool is built into the handle so it's always ready to use on furniture, flat surfaces and upholstery.

Long-lasting 4L s-bags



Large 4-liter dust chamber and long-lasting universal bags allow optimum suction power until full, plus sealed, mess-free disposal.

TriActive+ nozzle



TriActive+ nozzle utilizes 3 cleaning actions in one go. It features a larger opening at the front to suck up larger debris while the specially designed soleplate removes dust from deep within carpets. Air channels on both sides of the nozzle pick up any dust and dirt alongside walls or furniture.

ActiveLock couplings



ActiveLock couplings allow attachments to easily fit to the telescopic tube with a simple snap.



5 years warranty

Register at philips.com/welcome within 3 months of purchase to enjoy 5-year warranty on the motor for free!

Specifications

Performance

Input power (max): 900 W
Airflow (max): 32,17 l/s
Input power (IEC): 650 W
Sound power level: 77 dB
Vacuum (max): 17,5 kPa

Usability

Action radius: 9 m
Carrying handle: Front
Cord length: 6 m
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber
Tube coupling: ActiveLock
Power control: Remote control

Design

Color: Opal green

Filtration

Dust bag type: s-bag Classic Long
Performance
Dust capacity: 4 L
Exhaust filter: Allergy filter
Motor filter: Microfilter

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
Additional nozzle: Hard floor nozzle
Extra accessories: Remote control
Standard nozzle: TriActive+ nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH):
447x304x234 mm
Weight of product: 5,2 kg

