



Philips Performer Active
Vacuum cleaner with bag

• 2000W

FC8653/01

Maximum suction power for better cleaning results*

With AirFlow Max technology and 4L dust capacity

The new Philips Performer Active delivers a better clean thanks to the Airflow Plus technology and the Powerful 2000W motor

Excellent cleaning results

- Revolutionary Airflow Max technology for extreme suction
- 2000 W motor generates max. 400 suction power
- Specially designed 4L dust compartment for extreme suction

Convenience

- Reach all corners thanks to the extra long ergonomic grip

Integrated Anti-Allergy system

- HEPA AirSeal with HEPA 10 filter for a healthy air
- S-bag classic long performance last up to 50% longer

PHILIPS

Specifications

Design

- Color: Star Blue

Performance

- Input power (max): 2000 W
- Input power (IEC): 1800 W
- Suction power (max): 400 W
- Vacuum (max): 30 kPa
- Airflow (max): 42 l/s
- Noise level (Lc IEC): 82 dB

Filtration

- Dust capacity: 4 l
- Exhaust filter: HEPA 10 Washable filter
- Motor filter: Micro Filter

Usability

- Action radius: 9 m
- Cord length: 6 m

- Tube type: Metal 2-piece telescopic tube
- Handgrip: Ergonomic grip with air slider
- Carrying handle: Front
- Tube coupling: Conical
- Park or storage assist: Vertical and horizontal
- Wheel type: Rubber

Nozzles and accessories

- Standard nozzle: Multi-purpose Nozzle
- Accessories: Crevice tool, Small nozzle

Sustainability

- User manual: 100% recycled paper

Weight and dimensions

- Weight of product: 5.2 kg
- Dimensions of product (LxWxH):
447x304x234 mm

Highlights

Airflow Max technology

Airflow Max technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get the highest suction power, even as the bag fills-up!

2000 Watt motor

2000 W motor generates max. 400 suction power for excellent cleaning results.

4L dust capacity

The specially designed 4L dust chamber maximizes airflow, allowing the dustbag to unfold, so you get the maximum suction power for the best results.

Extra long ergonomic grip

This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

HEPA 10 AirSeal Washable

HEPA 10 Filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

S-bag Classic long performance

This new Philips synthetic dust bag has been developed to provide long lasting vacuum cleaner performance, i.e. a high level of suction power and maximum filtration, up to the moment the dust bag is full and ready for disposal.



Issue date 2013-06-11

Version: 2.0.1

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

**Results compared to Philips PowerLife, tested internally August 2013