

PHILIPS

Vacuum cleaner
with bag

Performer Active

2100W

AirflowMax technology

EPA 10 filter

Animal+

FC8657/01



Maximum suction power for better cleaning results*

With AirFlow Max technology and 4L dust capacity

The new Philips Performer Active delivers a better clean thanks to the Airflow Plus technology and the Powerful 2100W motor

Excellent cleaning results

- Revolutionary Airflow Max technology for extreme suction
- 4L dust capacity for longer cleaning
- 2100 Watt motor generates max. 425 suction power

Convenience

- Reach all corners thanks to the extra long ergonomic grip

Integrated Anti-Allergy system

- EPA AirSeal with EPA 10 filter for a healthy air
- S-bag Classic Long Performance lasts up to 50% longer

Outstanding results on carpets and furniture

- Turbo Brush nozzle removes 25% more hairs and dust

Highlights

Airflow Max technology




Airflow Max technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get the highest suction power, even as the bag fills-up!

4L dust capacity



The specially designed 4L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

EPA 10 AirSeal



EPA 10 Filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

S-bag Classic Long Performance



This new Philips synthetic dust bag has been developed to provide long lasting vacuum cleaner performance, i.e. a high level of suction

power and maximum filtration, up to the moment the dust bag is full and ready for disposal.

Turbo Brush nozzle



The Turbo Brush nozzle allows deep cleaning of carpets and quick hair and fluff removal from carpets. The rotating brush actively removes small dust particles and hairs, resulting in a 25% better cleaning performance on carpets. The wheels of the nozzle prevent damage in case of use on hard-floors.

2100 Watt motor



2100 Watt motor generates max. 425 suction power for excellent cleaning results.

Specifications

Design

Color: Sparkle Black

Performance

Input power (max): 2100 W

Input power (IEC): 1800 W

Suction power (max): 425 W

Vacuum (max): 34 kPa

Airflow (max): 47 l/s

Noise level (Lc IEC): 80 dB

Filtration

Dust capacity: 4 L

Exhaust filter: EPA 10 filter

Motor filter: Microfilter

Usability

Action radius: 9 m

Cord length: 6 m

Tube type: Metal 2-piece telescopic tube

Handgrip: Ergonomic grip with air slider

Carrying handle: Front

Tube coupling: Conical

Park or storage assist: Vertical and horizontal

Wheel type: Rubber

Nozzles and accessories

Standard nozzle: Multi-purpose nozzle

Additional nozzle: Full turbo brush

Accessories included: Crevice tool, Small nozzle

Sustainability

User manual: 100% recycled paper

Weight and dimensions

Weight of product: 5.2 kg

Dimensions of product (LxWxH):

447x304x234 mm

