

PHILIPS

Vacuum cleaner
with bag

Performer Active

2100 W

AirflowMax technology

EPA 10 filter

FC8658/01



Maximum suction power for better cleaning results*

With AirFlow Max technology and 4L dust capacity

The new Philips Performer Active delivers a better clean thanks to the Airflow Plus technology and the Powerful 2100W motor

Excellent cleaning results

- Revolutionary Airflow Max technology for extreme suction
- 2000 W motor generates max. 425 suction power
- 4L dust capacity for longer cleaning

Convenience

- Reach all corners thanks to the extra long ergonomic grip

Integrated Anti-Allergy system

- EPA AirSeal with EPA 10 filter for a healthy air
- S-bag Classic Long Performance lasts up to 50% longer

With TriActive nozzle

- New 3-in-1 TriActive nozzle picks up coarse and fine dust

Highlights

Airflow Max technology



Airflow Max technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get the highest suction power, even as the bag fills-up!

2000 Watt motor




2000 W motor generates max. 425 suction power for excellent cleaning results.

4L dust capacity



The specially designed 4L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

EPA 10 AirSeal



EPA 10 Filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

S-bag Classic Long Performance



This new Philips synthetic dust bag has been developed to provide long lasting vacuum cleaner performance, i.e. a high level of suction

power and maximum filtration, up to the moment the dust bag is full and ready for disposal.

TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

Specifications

Design

Color: Full red

Performance

Airflow (max): 47 l/s

Input power (IEC): 1800 W

Input power (max): 2100 W

Sound power level: 80 dB

Suction power (max): 425 W

Vacuum (max): 34 kPa

Filtration

Exhaust filter: EPA 10 filter

Motor filter: Microfilter

Dust capacity: 4 L

Usability

Tube type: Metal 2-piece telescopic tube

Carrying handle: Front

Tube coupling: Conical

Wheel type: Rubber

Action radius: 9 m

Cord length: 6 m

Nozzles and accessories

Standard nozzle: TriActive nozzle

Accessories included: Crevice tool, Small nozzle

Sustainability

User manual: 100% recycled paper

Weight and dimensions

Weight of product: 5.2 kg

Dimensions of product (LxWxH):
447x304x234 mm

