

PHILIPS

Bagless vacuum cleaner

Anti-allergy



FC8732/01



Take the effort out of cleaning

Extra long cord, no bag required

EasyClean is designed for those people who want a thorough cleaning result at minimal effort.

Easily removes dirt and dust

- 1800 Watt motor generating max. 300 Watt suction power

Clean air in your home

- Super Clean Air HEPA 12 filter, 99.5% filtration

Higher cleaning efficiency

- Improved cyclone for longer lasting suction power

Easy dust disposal

- Dust bucket can easily be removed and emptied

Big reach

- An extra big 11 m reach


Highlights

1800 Watt motor




1800 Watt motor generating max. 300 Watt suction power to ensure a perfect cleaning result.

Super Clean Air HEPA 12 filter



This Super Clean Air HEPA 12 filter catches at least 99.5% of all harmful microscopic vermin that causes respiratory allergies.

Improved cyclone



This EasyClean has an improved cyclone that filters even more dust out the the air.

Easy to empty dust bucket



The bagless vacuum cleaner has a transparent dust bucket that shows the dust removed from your floor and makes it easy to find back accidentally sucked up valuables.

11 m reach



Thanks to its 8 m cord you have a 11 m reach without having to switch the plug.

Specifications

Design

Model: Anti-allergy
Color(s): Raven black

Motor

Max. input power: 1800 W
IEC input power: 1600 W
Max. suction power: 300 W
Airflow: 36 l/s
Vacuum: 29 kPa

Vacuum cleaner specifications

Noise level Lc IEC: 79 dB
Electronic power control: Yes, on appliance
Exhaust filter: Super clean air HEPA 12 filter (FC8044)
Tube: Metal lacquered telescopic tube
Coupling: Button coupling
Carrying handle: Top
Wheels: Plastic wheels
Cyclonic filter: HEPA 10, Gore-Tex (FC8047/02)
Dust capacity: 2 l
Cord length: 8 m
Action radius: 11 m
Park/storage assist
Weight: 6 kg

Accessories

Nozzle: Standard, all purpose nozzle
Accessories: Brush and crevice nozzle
Accessory storage: Tube clip

