




Philips PerformerPro  
Vacuum cleaner with bag  
with TriActive+ nozzle

- 2200W
- Parquet



FC9192/01



Highest suction power, even as the bag fills up\*

with 2200W motor and 5L dust capacity

With its powerful 2200W motor and specially designed dust chamber, Philips PerformerPro vacuum cleaner maintains high airflow, giving you the highest suction power. For great cleaning results, even as the bag fills up!\*

#### Excellent cleaning results

- 2200 Watt motor generating max. 500W suction power
- Revolutionary Airflow Max technology for extreme suction
- 5L dust capacity for longer cleaning
- New 3-in-1 TriActive+ nozzle picks up coarse and fine dust

#### Integrated Anti-Allergy system

- HEPA AirSeal with HEPA 12 filter retains 99.5% of dust
- s-bag Ultra Long Performance captures even more fine dust

#### Superior hard-floor cleaning

- Super Parquet nozzle removes 3 x more sticky dirt

#### Convenience

- 360Flex hose swivel for smooth maneuvering
- SmartLock coupling to easily adjust to each cleaning task
- Long reach for convenient cleaning
- Extra long grip with air slide for farther reach

**PHILIPS**

# Highlights

## 2200 Watt motor



2200 W motor generates max. 500W suction power for excellent cleaning results.

## TriActive+ nozzle



The TriActive+ nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down 2) It sucks up big bits with its larger opening at the front 3) It sweeps up the dust and dirt closely alongside furniture and walls with its two side brushes

## Super Parquet nozzle

The Super Parquet nozzle allows you really clean hard floors of all kinds in one go, without the risk of harming them. Using the absorption capacity of the micro-fibre pads, together with the suction power of the vacuum cleaner, you achieve maximum result without requiring any detergents or brushes.

## HEPA AirSeal with HEPA12




HEPA 12 filter and AirSeal capture even the finest dust before the air is blown out for a dust-free environment and clean, allergen free air. The exhaust air is even cleaner than the air in the room.

## s-bag Ultra Long Performance



The Philips s-bag Ultra Long Performance made of five layers of high quality, non-clogging material captures even the finest dust. This excellent filtration gives you a better cleaning result and clean air in your home. The multilayer filtration also maintains the vacuum cleaners high suction power during the entire lifetime of the bag. The s-bag ULP has been tested and certified by the independent test institute TÜV Rheinland Group, proven to last up to 80% longer than a standard dustbag.

## Long reach



11 m reach allows you to clean a larger surface without having to switch the plug.

## 5L dust capacity



The specially designed 5L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

## Airflow Max technology



Airflow Max technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get the highest suction power, even as the bag fills-up!

# Specifications

## Design

- Color: Full red

## Performance

- Airflow (max): 51 l/s
- Input power (IEC): 1800 W
- Input power (max): 2200 W
- Noise level (Lc IEC): 79 dB
- Suction power (max): 500 W
- Vacuum (max): 36 kPa

## Usability

- Tube type: Metal 2-piece telescopic tube
- Handgrip: Ergonomic grip with air slider
- Tube coupling: SmartLock
- Carrying handle: Top and front
- Dust bag full indicator
- Park or storage assist: Vertical and horizontal
- Power control: Electronic on appliance
- Wheel type: Rubber

- Action radius: 11 m
- Cord length: 8 m

## Filtration

- Dust bag type: s-bag Ultra Long Performance
- Exhaust filter: HEPA 12 with Airseal
- Motor filter: Triple layer
- Dust capacity: 5 l
- HEPA Air Seal

## Nozzles and accessories

- Standard nozzle: TriActive+ nozzle
- Additional nozzle: Super Parquet nozzle
- Accessories: Crevice tool, 2-in-1 brush/small nozzle
- Accessory storage: On tubeclip

## Weight and dimensions

- Weight of product: 5.0 kg
- Dimensions of product (LxWxH): 500 x 310 x 300 mm



Issue date 2013-06-08

Version: 7.0.1

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* Suction power tested in accordance with international standard IEC 60312-1, tested by external test institute SLG Prüf- und Zertifizierungs GmbH (Philips Consumer LifeStyle B.V., August 2012)