


# PHILIPS

Bagless vacuum cleaner

All floors



FC9210/01



## Professional cleaning

High cleaning power that lasts and lasts

Thanks to Philips' new Cyclone Filter technology, the bagless Marathon delivers suction power that lasts. Its efficient design and 2000 W motor deliver very high max. suction power in its category, and it's the quietest bagless available.

### **Thorough cleaning results all the time**

- 2000 Watt motor generating max. 350 Watt suction power
- High performance cyclone filter for lasting suction power

### **Highly efficient anti-allergy system**


- HEPA AirSeal plus HEPA 13 washable filter

### **Easy cleaning, even around furniture**

- Tri-active nozzle with unique 3-in-1 action

## Highlights

### Powerful and quiet motor



The Marathon's powerful 2000 Watt motor generates very high max. suction power in its category. Its efficient design makes it also exceptionally quiet.

### HEPA AirSeal, HEPA 13 filter



This vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

### Tri-active nozzle



This unique nozzle is aerodynamically designed for maximum cleaning efficiency, has side brushes to remove dust from corners and curves, and has a front opening to pick up the big bits. Each stroke will deliver an immediate clean result.

## Specifications

### Design

Color(s): Black  
Model: All Floors

### Motor

Max. input power: 2000 W  
IEC input power: 1800 W  
Max. suction power: 350 W  
Airflow: 40 l/s  
Vacuum: 30 kPa

### Vacuum cleaner specifications

Noise level Lc IEC: 76 dB  
Electronic power control: Yes, on appliance  
HEPA AirSeal  
Exhaust filter: HEPA 13 washable filter (FC8038)  
Dust capacity: 2 l  
Cord length: 7 m  
Tube: Metal lacquered telescopic tube  
Action radius: 10 m  
Coupling: Button coupling  
Carrying handle: Top  
Wheels: Rubber wheels  
Park/storage assist  
Weight: 7.2 kg

### Accessories

Nozzle: Tri-active nozzle  
Accessories: Brush, crevice and small nozzle  
Accessory storage: On handgrip

