


PHILIPS

Bagless vacuum cleaner

ErgoFit

AutoClean

RemoteControl



FC9266/01



Maximum comfort, minimum effort

Enjoy a better posture with up to 70% less bending

Feel the relief of a better posture! This vacuum cleaner results in significantly less bending while cleaning and brings you more comfort

Helps prevent strain on back and wrists

- Unique ergonomically designed PostureProtect handle

Change controls without bending down

- Controls in the handle with LCD-display, with ECO-setting

Effortless manoeuvring

- Rotating hose connection for easier manoeuvring

Outstanding suction power

- 2000 Watt motor generating max. 375 Watt suction power

Effortlessly maintain optimal suction

- Automatic filter-cleaning system

Highlights

PostureProtect handle



The patented PostureProtect handle offers you a 4 x better body posture: it helps to prevent bending while cleaning; it supports keeping your wrist in a comfortable position; both handles make manoeuvring easy; and you can regulate the vacuum cleaner with fingertip controls.

Fingertip control, LCD-display




With the buttons on the handgrip you can easily operate your vacuum cleaner — without bending! The LCD screen shows you the suction power level and time you spent cleaning. Also it reminds you when to clean the filter-cylinder. How easy! The ECO-setting enables you to clean in an energy-efficient way.

Rotating hose connection



This hose has a pivoting connection to the handle and therefore allows for easier manoeuvring and less wrist strain.

Outstanding cleaning power



Very efficient 2000 Watt motor, generating a suction power of max. 375 Watt.

Automatic filter-cleaning



Effortlessly maintain optimal suction power with only one touch of a button. This automatic filter-cleaning system unclogs your filter without touching the dust.

Exceptionally silent



The sound level of this product is very low within its category.

Specifications

Design

Colour: Bordeaux red
Material: Luxe

Filtration

Dust capacity: 1.5 l
Exhaust filter: Ultra Clean Air HEPA 13 washable filter
Filter cleaning system: AutoClean system
Filter type: Gore-Tex HEPA 10
HEPA AirSeal

Nozzles and accessories

Accessories: Crevice tool, Small nozzle
Accessory storage: On handgrip
Standard nozzle: TriActive nozzle

Performance

Airflow (max): 37 l/s
Input power (IEC): 1800 W
Input power (max): 2000 W
Noise level (Lc IEC): 76 dB
Suction power (max): 375 W
Vacuum (max): 33 kPa

Usability

Action radius: 13 m
Carrying handle: Top and front
Cord length: 9 m
Tube coupling: Button
Handgrip: PostureProtect handle
Power control: Electronic on handgrip
Tube type: Aluminium 3-piece telescopic tube
Wheel type: Rubber

Weight and dimensions

Weight of product: 7.9 kg

