

Philips SilentStar
Vacuum cleaner with bag
with SilentSeal nozzle

Eco

SilentSeal nozzle
HEPA 13 washable filter



FC9302/01



The power of silence

Tough on dust, gentle on your ears

Enjoy a relaxing, undisturbed home life with Philips SilentStar vacuum cleaner. With its unique SilentSeal nozzle, this vacuum cleaner delivers powerful cleaning performance with minimal noise.

Minimum noise, maximum suction

- Optimal performance & low noise due to the SilentSeal nozzle
- Aerodynamic air channel reduces noise to a quiet 70 dB

Low power consumption, high-power results

- 1250 Watt HD motor delivering 2000 Watt performance*

Highly efficient anti-allergy system

- HEPA AirSeal plus HEPA 13 washable filter
- ECARF Seal of Quality for trusted results

Easy to use all over the house

- Two comfortable carrying handles for extra convenience



asimpleswitch.com




asimpleswitch.com

PHILIPS


Highlights

SilentSeal nozzle



The SilentSeal nozzle contributes to an optimal performance in both low noise and dust and fluff pick up. It is optimally sealed for efficient airflow resulting in best cleaning performance - made by WesselWerk.

Aerodynamic air channel



The air channel has been finetuned to make sure the air slides a smooth way out that minimizes noise creation. Additionally a special motor suspension reduces vibrations.

New 1250 Watt HD motor

Highly efficient 1250 Watt HD (High Density) motor generates max. 400 Watt suction power, which


means that it uses 30% less energy with the same cleaning result as a 2000 Watt appliance.*

HEPA AirSeal, HEPA 13 filter



This Philips vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

Comfortable carrying handles



This vacuum cleaner has not one, but two carrying handles. When it is on its wheels, there is a handle on top which enables you to easily move the cleaner around with very little bending. The second handle on the front side of the appliance enables you to comfortably carry it around in an upright position.

Specifications

Design

- Color: Mystic blue

Filtration

- Dust bag type: s-bag
- Exhaust filter: Ultra Clean Air HEPA 13 washable filter
- HEPA AirSeal
- Dust capacity: 3.5 l

Nozzles and accessories

- Accessories: Brush, Crevice tool, Small nozzle
- Accessory storage: On handgrip
- Standard nozzle: Low noise SilentSeal nozzle

Performance

- Airflow (max): 42 l/s
- Input power (IEC): 1250 W
- Input power (max): 1250 W
- Noise level (Lc IEC): 70 dB
- Suction power (max): 400 W
- Vacuum (max): 32 kPa

Sustainability

- Packaging: > 90% recycled materials
- User manual: 100% recycled paper

Usability

- Carrying handle: Top and front
- Clean Comfort cassette
- Tube coupling: Button
- Dust bag full indicator
- Power control: Electronic on appliance
- Tube type: Metal 2-piece telescopic tube
- Wheel type: Rubber
- Action radius: 11 m
- Cord length: 8 m

Weight and dimensions

- Dimensions of product (LxWxH): 500 x 290 x 250 mm
- Weight of product: 6.8 kg



Issue date 2018-03-23

Version: 9.1.1

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Philips internal measurement; 2010.