

PHILIPS

Bagless vacuum cleaner

PowerPro Active

1.7 L

Turbo brush



FC9533/09



Full performance with PowerCyclone 4 Quick and easy emptying

The new Philips PowerPro Active bagless vacuum cleaner delivers top cleaning performance, thanks to PowerCyclone technology and TriActive+ nozzle, engineered to maximize dust pick-up. The dust container is easy to empty, with no dust cloud.

Remarkable cleaning results

- PowerCyclone 4 technology separates dust and air in one go
- New 3-in-1 TriActive+ nozzle picks up coarse and fine dust
- Turbo Brush nozzle removes 25% more hairs and dust

Effortless cleaning

- Advanced dust container design for hygienic emptying
- ActiveLock couplings to easily adjust to each cleaning task
- Reach all corners thanks to the extra long ergonomic grip
- Soft brush integrated into handle, always ready to use
- Variable power setting

Clean air filter system

- Ultra-Hygiene filter captures more than 99% of fine dust

Highlights

PowerCyclone 4 Technology



PowerCyclone 4 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

TriActive+ nozzle



The TriActive+ nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It sweeps up the dust and dirt alongside furniture and walls with its two side brushes.

Turbo Brush nozzle



The Turbo Brush nozzle allows deep cleaning of carpets and quick hair and fluff removal from carpets. The rotating brush actively removes small dust particles and hairs, resulting in a

25% better cleaning performance on carpets. The wheels of the nozzle prevent damage in case of use on hard-floors.

Easy to empty dust container




The dust container is carefully designed to dispose collected dirt without creating a dust cloud. It is one-hand operated and thanks to its unique shape and smooth surface, you can easily control the emptying of the dust container.

ActiveLock couplings



The ActiveLock couplings allow you to easily connect and disconnect the different nozzles and accessories from the telescopic tube while cleaning.

Extra long ergonomic grip




This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

Soft brush at your fingertips




A dusting brush attachment is built right into the handle so it's always ready to use for furniture, flat surfaces and upholstery.

Power control



The variable power setting allows you to select the optimal level of suction for the different types of surfaces you vacuum.

Ultra-Hygiene filter



Developed to capture the finest dust before the air is blown out, to meet the needs of people demanding a higher level of hygiene.

Specifications

Performance

Airflow (max): 27,8 l/s
Input power (IEC): 750 W
Sound power level: 78 dB
Vacuum (max): 16,8 kPa

Usability

Action radius: 9 m
Carrying handle: Top and front
Cord length: 6 m
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber
Tube coupling: ActiveLock
Power control: Electronic on appliance

Design

Color: Dark Royal Blue

Filtration

Dust capacity: 1,7 L
Exhaust filter: Microfilter
Motor filter: Ultra-Hygiene

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
Accessory storage: On tubeclip

Additional nozzle: Hard floor nozzle, Turbo brush

Standard nozzle: TriActive+ nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 473 x 304 x 301 mm
Weight of product: 6 kg

