

# PHILIPS

Bagless vacuum cleaner

PowerPro Expert

Parquet+



FC9723/09



## 40% more dust pick-up\* for a better clean

### Designed for easy dust disposal

Philips PowerPro Expert bagless vacuum cleaner takes cleaning performance to the next level. PowerCyclone 6 and TriActiveMax nozzle ensure exceptional cleaning results on all floors. Specially designed bucket makes emptying effortless.

#### Exceptional performance

- A-class performance on hard floors
- PowerCyclone 6 for exceptional dust and air separation
- New 3-in-1 TriActiveMax nozzle maximizes dust pick-up
- Ultra slim flexible hard floor nozzle
- Nozzle for optimal cleaning on all hard floors

#### Easy dust disposal

- Advanced dust bucket design for easy emptying

#### Effortless cleaning

- Lifetime washable filter
- Lightweight design for maneuverability

#### Clean air filter system

- EPA10 filter system with AirSeal for healthy air



asimpleswitch.com

# Highlights

## A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

## PowerCyclone 6



The aerodynamic design of PowerCyclone 6 minimizes air resistance and ensures exceptional cleaning performance through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

## TriActiveMax nozzle



TriActiveMax nozzle with 3-in-1 cleaning actions perfectly seals to the floor to maximize dust pick-up. 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its

larger opening at the front 3) It sweeps up the dust and dirt closely alongside furniture and walls with its two side brushes.

## DiamondFlex hard floor nozzle



Ultra slim hard floor nozzle for top maneuverability and reach. Ultra slim design and 180 degree rotation enable easy reach in tight spaces and under furniture. Larger front opening picks up bigger pieces.

## Easy to empty dust bucket



The dust container is perfectly designed for effortless dust disposal. Thanks to its unique shape and smooth surface, dust is collected at one side of the bucket and evenly glides into the dust bin.

## Lifetime washable filter



The foam filter can be easily washed under the tap for life-long performance.

## Lightweight design



Only 5.5 kg lightweight design ensures great maneuverability.

## Hard floors nozzle



The Hard floors nozzle ensures optimal cleaning on all hard floors, especially on parquet and tiles. 1) The special soft brush hairs protect the floors against scratches. 2) The soft bristles pattern ensures optimal dust collection on all hard floors. 3) The nozzle is lightweight and equipped with wheels for great maneuverability on all floors.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Performance

Annual energy consumption: 27.9 kW-h  
Sound power level: 76 dB  
Airflow (max): 26 l/s  
Vacuum (max): 17 kPa  
Input power (IEC): 650 W

## Usability

Power control: Electronic on appliance  
Tube type: Metal 2-piece telescopic tube  
Tube coupling: SmartLock  
Wheel type: Rubber  
Carrying handle: Top and front  
Action radius: 10 m  
Cord length: 7 m

## Design

Color: Titanium

## Filtration

Exhaust filter: EPA 10 filter  
Motor filter: Lifetime washable filter  
Dust capacity: 2 L

## Nozzles and accessories

Standard nozzle: TriActiveMax nozzle  
Additional nozzle: DiamondFlex nozzle, Hard floor nozzle  
Accessories included: Crevice tool, 2-in-1 brush/small nozzle

## Sustainability

Packaging: > 90% recycled materials  
User manual: 100% recycled paper

## Weight and dimensions

Weight of product: 5.5 kg  
Dimensions of product (LxWxH):  
505x292x292 mm  
Dimensions of packaging (LxWxH):  
650x330x310 mm

