

PHILIPS

Bagless vacuum cleaner

7000 series

900 W

PowerCyclone 8

Allergy Lock

Mini turbo brush



FC9744/09

Highest suction power with PowerCyclone 8* AllergyLock capturing >99.9%** of fine dust

The Philips Bagless Vacuum 7000 Series features our highest ever suction power. Make supreme cleaning effortlessly simple with PowerCyclone 8 technology and TriActive+ nozzle featuring 3 optimized cleaning actions in one.

Superior performance

- 900W motor for high suction power
- 99.9% dust pick-up*** to deliver high cleaning performance
- PowerCyclone 8 enables highest suction power for longer
- Allergy Lock traps dust inside for a high level of hygiene
- TriActive+ nozzle to deliver high performance on all floors
- CarpetClean nozzle slides easy for a deep carpet cleaning
- Mini Turbo brush for easy (pet) hair and fluff removal
- Allergy H13 filter system captures >99.9% of fine dust


Effortless cleaning

- On board accessories: Conveniently stored, always at hand
- Digital power control function to adjust suction power
- Dust container designed for hygienic emptying with one hand
- Soft brush integrated into handle, always ready to use



Highlights

High-efficiency 900W motor



High-efficiency 900W motor with over 50,000 RPM, generates high suction power for a superior clean every time. Register at Philips.com within 3 months of purchase for a 5-year motor warranty.

99.9% dust pick-up***



TriActive+ nozzle and extreme suction power ensure you can vacuum 99.9% of fine dust***.

PowerCyclone 8 technology



PowerCyclone 8 technology features a powerful, swirling action to maximize air flow and enable highest suction power. Super accelerated air flow in the cylindrical chamber efficiently separates dust from the air at >185km/h, ensuring stronger suction power for longer, for immaculate cleaning results.

Allergy lock



Allergy Lock system uses a sensor to ensure dust container is fully sealed before operating, trapping dust and allergens inside for a clean and ultra hygienic environment.

TriActive+ nozzle



TriActive+ nozzle utilizes 3 cleaning actions in one go. It features a larger opening at the front to suck up larger debris while the specially designed soleplate removes dust from deep within carpets. Air channels and brushes on both sides of the nozzle pick up any dust and dirt alongside walls or furniture.

On board accessories



Onboard accessories are stored conveniently inside the back compartment so they're always easy to access when you need them.



IF DESIGN AWARD 2018

IF award-winning products and projects, concepts and more, selected by the top names in design. For 65 years, the iF DESIGN AWARD has been recognized as an arbiter of quality for exceptional design. The iF label is renowned worldwide for outstanding design services, and the iF DESIGN AWARD is one of the most important design prizes in the world.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



5 years warranty

Register at philips.com/welcome within 3 months of purchase to enjoy 5-year warranty on the motor for free!

Specifications

Performance

Airflow (max): 32.5 l/s

Input power (max): 900 W

Sound power level: 67 – 75 dB

Nozzles and accessories

Accessory storage: On board

Additional nozzle: Mini turbo brush, Carpet Clean nozzle, Hard floor nozzle

Standard nozzle: TriActive+ nozzle

Accessories included: Crevice tool, Integrated brush, Small nozzle

Extra accessories: Filter replacement: FC8003/01

Design

Color: Opal green

Filtration

Dust capacity: 2 L

Exhaust filter: Allergy H13 filter

Motor filter: Lifetime washable filter

Filtration level: HEPA13 level****

Sustainability

Packaging: > 90% recycled materials

Stand-by power consumption: < 0,5 W

User manual: 100% recycled paper

Usability

Action radius: 10 m

Carrying handle: Top and front

Cord length: 7 m

Power control: Electronic on appliance

Tube coupling: SmartLock

Tube type: Metal 2-piece telescopic tube

Wheel type: Rubber

Weight and dimensions

Dimensions of product (LxWxH):

505x292x292 mm

Weight of product: 5.5 kg

