

PHILIPS

Bagless vacuum cleaner

PowerPro Ultimate

2,2L NanoClean

Super Parquet



FC9921/09



Full performance with PowerCyclone Mess free dust disposal

The new Philips PowerPro Ultimate bagless vacuum cleaner stands for superior cleaning performance. PowerCyclone 7 enables exceptional dust and air separation. TriActiveMax nozzle is for excellent performance on all floors.

Superior performance

- PowerCyclone 7 keeps strong suction power for longer
- Multi-Purpose nozzle
- TriActive Z hard floor nozzle for dust and crumbs
- Allergy filter captures more than 99.90% of fine dust

Mess free dust disposal

- NanoClean Technology for mess free dust disposal
- Extra Ergonomic Dust Bucket for controlled emptying

Effortless cleaning

- ErgoGrip remote control for No - bend Play and Pause
- Adjustable, long reach tool for hard-to-reach places



asimpleswitch.com

Highlights

PowerCyclone 7



The aerodynamic design of PowerCyclone 7 minimizes air resistance and ensures exceptional cleaning performance through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air

TriActiveMax nozzle



TriActiveMax nozzle perfectly seals to the floor and performs 3 actions in one go to thoroughly clean your floors: 1) A specially designed sole plate gently opens the carpet and removes the dust from deep down. 2) Larger front opening pick up bigger particles. 3) Side brushes ensure perfect cleaning along the plinths.

TriActive Z hard floor nozzle



The new TriActive Z hard floor nozzle removes all dust and crumbs in one go. Unique Z-shaped design guides the dust and the bigger crumbs into the air channel without pushing

them forward. Side air channels perfectly clean along the plinths. Now there is no more need to lift the nozzle to remove bigger crumbs and ensure an exceptional clean of your hard floors.

Allergy filter



Developed to meet the specific needs of allergy sufferers and more generally of people demanding a higher level of hygiene.

NanoClean Technology



The new innovative technology is especially developed to prevent the usual dust cloud. The new innovative technology is especially developed to prevent the usual dust cloud. The dust settles at the bottom of the dust bucket rather than staying in the air. When the bucket is opened there is no usual dust cloud.

Extra Ergonomic Dust Bucket



The side of the bucket has a specially designed spout-like shape. This enables to empty the bucket in a controlled manner without spilling the dust.

ErgoGrip Remote Control



ErgoGrip remote control enables easy maneuverability of the nozzle in tight spaces. Integrated remote control makes it easy to increase, reduce the power or even turn off the vacuum cleaner.

Extra long reach

Our long reach tool helps you clean high shelves or cupboard tops, with an adjustable brush for precision performance.



5 years warranty

Register at philips.com/welcome within 3 months of purchase to enjoy 5-year warranty on the motor for free!



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Performance

Sound power level: 75 dB
Airflow (max): 27 l/s
Vacuum (max): 17 kPa
Input power (IEC): 650 W

Design

Color: Titanium

Usability

Tube type: Aluminium 2-P telescopic tube
Carrying handle: Top and front
Power control: Remote control
Tube coupling: SmartLock

Wheel type: Rubber

Action radius: 11 m

Cord length: 8 m

Filtration

Exhaust filter: HEPA13 filter

Motor filter: Lifetime washable filter

Dust capacity: 2.2 L

Nozzles and accessories

Accessories included: Crevice tool, 2-in-1 brush/small nozzle

Additional nozzle: Hard floor nozzle, TriActiveZ

nozzle

Standard nozzle: TriActiveMax nozzle

Extra accessories: Remote control

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Weight and dimensions

Dimensions of packaging (LxWxH): 595 x 400 x 352 mm

Dimensions of product (LxWxH): 506 x 310 x 317 mm

Weight of product: 6.2 kg

