



Philips PowerLife
Steam iron with
SteamGlide soleplate and
Safety Auto Off

Steam 40g/min; 130g steam boost

SteamGlide soleplate
Safety Auto off + Anti-calc
2400 Watts



GC2965/80



Built for powerfull ironing

With electronic safety shut-off

For great results day after day, you want an iron that never lets you down. With its new SteamGlide soleplate, constant high steam output and Calc buster pill, this practical iron gives you value for money that lasts!

Easily removes creases

- Continuous steam output up to 40 g/min
- 130 g steam boost to remove stubborn creases easily

Powerful performance

- 2400 Watt enables constant high steam output

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Comfortable ironing

- Cord freedom with the 360 degree swivel solution
- Vertical steam for crease removal in hanging fabrics

Safe ironing

- 3 ways of Safety Auto Off

PHILIPS

Highlights

2400 Watt

2400 W
max

2400 Watt enables constant high steam output.

Up to 40 g/min of steam



Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 130 g



The steam boost can be used for vertical steaming and tough creases.

Cord freedom


Cord freedom with the 360 degree swivel solution

SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistancy, glides excellent and is easy to clean.

Vertical steam



Vertical
shot of steam

This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

Safety Auto Off

Safety
auto
off

Iron shuts off automatically when the iron is hold still for 30s on soleplate, 30s lying on a side or standing on its heel rest for 8 minutes.

Specifications

Fast & powerful crease removal

- Soleplate: SteamGlide
- Vertical steaming
- Variable steam settings
- Spray

Comfortable ironing

- Cord length: 1.8 m

Easy to use

- Water tank capacity: 300 ml
- Drip stop
- Safety auto off
- Cord freedom (swivel): 360 degree cord freedom
- Extra stability: Rubber bumper
- Power cord length: 1.8 m outside Europe, 1.9 m within Europe

Calc management

- Suitable for tap water
- Calc clean solution: Double active calc clean

Technical specifications

- Power Global: 2400 W
- Voltage: 220-240 V

Weight and dimensions

- Product dimensions: 29.5 x 11.6 x 19.5
- Product weight: 1.2 kg

Crease removal

- Continuous steam: Up to 40 gr/min
- Steam Boost: Up to 130 gr/min



Issue date 2015-07-30

Version: 4.0.1

EAN: 08 71010 36328 87

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com