

PHILIPS

Steam iron

3300 series

2300W

35 g/min steam

100g steam boost

GC3330/32



Great results, minimum effort

3x easier

This Philips steam iron offers you not only extra convenience because of the large water inlet, extra-long cord and water-level indicator; its new SteamGlide soleplate also makes ironing easier and smoother!

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Comfortable ironing

- Less refilling with extra-large 300 ml water tank
- Extra-long 3 m cord for maximum reach
- Extra-clear indicator for highly visible water level
- Soft grip for lasting ironing comfort

Longer lifetime

- Double Active Calc System prevents scale build-up

Reaches into tricky areas

- Pointed tip for ironing tricky areas

Safe ironing

- Drip-stop system keeps your garments spotless while ironing

Highlights

Drip-stop system



The Drip Stop system of your Philips steam iron lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

300 ml water tank



Fewer refills are required thanks to a large 300 ml water tank. So you can iron more clothes in one go.

Double Active Calc System



Double Active Calc system of your Philips steam iron prevents scale build-up through anti scale pills and an easy to use calc clean function.

Extra-long 3 m cord



With the extra-long 3 m cord of your Philips iron, you can easily reach right up to the edges of your ironing board - and further!

Highly visible water level



The extra-clear indicator of your Philips iron, makes the water level highly visible, so you always know if you have enough water at a glance.

Pointed tip



The uniquely pointed tip allows you to iron even the hardest to reach areas.

SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistancy, glides excellent and is easy to clean.

Soft grip

The soft handgrip of this Philips iron allows for comfortable ironing even during longer sessions.

Specifications

Comfortable ironing

Additional comfort: 360 degree cord freedom, Extra-clear water level indicator, Soft grip

Cord length: 3 m

Water tank capacity: 300 ml

Crease removal

Continuous steam: Up to 35 gr/min

Reaching tricky areas: Pointed tip Spray

Steam Boost: Up to 100 gr/min

Vertical Steam

Easy to use

Easy to set up and store: Extra-large water inlet, Integrated cord storage solution

Technical specifications

Frequency: 50-60

Power: 2300

Voltage: 220 - 240

Weight and dimensions

Product dimensions: 328 x 129 x 163

Product weight: 1,64

