

Philips
Steam iron



GC4490

2400 W Power tool for ironing

More power, more steam, more performance

This powerful iron comes with the most robust soleplate of all irons. Nothing can scratch this iron while it glides smoothly over your garment. The powerful steam boost helps you to blast all creases away easily.

Easily removes creases

- Continuous steam output up to 40 g/min

Powerful performance

- 2400W for 40g steam output
- Robust scratch proof soleplate

Reaches into tricky areas

- Steam tip allows you to have steam in hard-to-reach areas

Safe ironing

- Drip-stop system keeps your garments spotless while ironing

PHILIPS
sense and simplicity

Specifications

Fast & powerful crease removal

- Soleplate: Anodilium
- Continuous steam output
- Continuous steam output: 40 g/min
- Steam boost: 100 g
- Vertical steam
- Spray
- Steam tip
- Power: 2400 W

Easy to use

- Water tank capacity: 335 ml
- Filling and emptying water: Extra large filling hole

- Drip stop
- Soft grip
- Cord storage: Cord clip
- Power cord length: 3 m
- Cord freedom (swivel): 360 degree cord freedom

Calc management

- Suitable for tap water
- Calc clean solution: Double active calc clean

Technical specifications

- Weight of iron: 1.6 kg
- Voltage: 220 - 240 V

Highlights

Anodilium soleplate man iron

For an endless excellent gliding experience.

Up to 40 g/min of steam



Continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.



Issue date 2012-01-06

Version: 4.0.1

© 2012 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com