



Philips Azur  
Steam iron with Anodilium  
soleplate

**2600 W**

170 g steam boost



**GC4890**

## 2600 W Power tool for ironing

More power, more steam, more performance

This powerful iron comes with the most robust soleplate of all irons. Nothing can scratch this iron while it glides smoothly over your garment. The powerful steam boost helps you to easily blast all creases away.

### **Easily removes creases**

- 170 g steam boost for the most stubborn creases
- Steam output of up to 50 g/min for better crease removal
- 2600 W for quick heat up and powerful performance

### **Easy gliding on all fabrics**

- Scratch-resistant, highly durable Anodilium soleplate

### **Reaches into tricky areas**

- Steam tip allows you to have steam in hard-to-reach areas

### **Safe ironing**

- Drip-stop system keeps your garments spotless while ironing

**PHILIPS**

sense and simplicity

Steam iron with Anodilium soleplate  
2600 W 170 g steam boost

## Specifications

### Fast and powerful crease removal

- Soleplate: Anodilium
- Continuous steam output
- Continuous steam output: 50 g/min
- Steam boost: 170 g
- Vertical steam
- Spray
- Steam tip
- Power: 2600 W

### Easy to use

- Water tank capacity: 350 ml
- Filling and emptying water: Extra large filling hole

- Drip stop
- Soft grip
- Cord storage: Cord clip
- Power cord length: 2.5 m
- Cord freedom (swivel): 360 degree cord freedom

### Calc management

- Suitable for tap water
- Calc clean solution: Double active calc clean


### Technical specifications

- Weight of iron: 1.6 kg
- Voltage: 220 - 240 V

GC4890/02


## Highlights

### Anodilium soleplate



Excellent gliding, excellent scratch resistance, excellent to clean, excellent durability!

### Steam tip



The unique steam tip combines the prominently pointed front of the soleplate with special elongated steam slots in the tip, to reach into the smallest and most difficult areas for the best ironing results.

### Drip-stop system

Drip-Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

### Continuous steam up to 50 g

Continuous steam output of up to 50 g/min for better crease removal

### 2600 W for quick heat up

2600 W for quick heat up and powerful performance

### 170 g steam boost



Applying the steam boost will release a steam shot up to 170 g to remove even the toughest creases



Issue date 2012-05-04

Version: 9.1.1

© 2012 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)