

Steam generator
iron

PerfectCare Pure

Max 5 bar pump pressure

240 g steam boost

PureSteam cartridge

GC7631/20



Faster and easier ironing

Powerful, compact, 5 years warranty against scale

Iron your garments without adjusting temperature thanks to the revolutionary OptimalTEMP technology. Most compact & lightest steam generator, easy to store & carry. 99% calc free, Pure Steam anti-scale cartridges increase life by 5 times

Carefree ironing, no temperature setting required

- Iron from jeans to silk with no temperature setting required
- Safe to leave the hot soleplate on the ironing board

Fast and powerful ironing

- Ready to use in 2 minutes with unlimited refill
- Max 5 bar pump pressure
- 1.5 L water tank, up to 2 hours of ironing
- 99% calc-free with PureSteam Anti-scale cartridge
- The most compact and lightest steam generator
- Steam boost up to 240 g
- Our best gliding soleplate

Highlights

Steam ready in 2 minutes



Steam is ready to use in 2min and can be refilled at anytime during ironing.

Max 5 bar pump pressure



The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

1.5 L water tank



Thanks to the 1.5 L watertank capacity, you can iron up to 2 hours continuously without any refills. The large filling hole makes the refilling fast. You can either fill your steam generator iron under the tap or use a jug / large bottle.

99% calc-free

PureSteam Anti-scale cartridge filters 99% of scale from tap water. It ensures consistent steam flow and prevents calc residues on clothes.

Compact and light

The compact design makes your appliance easy to storage. Space will never be an issue again! As it is very light, your appliance is easy to carry. Its light weight iron will make your ironing much more comfortable.

OptimalTEMP technology



"Now you can iron from jeans to silk with no temperature setting required. Guaranteed no burn on all ironable fabrics. Revolutionary technology with the 1) Advanced Smart Control Processor which controls precisely the soleplate temperature. You do not need to adjust temperature 2) Compact ProVelocity steam engine delivers more steam for ironing faster. It enables compact design of your steam generator for easier storage"

Safe rest



The Philips innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. During ironing, no need to put your iron

back to the base station, just leave the hot iron soleplate directly on the garments or cotton ironing board cover without additional resting accessory. It will not damage any of your ironable garments, neither the board. This makes your ironing easier with less wrist efforts.

Steam boost up to 240 g

The steam boost can be used for vertical steaming and tough creases.

T-ionicGlide soleplate



Our best gliding and most scratch resistant, 5star rated soleplate with integrated Titanium-Oxide layer



Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO₂ emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast & powerful crease removal

Soleplate: T-ionicGlide
OptimalTEMP technology
Vertical steaming
Steam tip
Power: 2400 W
Steam boost: 240 g
Continuous steam output: 120 g/min
Pressure: Max 5 bar
Safe rest
Turbo steam
Variable steam settings

Easy to use

Water tank capacity: 1500 ml
Filling and emptying water: Extra large filling hole
Refill any time
Heat up time: 2 min
Hose storage: Hose storage compartment
Cord storage: Cord clip
Hose length: 1.6 m
Safe for all fabrics: Even for delicates like silks
Power cord length: 1.8 m

Sustainability

Energy saving mode
User manual: 100% recycled paper

Calc management

Suitable for tap water
Calc clean solution: PureSteam Anti-scale cartridge
Calc clean reminder

Weight and dimensions

Packaging dimensions (WxHxL): 40 x 23 x 28 cm
Product dimensions (WxHxL): 35.4 x 19.3 x 22.4 cm
Weight of iron: 1.2 kg
Weight of iron + base: (with 1 cartridge) 3.19 kg

