

# PHILIPS

Steam generator  
iron

FastCare

Max 5.5 bar pump pressure

250 g steam boost

Carry lock

2.2 L detachable watertank



GC7715/80



## Fast and convenient ironing

### With detachable water tank

A large detachable water tank for easy refill, strong steam boost and the SteamGlide Ceramic soleplate will help you reducing your ironing time significantly while carry lock and Smart CalcClean make ironing convenient.

#### Maximum convenience

- 2,2L XL detachable water tank, ideal for families
- Carry lock for easy and safe transportation
- Refill tap water anytime
- Silent Steam for quiet ironing while watching TV
- Intelligent calc clean reminder with sound & light
- Automatically turned off for peace of mind and energy saving

#### Fast ironing

- Max 5.5 bar pump pressure
- Ready to use in 2 minutes with unlimited refill
- Smooth and easy gliding with Steam Glide Ceramic soleplate
- Continuous steam
- Steam boost up to 250g

# Highlights

## 2,2 L detachable water tank



A large detachable water tank for easy refill, strong steam boost and the SteamGlide Ceramic soleplate will help you reducing your ironing time significantly while carry lock and Smart CalcClean make ironing convenient

## Safe Carry Lock



Your steam generator iron comes with a safety carry lock. You can lock your iron safely on the base, making it safer and reducing the risk of people touching the hot soleplate. You can also carry the steam generator easily.

## Refill tap water anytime



Your steam generator iron is designed to use tap water. While ironing, when you run out of water in the watertank, you can refill it easily without waiting or turning your appliance off.

## Quiet ironing



Watching TV or listening to music while ironing? This steam generator iron operates on a low noise level for an even more pleasant ironing experience.

## Smart Calc Clean



Smart Calc Clean is an integrated descaling and cleaning function to protect your appliance. To ensure an optimal steam performance, long lasting life and in order to prevent white flakes, your steam generator iron will remind you to perform the descaling process. For maximum convenience make sure to always use the Smart Calc Clean container provided with your appliance.

## Max 5,5 bar pump pressure



The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

## Ready to use in 2 minutes



Steam is ready to use in 2min and can be refilled at anytime during ironing.

## SteamGlide Ceramic soleplate



SteamGlide Ceramic combines good gliding and scratch resistance to help in smooth ironing

## Continuous steam



The more steam, the faster the ironing. The unique technology used in a Philips steam generator iron generates powerful steam making ironing easier, better and faster.

## Steam boost up to 250 g



The steam boost can be used for vertical steaming and tough creases.

# Specifications

## Easy to use

Heat up time: 2 min

Power cord length: 1.6 m

Safety auto off

Water tank capacity: 2200 ml

Detachable water tank

Ready to use: Sound indicator

Refill any time during use

Soleplate name: SteamGlide Ceramic

Tap water suitable

## Fast crease removal

Continuous steam: 120 g/min

Power: 2400 W

Pressure: 5.5

Steam boost: 250 g

Steam-on-demand

Voltage: 220-240 V

## Green efficiency

User manual: 100% recycled paper

## Guarantee

2 year worldwide guarantee

## Storage

Carry lock: For transportation and safety

Hose storage: Hose storage compartment

## Technology

ProVelocity steam engine

