

# PHILIPS

Steam generator  
iron

PerfectCare Silence

Up to 6 bar pressure

270 g steam boost

Carry lock

1.5L detachable water tank



GC9520/02



## Ultra fast and quiet ironing

### Ultra fast and quiet ironing

Enjoy ironing with family around, while watching tv, without being disturbed by the noise. Philips PerfectCare Silence steam generator iron combines powerful steam and fast ironing at low sound.

#### Carefree ironing, no temperature setting required

- Silent steam technology: Powerful steam with minimum sound
- Iron from jeans to silk with no temperature setting required
- Safe to leave the hot soleplate on the ironing board

#### Fast and powerful ironing

- Descale effectively and easily your appliance to prolong it
- Steam boost up to 270 g
- Ready to use in 2 minutes with unlimited refill
- Up to 6 bar pressure
- 1.5 L detachable water tank, up to 2 hours of ironing
- Lock your iron securely to the base station



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## Silent steam Technology



Enjoy ironing with family around or while watching TV, without being disturbed by the noise of the steam. Silent steam technology delivers quiet yet very powerful steam. The steam generator is fitted with silencing steam filters to reduce the noise of the steam, and a sound-absorbing platform to reduce the noise of the pump in the base.

## OptimalTEMP technology



Now you can iron from jeans to silk with no temperature setting required. Guaranteed no burn on all ironable fabrics. Revolutionary technology with the 1) Advanced Smart Control Processor which controls precisely the soleplate temperature. You do not need to adjust temperature 2) Powerful Cyclonic steam chamber which delivers powerful consistent steam, making ironing easier and faster.

## Easy De-Calc



Ultra long lasting steam performance: Philips' exclusive Easy De-Calc function provides the ideal way to get rid of limescale and extend the lifetime of your steam generator iron. Your iron will remind you with light and sound when

to perform cleaning. Only when your appliance is cold, simply open the Easy De-Calc knob, and collect the dirty water and scale in a cup.

## Safety carry lock



Your steam generator iron comes with a safety carry lock. You can lock your iron safely on the base, making it safer, reducing the risk of people touching the hot soleplate. You can also carry the steam generator easily.

## Safe rest



The Philips innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. During ironing, no need to put your iron back to the base station, just leave the hot iron soleplate directly on the garments or cotton ironing board cover without additional resting accessory. It will not damage any of your ironable garments, neither the board. This makes your ironing easier with less wrist efforts.

## Steam boost up to 270 g



The steam boost can be used for vertical steaming and tough creases.

## Steam ready in 2 minutes



Steam is ready to use in 2min and can be refilled at anytime during ironing.

## Up to 6 bar pressure

The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

## 1.5 L detachable water tank

The watertank can be removed to be refilled easily under the tap. The large filling hole makes the refilling fast. Thanks to the 1.5 L watertank capacity, you can iron up to 2 hours continuously without any refills.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Fast & powerful crease removal

OptimalTEMP technology

Pressure: Up to 6

Steam boost: 270 g

Soleplate: SteamGlide

Safe rest

Variable steam settings

Vertical steaming

Steam output control

Steam tip

Power: 2400 W

## Easy to use

Heat up time: 2 min

Refill any time

Safety auto off

Storage solution: Carry lock

Safe for all fabrics: Even for delicates like silks

Water tank capacity: 1500 ml

Filling and emptying water: Detachable water tank, Extra large filling hole

Power cord length: 1.8 m

Cord storage: Cord storage compartment

Hose length: 1.7 m

Hose storage: Hose storage compartment

Cord freedom (swivel): 180 degree cord freedom

## Sustainability

Energy saving mode

## Calc management

Suitable for tap water

Calc clean reminder

Calc clean solution: Easy De-calc

## Technical specifications

Weight of iron: 1.2 kg

Weight of iron + base: 5.4 kg

Product dimensions: 28.3 x 26.3 x 42.4 cm

Packaging dimensions: 33.5 x 30.5 x 49.1 cm

Voltage: 220 - 240 V

