



Philips PerfectCare Elite
Steam generator iron

Max 6.7 bar pressure

Up to 470 g steam boost
1.8 L water tank capacity
Detachable water tank



GC9630/20

Most powerful steam for the fastest ironing*

with Ultra-light iron

PerfectCare Elite is the best and most efficient steam generator iron from Philips. With OptimalTEMP technology, you can now iron from jeans to silk with no temperature setting needed. Guaranteed no burns on all ironable garments.

No temperature setting needed, guaranteed no burn

- Iron jeans to silk, no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board
- Tested and approved by independent textile experts

Fast ironing with continuous powerful steam

- Powerful steam for ultimate crease removal
- Easy and efficient descaling system
- Philips best gliding and most scratch resistant soleplate
- Save energy with ECO mode

Ultimate ironing experience

- Light weight and comfortable to handle
- Large detachable water tank for easy refilling
- Safe and secure carry lock
- Automatic switch off for safety and energy saving



asimpleswitch.com

PHILIPS


Highlights

1.8 L detachable water tank



The detachable water tank allows you to easily refill anytime without stopping the appliance. It has a large filling hole so you can simply fill the water tank under the tap. It has a 1.8 L capacity, so you get the convenience of up to 2 hours of continuous use, with no need to top-up the tank.

Energy saving



ECO mode allows you to save energy without compromising your ironing results. The ECO mode uses a reduced amount of steam, but still a sufficient amount to iron all your garments.

OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing

temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron fabrics from jeans to silk, with guaranteed no burns thanks to the perfect combination of temperature and continuous powerful steam.

Safe carry lock



Your steam generator iron includes a safe carry lock which securely fastens your iron to its base without the risk of slipping or someone touching the hot soleplate. It ensures safe and easy transportation around the house, to and from storage.

Safe rest



Innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. As well as the reassurance this provides whilst ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often

Safety auto off



The safety auto off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you safety peace of mind.



Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Steam generator iron

Max 6.7 bar pressure Up to 470 g steam boost, 1.8 L water tank capacity, Detachable water tank

GC9630/20

Specifications

Easy to use

- Cord freedom (swivel): 360 degree cord freedom
- Detachable water tank
- Extra large filling hole
- Heat up time: 2 min
- Hose length: 1.7 m
- Low water alert
- Power cord length: 1.8 m
- Precision steam tip
- Ready to use: Light indicator, Sound indicator
- Refill any time during use
- Safe on all fabrics: Even delicates like silk
- Safety auto off
- Soleplate gliding performance: 5 stars
- Soleplate name: T-ionicGlide
- Soleplate scratch resistance: 5 stars
- Tap water suitable
- Water tank capacity: 1800 ml

Fast crease removal

- Continuous steam: Up to 135 g/min
- Power: Max 2400 W
- Pressure: Max 6.7 bar
- Ready to use: 2 min
- Steam boost: Up to 470 g
- Steam-on-demand
- Variable steam levels
- Vertical steam
- Voltage: 220 - 240 V

Green efficiency

- Energy saving mode

- Product packaging: 100% recyclable
- User manual: 100% recycled paper

Guarantee

- 2 year worldwide guarantee

Scale management

- Descaling and cleaning: Easy De-calc Plus
- Descaling reminder: Light, Yes

Size and weight

- Packaging dimensions (WxHxL): 31 x 35 x 51 cm
- Product dimensions (WxHxL): 23.3 x 28.5 x 45.3 cm
- Weight of iron: 0.8 kg
- Weight of iron + base: 5.1 kg

Storage

- Carry lock: For transportation and safety
- Cord storage: Cord storage compartment, Velcro fix
- Hose storage: Hose storage compartment

Technology

- Cyclonic steam chamber
- For all ironable fabrics
- No burn
- No temperature setting needed
- OptimalTEMP Technology
- Smart Control Processor



Issue date 2017-08-02

Version: 19.2.1

EAN: 08 71010 38033 55

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Iron weight & steam rate (norm IEC60311), vs. the 10 best selling steam generators; tested Dec. 2014